



BASIC SWITCH W/O ACTUATOR HEAD METAL ENCLOSURE, ACC.TO EN50041 ASISAFE INTEGRATED AS-I STATUS:1:F-IN1, 2:F-IN2 3:AS-I/FAULT SLOW-ACTION CONTACTS 2 NC, W/ M12 CONNECTOR 4-POLE CHANNEL 1 ON NC,CHANNEL 2 ON NC

Product designation		basic switch with ASIsafe
Manufacturer article number		
<ul style="list-style-type: none"> <li>of the supplied basic switch</li> </ul>		<a href="#">3SF1114-1KA00-1BA1</a>

General technical data:

Product function		
<ul style="list-style-type: none"> <li>positive opening</li> </ul>		Yes
Insulation voltage		
<ul style="list-style-type: none"> <li>Rated value</li> </ul>	V	30
Degree of pollution		class 3
Shock resistance		30g / 11 ms
Vibration resistance		0.35 mm / 5g
Surge voltage resistance Rated value	kV	0.8
Mechanical service life (switching cycles)		
<ul style="list-style-type: none"> <li>typical</li> </ul>		15 000 000
Protection class IP		IP66/IP67
Equipment marking		
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> <li>acc. to DIN EN 81346-2</li> </ul>		B B
Active principle		mechanical
Repeat accuracy	mm	0.1

Enclosure:

Design of the housing		block, narrow
Material of the enclosure		metal
Coating of the enclosure		cathodic immersion coating
Design of the housing acc. to standard		Yes

### Drive Head:

Design of the switching function	positive opening
----------------------------------	------------------

### Connections/ Terminals:

Type of electrical connection	plug M12
-------------------------------	----------

### Mechanical data:

Design of plug-in connection	M12 plug, 4-pole: Pin 1 = ASI+ , Pin 2 = not assigned, Pin 3= ASI-, Pin 4 = not assigned
------------------------------	--

### Ambient conditions:

<b>Ambient temperature</b>		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +80

### Supply voltage:

<b>Type of voltage of the supply voltage</b>		
• of the optional LED indicator		DC
<b>Supply voltage</b>		
• of LED	V	24

### Installation/ mounting/ dimensions:

mounting position	any
Mounting type	screw fixing

### Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Special Test Certificate](#)

[other](#)

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

#### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

#### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SF11141KA001BA1>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SF11141KA001BA1/all>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SF11141KA001BA1&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SF11141KA001BA1&lang=en)



last modified:

09.03.2015