

Connector Plug

7/8"; 5-pin

ZAT77NN01



Part Number



Technical Data

Mechanical Data	
Connection 1	Plug, straight
Connection mode 1	7/8", 5-pin
Torque	0,4 Nm
Cable Diameter	8...10 mm
Wire cross-section	≤ 1,5 mm ²
Assembling	Screw Terminal Technology
Degree of Protection	IP67
Temperature Range	-40...90 °C
Material Sleeve Nut	Aluminum, anodised
Packaging unit	1 Piece
Connection Diagram No.	S82
Connection Equipment No.	77

● Plug 7/8", straight



Legend			
+	Supply Voltage +	PT	Platinum measuring resistor
-	Supply Voltage 0 V	nc	not connected
~	Supply Voltage (AC Voltage)	U	Test Input
A	Switching Output (NO)	Ū	Test Input inverted
Ā	Switching Output (NC)	W	Trigger Input
V	Contamination/Error Output (NO)	W-	Ground for the Trigger Input
Ṽ	Contamination/Error Output (NC)	O	Analog Output
E	Input (analog or digital)	O-	Ground for the Analog Output
T	Teach Input	BZ	Block Discharge
Z	Time Delay (activation)	AW	Valve Output
S	Shielding	a	Valve Control Output +
RxD	Interface Receive Path	b	Valve Control Output 0 V
TxD	Interface Send Path	SY	Synchronization
RDY	Ready	SY-	Ground for the Synchronization
GND	Ground	E+	Receiver-Line
CL	Clock	S+	Emitter-Line
E/A	Output/Input programmable	≡	Grounding
IO-Link	IO-Link	SnR	Switching Distance Reduction
PoE	Power over Ethernet	Rx +/-	Ethernet Receive Path
IN	Safety Input	Tx +/-	Ethernet Send Path
QSSD	Safety Output	Bus	Interfaces-Bus A(+)/B(-)
Signal	Signal Output	La	Emitted Light disengageable
BL-D +/-	Ethernet Gigabit bidirect. data line (A-D)	Mag	Magnet activation
EN ^{resaz}	Encoder 0-pulse 0-0 (TTL)	RES	Input confirmation
		EDM	Contactor Monitoring
		EN ^{resaz}	Encoder A/A (TTL)
		EN ^{resaz}	Encoder B/B (TTL)
		ENA	Encoder A
		ENb	Encoder B
		AMIN	Digital output MIN
		AMAX	Digital output MAX
		AOK	Digital output OK
		SY in	Synchronization In
		SY OUT	Synchronization OUT
		OLr	Brightness output
		M	Maintenance
		rsv	reserved
			Wire Colors according to DIN IEC 757
		BK	Black
		BN	Brown
		RD	Red
		OG	Orange
		YE	Yellow
		GN	Green
		BU	Blue
		VT	Violet
		GY	Grey
		WH	White
		PK	Pink
		GNYE	Green/Yellow

Specifications are subject to change without notice