

Flat and copy milling heads

For milling inserts: RCKX, OCKX, XCKX, XOKX, SAHT

ATORN[®]

Application


With a total of 5 different insert types in different cemented carbide grades, there is a wide range of application possibilities. Minimum-vibration milling is guaranteed with low chipping forces and good chip removal for round, square or octagonal inserts. The low cutting force reduces the drive power required by up to 25%, which facilitates use on less efficient machines without issue.

Version

- Wear-resistant, nickel-plated version
- With internal cooling
- Clamping screw tightening torque (indexable insert) M5 = 8 Nm

Advantage

- Versatile with its 5 different insert types
- Low chipping forces
- Minimum-vibration milling
- Low power consumption
- High axial infeed



Art. No.	16027 180
Max. cutting edge diameter	80 mm
Length	50 mm
Bore diameter	27 mm
Number of cutting edges	6 PCS

EAN-Code

4050293538892