



HBL7465V -- Twist-Lock Valise Plug



| Product Specifications | |
|-------------------------------------|--|
| Product Type |  <p>Twist-Lock Devices</p> |
| Product Item | Connector Body |
| Wiring Scheme | 2 Pole, 2 Wire Non-Grounding |
| Amperage | 15A |
| Voltage | 125V AC |
| NEMA Configuration | ML-1R |
| Item Style | Valise |
| Device Color | Black |
| Cord Dia. | .218"-.375" (5.5-9.5) |
| Blade Holder Material | Black Nylon |
| Housing Material | Black nylon |
| Cord Clamp Material | Nylon |
| Blade Material | Brass |
| Terminal Clamp Material | Cold rolled steel-nickel-plated |
| Terminal Screw Material | #8-32 Steel (copper flash, nickel plate & molykote) |
| Cord Clamp Screw Material | Steel-zinc-plated |
| Body Holding Screw Material | Steel-zinc-plated |
| Ratings | Molded into face |
| Dielectric Voltage Withstand | 2000V minimum |

| | |
|--------------------------------|---|
| Current Interrupting | Certified for current interrupting at full rated current. |
| Temperature Rise | Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75. |
| Cord Accommodation | Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49. |
| Terminal Accommodation | 15A-#14AWG |
| Terminal Identification | Terminals identified in accordance with UL 498 (Black, White) |
| Flammability | HB or better per UL 94 or CSA 22.2 No. 0.6 |
| Operating Temperatures | Maximum Continuous 75 C Minimum -40 C (w/o impact) |
| Moisture Resistance | IP20 |
| Catalog Page | Click here for catalog page B2 |
| Brochures | Click here for product brochure |
| Hubbellnet | Click here for Hubbellnet |
| Catalog Section | Click here for Section-B |
| UPC Number | 78358523728 |
| Weight in LBs | 0.1 |