

PRODUCT DATASHEET FP16561_LISA3-WW-PIN

LISA3-WW-PIN

~45° wide beam with location pin installation

TECHNICAL SPECIFICATIONS:

Dimensions Ø 9.9 mm

Height 7 mm

Fastening pin

Colour black

Box size 310 x 230 x 60 mm

Box weight 1.4 kg

Quantity in Box 2000 pcs

ROHS compliant yes 10




MATERIAL SPECIFICATIONS:

Component Type Material Colour

LISA3-WW Single lens PMMA LISA3-HLD-PIN Holder PC



PRODUCT DATASHEET FP16561_LISA3-WW-PIN





PRODUCT DATASHEET FP16561_LISA3-WW-PIN

PHOTOMETRIC DATA (MEASURED):



Published: 21/01/2019

PRODUCT DATASHEET FP16561_LISA3-WW-PIN

PHOTOMETRIC DATA (SIMULATED):




LED XP-E FWHM 51.0°

Efficiency 91 %

Peak intensity 1.230 cd/lm

LEDs/each optic 1 Light colour White Required components:




CREE \$

LED XP-E2

FWHM 45.0° Efficiency 90 %

Peak intensity 1.460 cd/lm

LEDs/each optic 1 Light colour White Required components:




CREE 🕏

LED XP-G2 FWHM 49.0°

Efficiency 90 %

Peak intensity 1.900 cd/lm LEDs/each optic 1

LEDs/each optic 1
Light colour White
Required components:



CREE 🕏


 LED
 XP-G2 HE

 FWHM
 53.0°

 Efficiency
 86 %

Peak intensity 1.022 cd/lm

LEDs/each optic 1
Light colour White
Required components:



PRODUCT DATASHEET FP16561_LISA3-WW-PIN

PHOTOMETRIC DATA (SIMULATED):


CREE 💠

LED XT-E **FWHM** 44.0°

Efficiency 87 %

Peak intensity 1.470 cd/lm LEDs/each optic 1

Light colour White Required components:




MUMILEDS

LED LUXEON 3030 2D (Round LES)

FWHM 37.0° 86 % Efficiency Peak intensity 1.890 cd/lm

LEDs/each optic 1 White Light colour Required components:




LUMILEDS

LED LUXEON TX **FWHM** 45.0°


Efficiency 87 % Peak intensity 1.420 cd/lm

LEDs/each optic 1 Light colour White Required components:



MUMILEDS

LED LUXEON V2 **FWHM** 44.0° Efficiency 89 % Peak intensity 1.480 cd/lm




PHOTOMETRIC DATA (SIMULATED):



LED LUXEON Z **FWHM** 38.5° Efficiency 89 % Peak intensity 1.950 cd/lm

LEDs/each optic 1 Light colour White Required components:




MUMILEDS

LED LUXEON Z ES

FWHM 40.0° 90 % Efficiency Peak intensity 1.922 cd/lm


LEDs/each optic 1 White Light colour Required components:



WNICHIA


LED NVSW219D **FWHM** 50.0° Efficiency 86 % Peak intensity 1.110 cd/lm

LEDs/each optic 1 Light colour White Required components:



WNICHIA

LED NVSW219F **FWHM** 52.0° Efficiency 88 % Peak intensity 1.136 cd/lm



PRODUCT DATASHEET FP16561_LISA3-WW-PIN


PHOTOMETRIC DATA (SIMULATED):

WNICHIA

LED NVSxx19B/NVSxx19C

FWHM 45.0° Efficiency 85 % Peak intensity 1.320 cd/lm

LEDs/each optic 1 Light colour White Required components:




OSRAM Opto Semiconductors

LED Duris S5 (2 chip)

FWHM 36.0° 88 % Efficiency Peak intensity 1.890 cd/lm

LEDs/each optic 1 White Light colour Required components:




OSRAM Opto Semiconductors

LED Duris S5 (Single chip)

FWHM 37.0° Efficiency 86 % Peak intensity 1.910 cd/lm


LEDs/each optic 1 Light colour White Required components:



OSRAM Opto Semiconductors

LED OSCONIQ P 3030

FWHM 38.0° Efficiency 87 % 1.898 cd/lm Peak intensity



PRODUCT DATASHEET FP16561_LISA3-WW-PIN

PHOTOMETRIC DATA (SIMULATED):


OSRAM

LED

OSLON Square CSSRM2/CSSRM3

FWHM 43.0° 88 % Efficiency Peak intensity 1.590 cd/lm

LEDs/each optic 1 Light colour White Required components:




OSRAM Opto Semiconductors

LED

OSLON Square EC

FWHM 44.0° 88 % Efficiency Peak intensity 1.420 cd/lm

LEDs/each optic 1 White Light colour Required components:




OSRAM Opto Semiconductors

LED OSLON SSL 150


FWHM 45.0° Efficiency 90 % Peak intensity 1.420 cd/lm

LEDs/each optic 1 Light colour White Required components:



SAMSUNG

LED LH351C **FWHM** 46.0° Efficiency 85 % 1.270 cd/lm Peak intensity



PHOTOMETRIC DATA (SIMULATED):

SAMSUNG


LED LH351D

FWHM 47.0°

Efficiency 84 %

Peak intensity 1.100 cd/lm

LEDs/each optic 1 Light colour White Required components:



SAMSUNG


LED LM301A

FWHM 36.0°

Efficiency 88 %

Peak intensity 1.980 cd/lm

LEDs/each optic 1
Light colour White
Required components:




SAMSUNG

LED LM302A

FWHM 38.0° Efficiency 88 %

Peak intensity 1.860 cd/lm

LEDs/each optic 1
Light colour White
Required components:



9/10



PRODUCT DATASHEET FP16561_LISA3-WW-PIN

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

10/10

www.ledil.com/ where_to_buy