

BLINDNIETE


FLACHRUNDKOPF (~ DIN EN ISO 15979)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15979)


RIVETS AVEUGLES

TÊTE PLATE (~ DIN EN ISO 15979)



Stahl verzinkt
Steel zinc plated
Acier zingué

Stahl verzinkt
Steel zinc plated
Acier zingué



Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,15 mm

D2 = 8,0 + 0 / - 1,0 mm

k = 1,0 + / - 0,3 mm

d = 2,5 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

4,1 mm

	F-Max		CODE				
4,0 x 6,0 mm	10,9 mm	0,5 - 2,5 mm	70801 40600	1550 N	1990 N	1000	10000
4,0 x 8,0 mm	12,9 mm	2,5 - 4,5 mm	70801 40800			1000	10000
4,0 x 10,0 mm	14,9 mm	4,5 - 6,5 mm	70801 40100			1000	10000
4,0 x 12,0 mm	16,9 mm	6,5 - 8,5 mm	70801 40120			1000	10000
4,0 x 14,0 mm	18,9 mm	8,5 - 10,5 mm	70801 40140			500	5000
4,0 x 16,0 mm	20,9 mm	10,5 - 12,5 mm	70801 40160			500	5000
4,0 x 18,0 mm	22,9 mm	12,5 - 14,5 mm	70801 40180			500	5000
4,0 x 20,0 mm	24,9 mm	14,5 - 16,5 mm	70801 40200			500	5000
4,0 x 24,0 mm	28,9 mm	17,5 - 19,5 mm	70801 40240			500	5000
4,0 x 25,0 mm	29,9 mm	18,5 - 20,5 mm	70801 40250			500	5000
4,0 x 30,0 mm	34,9 mm	20,0 - 25,0 mm	70801 40300	500	5000		

Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm

D2 = 9,5 + 0 / - 1,0 mm

k = 1,1 + / - 0,3 mm

d = 2,9 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

4,9 mm

	F-Max		CODE				
4,8 x 6,0 mm	11,4 mm	1,0 - 2,5 mm	70801 48060	2300 N	2920 N	500	5000
4,8 x 8,0 mm	13,4 mm	2,5 - 4,5 mm	70801 48080			500	5000
4,8 x 10,0 mm	15,4 mm	4,5 - 6,0 mm	70801 48100			500	5000
4,8 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70801 48120			500	5000
4,8 x 14,0 mm	19,4 mm	8,0 - 10,0 mm	70801 48140			500	5000
4,8 x 16,0 mm	21,4 mm	10,0 - 11,5 mm	70801 48160			500	5000
4,8 x 18,0 mm	23,4 mm	11,5 - 13,5 mm	70801 48180			500	5000
4,8 x 20,0 mm	25,4 mm	13,5 - 15,0 mm	70801 48200			500	5000
4,8 x 22,0 mm	27,4 mm	15,0 - 17,0 mm	70801 48220			500	5000
4,8 x 25,0 mm	30,4 mm	17,0 - 20,0 mm	70801 48250			250	2500
4,8 x 30,0 mm	35,4 mm	20,0 - 25,0 mm	70801 48300			250	2500
4,8 x 35,0 mm	40,4 mm	25,0 - 30,0 mm	70801 48351			250	2500
4,8 x 40,0 mm	45,4 mm	30,0 - 35,0 mm	70801 48400			250	2500