

## 0.50mm Pitch FFC/FPC - F32D Series

# RIGHT ANGLE ZIF FLEX CONNECTOR

F32D series is a 0.50mm pitch right angle ZIF flex connector with back flip mechanism, dual contact and surface mount termination. This connector features a height of 2.00mm and comes in 10 to 60 contacts. This series features a cable thickness of 0.30mm and provide enhanced durability of 30 mating cycles. It comes with a robust design and prevent solder and flux wicking. These are ideal for automotive, data, industrial, communication, consumer and medical applications.

- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Ensures high solderability and high durability



- ZIF (Zero Insertion Force) mechanism
- Back flip feature
- Design against solder and flux wicking
- High-temperature thermoplastic housing
- 10 to 60 positions available
- Lead and halogen-free

#### **BENEFITS**

- Absence of frictional mating wear resulting in high mating cycle life
- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Provides high solderability and high durability
- Wide operating temperature range of -40°C to +105°C
- Comprehensive range to satisfy different customer requirements
- Meets environmental, health and safety requirements

#### **TECHNICAL INFORMATION**

#### **MATERIAL**

- Housing: LCP, natural color (UL94V-0)
- Actuator: PA9T, black color (UL94V-0)
- Contact: Phosphor bronze, T=0.15mm
- Anchor-plate: Brass, T=0.15mm
- Mylar: T=0.10mm, thermostable, yellow color

#### **MECHANICAL PERFORMANCE**

- FFC/FPC Retention Force: 40gf/pin
- Terminal Retention Force: 50gf/terminal min
- Anchor-plate Retention Force: 100gf/plate min.
- Durability: 30 mating cycles

#### **ELECTRICAL PERFORMANCE**

- Voltage Rating: 50V AC/DC
- Current Rating: 0.5A
- Contact Resistance: 30MΩ max.
- Insulation Resistance:  $100M\Omega$  min.
- Dielectric Withstanding Voltage: No short or breakdown after 500V AC, 2mA, 1min.

#### **PACKAGING**

■ Tape & Reel

#### APPROVALS AND CERTIFICATIONS

- UL file number E106764
- RoHS compliant

#### **SPECIFICATION**

Aorora Product Specification: IS.EQC.052

#### **ENVIRONMENTAL**

■ Operating Temperature Range: -40°C to +105°C

#### **TARGET MARKETS/APPLICATIONS**



Car Multimedia Car Navigation Dashboard PND



Base Station Power Switches



Notebook Tablets Wearables Gaming DSC LCD & PDP TV



Router Server ODD HDD




Sensing element Monitoring camera Human Machine Interface Industrial PC Robotics



Ultrasonic Patient Monitor MRI CT Infusion Pump

### **PART NUMBER SELECTOR**



40R0RAF32D1019EA4