Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878 Issue date: 29/08/2022 Revision date: 29/08/2022 Supersedes version of: 04/03/2020 Version: 5.00

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : Silbergleit

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Use of the substance/mixture : Lubricating agent Lubricants and additives

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer/Supplier Email competent person

Service & Dienstleistung Kindle Jürgen sds@kft.de

Uhlsbergstraße, 34 77933 Lahr Germany

T 0176/80193553

1.4. Emergency telephone number

Emergency number : GIZ-Nord, Göttingen

Germany +49 551 19240

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315

Specific target organ toxicity – Single exposure, Category 3, Narcosis H336

Hazardous to the aquatic environment – Chronic Hazard, Category 3 H412

Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

Causes skin irritation. May cause drowsiness or dizziness. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



GHS07

Signal word (CLP)

: Warning

Contains

Kerosine (petroleum), hydrodesulfurized

Hazard statements (CLP)

: H315 - Causes skin irritation.

H336 - May cause drowsiness or dizziness.

H412 - Harmful to aquatic life with long lasting effects.

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Precautionary statements (CLP) : P261 - Avoid breathing mist, vapours, spray.

P264 - Wash hands thoroughly after handling.

P273 - Avoid release to the environment.

P280 - Wear protective gloves, protective clothing.
P302+P352 - IF ON SKIN: Wash with plenty of water.
P312 - Call a POISON CENTER, doctor if you feel unwell.

2.3. Other hazards

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

Component	
Paraffin waxes and Hydrocarbon waxes (8002-74-2)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
Kerosine (petroleum), hydrodesulfurized (64742-81-0)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
aluminium powder (stabilised) (7429-90-5)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Paraffin waxes and Hydrocarbon waxes substance with national workplace exposure limit(s) (GB)	CAS-No.: 8002-74-2 EC-No.: 232-315-6	≥ 70 - < 80	Not classified
Kerosine (petroleum), hydrodesulfurized	CAS-No.: 64742-81-0 EC-No.: 265-184-9 EC Index-No.: 649-423-00-8 REACH-no: 01-2119462828- 25-xxxx	≥ 20 - < 25	Skin Irrit. 2, H315 STOT SE 3, H336 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
aluminium powder (stabilised) substance with national workplace exposure limit(s) (GB) (Note T)	CAS-No.: 7429-90-5 EC-No.: 231-072-3 EC Index-No.: 013-002-00-1 REACH-no: 01-2119529243- 45-xxxx	≥ 0.25 – < 1	Flam. Sol. 1, H228 Water-react. 2, H261

Note T: This substance may be marketed in a form which does not have the physical hazards as indicated by the classification in the entry in Part 3. If the results of the relevant method or methods in accordance with Part 2 of Annex I of this Regulation show that the specific form of substance marketed does not exhibit this physical property or these physical hazards, the substance shall be classified in accordance with the result or results of this test or these tests. Relevant information, including reference to the relevant test method(s) shall be included in the safety data sheet. Full text of H- and EUH-statements: see section 16

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : In all cases of doubt, or when symptoms persist, seek medical attention.

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.

First-aid measures after skin contact : Wash skin with plenty of water. Take off contaminated clothing. If skin irritation occurs: Get

medical advice/attention.

First-aid measures after eye contact : Rinse eyes with water as a precaution. Remove contact lenses, if present and easy to do.

Continue rinsing. If eye irritation persists: Get medical advice/attention.

First-aid measures after ingestion : Rinse mouth out with water. Do NOT induce vomiting. Call a poison center or a doctor if you

feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : Local irritation symptoms. May cause drowsiness or dizziness.

Symptoms/effects after skin contact : Irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire. Water spray. Dry powder. Foam.

Carbon dioxide.

Unsuitable extinguishing media : Strong water jet.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released. Carbon monoxide. Carbon dioxide. Aluminium oxides.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained

breathing apparatus. Complete protective clothing.

Other information : Do not allow run-off from fire fighting to enter drains or water courses. Disposal must be

done according to official regulations. Cool closed containers exposed to fire with water

spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Ensure adequate air ventilation. Spills of this product present a serious slipping hazard.

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes. Avoid breathing mist, vapours,

spray.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information

refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid sub-soil penetration. Prevent entry to sewers and public waters. Notify authorities if product enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material. Take up mechanically (sweeping, shovelling)

and collect in suitable container for disposal.

Other information : Ensure adequate air ventilation. Disposal must be done according to official regulations.

29/08/2022 (Revision date) GB - en 3/11

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

6.4. Reference to other sections

Information for safe handling. See section 7. Concerning personal protective equipment to use, see section 8. For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wear personal protective equipment. Ensure good ventilation of the work station. Avoid

contact with skin and eyes. Use only outdoors or in a well-ventilated area. Avoid breathing

mist, vapours, spray.

Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the

product. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Ground/bond container and receiving equipment.

Storage conditions : Store in a well-ventilated place. Keep cool. Store locked up. Keep container tightly closed.

Information about storage in one common storage : Keep away from food, drink and animal feeding stuffs.

facility

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

Paraffin waxes and Hydrocarbon waxes (8002-74-2)		
United Kingdom - Occupational Exposure Limits		
Local name Paraffin wax		
WEL TWA (OEL TWA) [1]	2 mg/m³ fume	
WEL STEL (OEL STEL) 6 mg/m³ fume		
Regulatory reference EH40/2005 (Fourth edition, 2020). HSE		
aluminium powder (stabilised) (7429-90-5)		
United Kingdom - Occupational Exposure Limits		
Local name Aluminium		
WEL TWA (OEL TWA) [1] 2 mg/m³ alkyl compounds 2 mg/m³ salts, soluble 10 mg/m³ metal, inhalable dust 4 mg/m³ metal, respirable dust		
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE	

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

8.2.2.1. Eye and face protection

Eye protection:

Use splash goggles when eye contact due to splashing is possible. EN 166

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing. EN ISO 13688. EN 13034

Hand protection:

Chemically resistant protective gloves. Butyl rubber. Nitrile rubber. EN 374. Please follow the instructions related to the permeability and the penetration time provided by the manufacturer. Choosing the proper glove is a decision that depends not only on the type of material, but also on other quality features, which differ for each manufacturer. Gloves must be replaced after each use and whenever signs of wear or perforation appear

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment. Breathing apparatus with filter. Filter A (colour code: brown). EN 143. Breathing equipment is only to be used in order to handle the residual risk of short term jobs if all other risk minimizing measures have been carried out e.g. retention and/or local exhaust

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

Other information:

Do not eat, drink or smoke when using this product. Avoid contact with skin and eyes. Always wash hands after handling the product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid Colour : colourless. Appearance : Pasty. Odour : turpentine. Odour threshold : Not available : Not applicable Melting point : Not available Freezing point Boiling point : 175 °C Flammability : Not applicable

Explosive properties : Product is not explosive.

Oxidising properties : Non oxidizing.

Explosive limits : Not available

Lower explosion limit : Not applicable

Upper explosion limit : Not applicable

Flash point : 67 °C (DIN 22719)

Auto-ignition temperature : $> 300 \, ^{\circ}\text{C}$ Decomposition temperature : Not available pH : Not available

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Viscosity, kinematic $> 20.5 \text{ mm}^2/\text{s}$ Solubility : Water: Insoluble Partition coefficient n-octanol/water (Log Kow) : Not available Vapour pressure 8 mbar (20 °C) Vapour pressure at 50 °C : Not available : 0.8 g/cm3 (20 °C) Density Relative density : Not available Relative vapour density at 20 °C : Not available Particle characteristics : Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

9.2.2. Other safety characteristics

Other properties : No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

No decomposition if stored and applied as directed.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

No additional information available

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified (Based on available data, the classification criteria are not met) Acute toxicity (dermal) : Not classified (Based on available data, the classification criteria are not met) Acute toxicity (inhalation) : Not classified (Based on available data, the classification criteria are not met) Skin corrosion/irritation : Causes skin irritation. : Not classified (Based on available data, the classification criteria are not met) Serious eye damage/irritation Respiratory or skin sensitisation : Not classified (Based on available data, the classification criteria are not met) Germ cell mutagenicity : Not classified (Based on available data, the classification criteria are not met) Carcinogenicity : Not classified (Based on available data, the classification criteria are not met) Reproductive toxicity : Not classified (Based on available data, the classification criteria are not met)

STOT-single exposure : May cause drowsiness or dizziness.

y ,				
Kerosine (petroleum), hydrodesulfurized (64742-81-0)				
STOT-single exposure May cause drowsiness or dizziness.				
STOT-repeated exposure : Not classified (Based on available data, the classification criteria are not met)				
Aspiration hazard	: Not classified (Based on available data, the classification criteria are not met)			

29/08/2022 (Revision date) GB - en 6/11

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Silbergleit	
Viscosity, kinematic	> 20.5 mm²/s

11.2. Information on other hazards

No additional information available

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Harmful to aquatic life with long lasting effects.

Hazardous to the aquatic environment, short-term : Not classified (Based on available data, the classification criteria are not met)

(acute)

Hazardous to the aquatic environment, long-term : Harmful to aquatic life with long lasting effects.

(chronic)

Kerosine (petroleum), hydrodesulfurized (64742-81-0)		
LC50 - Fish [1] 2 - 5 mg/l (96 h; Oncorhynchus mykiss; (OECD 203 method))		
EC50 - Crustacea [1]	1.4 mg/l (48 h; Daphnia magna; OECD Guideline 202)	
EC50 72h algae	1 – 3 mg/l (72 h; Raphidocelis subcapitata; (OECD 201 method))	
NOEC chronic crustacea	0.48 mg/l (21 d; Daphnia magna; (OECD 211 method))	

12.2. Persistence and degradability

Paraffin waxes and Hydrocarbon waxes (8002-74-2)			
Persistence and degradability Inherently biodegradable.			
Biodegradation 31 % (28 d)			

12.3. Bioaccumulative potential

Paraffin waxes and Hydrocarbon waxes (8002-74-2)	
Partition coefficient n-octanol/water (Log Pow)	5.3 – 6.7

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

Contains no PBT/vPvB substances ≥ 0.1% assessed in accordance with REACH Annex XIII

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Disposal must be done according to official regulations. European waste catalogue. Do not discharge into drains or the environment. Do not dispose of with domestic waste.

29/08/2022 (Revision date) GB - en 7/11

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Product/Packaging disposal recommendations

HP Code

- : Recycle or dispose of in compliance with current legislation.
- : HP4 "Irritant skin irritation and eye damage:" waste which on application can cause skin irritation or damage to the eye.

HP14 - "Ecotoxic:" waste which presents or may present immediate or delayed risks for one or more sectors of the environment

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID	number			
Not applicable	Not regulated	Not regulated	Not applicable	Not applicable
14.2. UN proper shippir	ng name		,	
Not applicable	Not regulated	Not regulated	Not applicable	Not applicable
14.3. Transport hazard	class(es)			
Not applicable	Not regulated	Not regulated	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not regulated	Not regulated	Not applicable	Not applicable
14.5. Environmental ha	zards		•	
Not applicable	Not regulated	Not regulated	Not applicable	Not applicable

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not applicable

Rail transport

Not applicable

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

EU restriction list (REACH Annex XVII)		
Reference code	Applicable on	
3(b)	Silbergleit ; Kerosine (petroleum), hydrodesulfurized	

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

3(c)	Silbergleit ; Kerosine (petroleum), hydrodesulfurized
40.	aluminium powder (stabilised)

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Contains no substance subject to REGULATION (EU) No 1005/2009 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 September 2009 on substances that deplete the ozone layer.

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

Other information, restriction and prohibition

: Take note of Directive 94/33/EC on the protection of young people at work.

regulations

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on drug precursors)

15.1.2. National regulations

United Kingdom

National regulations

: This safety data sheet is for informational purposes only and does not comply with national legal requirements without reference to a national distributor. The national distributor is responsible for a legally compliant safety data sheet.

Take note of Directive 94/33/EC on the protection of young people at work.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

Version/s 3.00 is/are not available in this language.

Indication of changes				
Section	Changed item	Change	Comments	
	General revision			
1.3	Manufacturer/Supplier	Modified		
12.1	Ecotoxicity	Modified	LC50/EC50; CAS 64742-81-0	
15.1	National regulations	Added		
15.1	EU-Regulations	Added		

Abbreviations and acronyms:			
ATE	Acute Toxicity Estimate		
	RID		
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways		
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road		
LD50	Median lethal dose		
EC50	Median effective concentration		
IATA	International Air Transport Association		
LC50	Median lethal concentration		
PBT	Persistent Bioaccumulative Toxic		

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006		
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail		
SDS	Safety Data Sheet		
vPvB	Very Persistent and Very Bioaccumulative		
BCF	Bioconcentration factor		
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008		
DMEL	Derived Minimal Effect level		
DNEL	Derived-No Effect Level		
IARC	International Agency for Research on Cancer		
IMDG	International Maritime Dangerous Goods		
LOAEL	Lowest Observed Adverse Effect Level		
NOAEC	No-Observed Adverse Effect Concentration		
NOAEL	No-Observed Adverse Effect Level		
NOEC	No-Observed Effect Concentration		
OECD	Organisation for Economic Co-operation and Development		
PNEC	Predicted No-Effect Concentration		
STP	Sewage treatment plant		
TLM	Median Tolerance Limit		

Data sources : Information provided by the manufacturer. MSDSs of the suppliers. ECHA (European

Chemicals Agency).

Department issuing data specification sheet: : KFT Chemieservice GmbH

Im Leuschnerpark 3 D-64347 Griesheim

Phone: +49 6155-8981-400 Fax: +49 6155 8981-500

SDS Service: +49 6155 8981-522

Contact person : Dr. Lisa Schmitt

Full text of H- and EUH-statements:			
Aquatic Chronic 2	Hazardous to the aquatic environment – Chronic Hazard, Category 2		
Aquatic Chronic 3	Hazardous to the aquatic environment – Chronic Hazard, Category 3		
Asp. Tox. 1	Aspiration hazard, Category 1		
Flam. Sol. 1	Flammable solids, Category 1		
H228	Flammable solid.		
H261	In contact with water releases flammable gases.		
H304	May be fatal if swallowed and enters airways.		
H315	Causes skin irritation.		
H336	May cause drowsiness or dizziness.		
H411	Toxic to aquatic life with long lasting effects.		
H412	Harmful to aquatic life with long lasting effects.		
Skin Irrit. 2	Skin corrosion/irritation, Category 2		
STOT SE 3	Specific target organ toxicity – Single exposure, Category 3, Narcosis		

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Water-react. 2	Substances and Mixtures which, in contact with water, emit flammable gases, Category 2

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:					
Skin Irrit. 2	H315	Calculation method			
STOT SE 3	H336	Calculation method			
Aquatic Chronic 3	H412	Calculation method			

KFT SDS EU 00

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.