

## Safety data sheet according to 1907/2006/EC, Article 31

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML
- **Article number:** 440.0027100-0027109.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Sector of Use**
  - SU21 Consumer uses: Private households / general public / consumers
  - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**
  - PROC7 Industrial spraying
  - PROC11 Non industrial spraying
- **Application of the substance / the mixture** Lacquer
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolfraamweg 2  
NL-8471 XC Wolvega  
Nederland  
Tel : +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02

- **Signal word** Danger
- **Hazard statements**  
H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
- **Precautionary statements**
  - P101 If medical advice is needed, have product container or label at hand.
  - P102 Keep out of reach of children.
  - P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

**Trade name: PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 1)

- P211 Do not spray on an open flame or other ignition source.  
 P251 Do not pierce or burn, even after use.  
 P260 Do not breathe spray.  
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.  
 P501 Dispose of contents / container in accordance with regional regulations.

**Additional information:**

EUH208 Contains reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

Buildup of explosive mixtures possible without sufficient ventilation.

**2.3 Other hazards**

**Results of PBT and vPvB assessment**

• **PBT:** Not applicable.

• **vPvB:** Not applicable.

**SECTION 3: Composition/information on ingredients**

**3.2 Chemical characterisation: Mixtures**

• **Description:** Mixture of substances listed below with nonhazardous additions.

**Dangerous components:**

CAS: 115-10-6 EINECS: 204-065-8 Index number: 603-019-00-8 Reg.nr.: 01-2119472128-37	dimethyl ether Flam. Gas 1, H220 Press. Gas C, H280	25-<50%
CAS: 64-17-5 EINECS: 200-578-6 Index number: 603-002-00-5 Reg.nr.: 01-2119457610-43	ethanol Flam. Liq. 2, H225	12.5-<20%
CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25	propan-2-ol Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	2.5-<5%
CAS: 1336-21-6 EINECS: 215-647-6 Index number: 007-001-01-2	ammonia Skin Corr. 1B, H314 Aquatic Acute 1, H400	≤0.5%
CAS: 55406-53-6 EINECS: 259-627-5 Index number: 616-212-00-7	3-Iodo-2-propynylbutylcarbamate Acute Tox. 3, H331 STOT RE 1, H372 Eye Dam. 1, H318 Aquatic Acute 1, H400; Aquatic Chronic 1, H410 Acute Tox. 4, H302; Skin Sens. 1, H317	≤0.5%
CAS: 55965-84-9 Index number: 613-167-00-5	reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1) Acute Tox. 3, H301; Acute Tox. 3, H311; Acute Tox. 3, H331 Skin Corr. 1B, H314 Aquatic Acute 1, H400; Aquatic Chronic 1, H410 Skin Sens. 1, H317	≤0.5%

• **Additional information:** For the wording of the listed hazard phrases refer to section 16.

**SECTION 4: First aid measures**

**4.1 Description of first aid measures**

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

**Trade name: PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 2)

- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

**SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.  
Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**  
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

**SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Mount respiratory protective device.  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

**SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
No special measures required.
- **Information about fire - and explosion protection:**  
Keep ignition sources away - Do not smoke.  
Keep respiratory protective device available.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

**SECTION 8: Exposure controls/personal protection**

- **Additional information about design of technical facilities:** No further data; see item 7.

(Contd. on page 4)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

**Trade name: PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 3)

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

**115-10-6 dimethyl ether**

WEL Short-term value: 958 mg/m<sup>3</sup>, 500 ppm  
Long-term value: 766 mg/m<sup>3</sup>, 400 ppm

**64-17-5 ethanol**

WEL Long-term value: 1920 mg/m<sup>3</sup>, 1000 ppm

**67-63-0 propan-2-ol**

WEL Short-term value: 1250 mg/m<sup>3</sup>, 500 ppm  
Long-term value: 999 mg/m<sup>3</sup>, 400 ppm

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**

Solvent resistant gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

Butyl rubber, BR

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Not required.

**SECTION 9: Physical and chemical properties**

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

**Form:** Aerosol

**Colour:** According to product specification

· **Odour:** Characteristic

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

· **Change in condition**

**Melting point/freezing point:** Undetermined.

**Initial boiling point and boiling range:** Not applicable, as aerosol.

· **Flash point:** Not applicable, as aerosol.

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

Trade name: **PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 4)

· <b>Flammability (solid, gas):</b>	Not applicable.
· <b>Ignition temperature:</b>	240 °C (464 °F)
· <b>Decomposition temperature:</b>	Not determined.
· <b>Auto-ignition temperature:</b>	Product is not selfigniting.
· <b>Explosive properties:</b>	Not determined.
· <b>Explosion limits:</b>	
<b>Lower:</b>	3.3 Vol %
<b>Upper:</b>	26.2 Vol %
· <b>Vapour pressure at 20 °C (68 °F):</b>	4 hPa (3 mm Hg)
· <b>Density:</b>	Not determined.
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not applicable.
· <b>Solubility in / Miscibility with water:</b>	Not miscible or difficult to mix.
· <b>Partition coefficient: n-octanol/water:</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	57.1 %
<b>Water:</b>	6.3 %
<b>VOC (EC)</b>	---
	609.8 g/l
· <b>VOC-EU%</b>	57.13 %
· <b>Solids content:</b>	31.9 %
· <b>9.2 Other information</b>	No further relevant information available.

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

#### 64-17-5 ethanol

Oral	LD50	10,470 mg/kg (rat)
Dermal	LD50	>2,000 mg/kg (rat)
Inhalative	LC50 / 4h	120 mg/l (rat)

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

Trade name: **PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 5)

**67-63-0 propan-2-ol**

Oral	LD50	5,840 mg/kg (rat)
Dermal	LD50	13,900 mg/kg (rabbit)
Inhalative	LC50	>25 mg/l (rat) LC 50: 6h

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

**SECTION 12: Ecological information**· **12.1 Toxicity**· **Aquatic toxicity:****115-10-6 dimethyl ether**

EC50 / 96 h	155 mg/l (algae)
LC50 / 48 h	>4,000 mg/l (daphnia magna)
LC50 / 96 h	>4,000 mg/l (fish)

**64-17-5 ethanol**

LC50/96h	13,000 mg/l (oncorhynchus mykiss / Regenbogenforelle)
EC50 / 48 h	12,900 mg/l (algae)
LC50 / 48 h	12,340 mg/l (daphnia magna)

**67-63-0 propan-2-ol**

LC50/96h	9,640 mg/l (pimephales promelas; 96h)
LC50 / 24 h	9,714 mg/l (daphnia magna)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.

· **Additional ecological information:**· **General notes:**

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

· **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

**SECTION 13: Disposal considerations**· **13.1 Waste treatment methods**· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

**Trade name: PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 6)

· **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
15 01 04	metallic packaging
15 01 10*	packaging containing residues of or contaminated by hazardous substances

· **Uncleaned packaging:**

· **Recommendation:**

Dispose of packaging according to regulations on the disposal of packagings.  
Non contaminated packagings may be recycled.

**SECTION 14: Transport information**

· **14.1 UN-Number**

· **ADR, IMDG, IATA** UN1950

· **14.2 UN proper shipping name**

· **ADR** 1950 AEROSOLS  
· **IMDG** AEROSOLS  
· **IATA** AEROSOLS, flammable

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 2 5F Gases.  
· **Label** 2.1

· **IMDG, IATA**



· **Class** 2.1  
· **Label** 2.1

· **14.4 Packing group**

· **ADR, IMDG, IATA** not regulated

· **14.5 Environmental hazards:**

Not applicable.

· **14.6 Special precautions for user**

· **Danger code (Kemler):** -  
· **EMS Number:** F-D,S-U  
· **Segregation groups** Ammonium compounds  
· **Stowage Code** SW1 Protected from sources of heat.  
SW22 For AEROSOLS with a maximum capacity of 1 litre:  
Category A. For AEROSOLS with a capacity above 1 litre:  
Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.

(Contd. on page 8)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

Trade name: **PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 7)

· <b>Segregation Code</b>	SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>ADR</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity
· <b>Transport category</b>	2
· <b>Tunnel restriction code</b>	D
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity
· <b>UN "Model Regulation":</b>	UN 1950 AEROSOLS, 2.1

\*

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category P3a** FLAMMABLE AEROSOLS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3, 40
- **National regulations:**
- **Other regulations, limitations and prohibitive regulations**
- **Substances of very high concern (SVHC) according to REACH, Article 57**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H319 Causes serious eye irritation.

(Contd. on page 9)

GB



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 28.05.2018

Version number 1

Revision: 17.07.2017

**Trade name: PLASTI-KOTE® CHALK VARIOUS COLOURS 400 ML**

(Contd. of page 8)

*H331 Toxic if inhaled.**H336 May cause drowsiness or dizziness.**H372 Causes damage to organs through prolonged or repeated exposure.**H400 Very toxic to aquatic life.**H410 Very toxic to aquatic life with long lasting effects.*

· **Abbreviations and acronyms:**

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*IMDG: International Maritime Code for Dangerous Goods*

*IATA: International Air Transport Association*

*GHS: Globally Harmonised System of Classification and Labelling of Chemicals*

*EINECS: European Inventory of Existing Commercial Chemical Substances*

*ELINCS: European List of Notified Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*VOC: Volatile Organic Compounds (USA, EU)*

*LC50: Lethal concentration, 50 percent*

*LD50: Lethal dose, 50 percent*

*PBT: Persistent, Bioaccumulative and Toxic*

*SVHC: Substances of Very High Concern*

*vPvB: very Persistent and very Bioaccumulative*

*Flam. Gas 1: Flammable gases – Category 1*

*Aerosol 1: Aerosols – Category 1*

*Press. Gas C: Gases under pressure – Compressed gas*

*Flam. Liq. 2: Flammable liquids – Category 2*

*Acute Tox. 4: Acute toxicity – Category 4*

*Acute Tox. 3: Acute toxicity – Category 3*

*Skin Corr. 1B: Skin corrosion/irritation – Category 1B*

*Eye Dam. 1: Serious eye damage/eye irritation – Category 1*

*Eye Irrit. 2: Serious eye damage/eye irritation – Category 2*

*Skin Sens. 1: Skin sensitisation – Category 1*

*STOT SE 3: Specific target organ toxicity (single exposure) – Category 3*

*STOT RE 1: Specific target organ toxicity (repeated exposure) – Category 1*

*Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1*

*Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1*

· **\* Data compared to the previous version altered.**