

## T8 Luxline Plus

F58W/T8/827  
0001535



### Product features



## PRODUCT OVERVIEW

Product name	F58W/T8/827
Technology	Fluorescent
Watt (Rated) (W)	58.00
Lamp shape	Tube, double-ended
Type	T8 Luxline Plus
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940798
E-number SE	8356610
E-number Norway	3815421
Luminous flux (lm)	5200
Colour temperature (K)	2700
Light colour	Homelight
Colour Code	827
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	58.00
Product Voltage (V)	110
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	20000
Product EAN number	5410288015354

## DATA TABLE

### General data

Product name	F58W/T8/827
Technology	Fluorescent
Watt (Rated) (W)	58.00
Lamp shape	Tube, double-ended
Type	T8 Luxline Plus

## T8 Luxline Plus

F58W/T8/827

0001535

Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940798
E-number SE	8356610
E-number Norway	3815421

### Optical data

Luminous flux (lm)	5200
Luminous flux (Rated) (lm)	5200
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	2700
Light colour	Homelight
Colour Code	827
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 2000 h 50Hz	0.96
Rated lumen maint. factor (%) at 4000 h 50Hz	0.94
Rated lumen maint. factor (%) at 6000 h 50Hz	0.92
Rated lumen maint. factor (%) at 8000 h 50Hz	0.91
Rated lumen maint. factor (%) at 12000 h 50Hz	0.90
Rated lumen maint. factor (%) at 16000 h 50Hz	0.89
Rated lumen maint. factor (%) at 20000 h 50Hz	0.87

### Electrical data

Wattage (W)	58.00
Watt (Rated) - High frequency (W)	50.00
Current (A)	0.670
Mains voltage (V)	220-240V
Product Voltage (V)	110
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	670
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	68

## T8 Luxline Plus

F58W/T8/827

0001535

### Lifetime data

Average life (Nominal) (h)	20000
Average life (Rated) (h)	20000
Rated survival factor (%) at 2000 h 50Hz	0.99
Rated survival factor (%) at 4000 h 50Hz	0.98
Rated survival factor (%) at 6000 h 50Hz	0.96
Rated survival factor (%) at 8000 h 50Hz	0.94
Rated survival factor (%) at 12000 h 50Hz	0.92
Rated survival factor (%) at 16000 h 50Hz	0.80
Rated survival factor (%) at 20000 h 50Hz	0.50

### Physical data

Nominal Product Length (mm)	1500.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	1500.0
Length base to pin Min-Max (mm) - B	1504.7-1507.1
Max. Lamp Length (mm) - C/L	1514.2
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.2

### Packaging


Single packaging type	Carton
Product EAN number	5410288015354
Packaging single length / height (cm)	151.1
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288015351
Units per outer package	25
Packaging outer length / height (cm)	154.5
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

### Safety data

Lamp mercury content (mg)	2.80
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes

## PHOTOMETRY

T8 Luxline Plus  
F58W/T8/827  
0001535



## TECHNICAL DRAWINGS



0001535



**58**  
kWh/1000h




2019/2015

# SYLVANIA

T8 Luxline Plus  
F58W/T8/827  
0001535



0001535



**58**  
kWh/1000h



2019/2015