




- Features :
- Universal AC input/Full range
- Low leakage current<0.5mA
- Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- 100% full load burn-in test
- Fixed switching frequency at 65KHz
- 2 years warranty




**SPECIFICATION**

| MODEL                 |  | PT-65A  |            |          | PT-65B       |            |          | PT-65C   |            |          | PT-65D                          |          |            |
|-----------------------|--|---|------------|----------|--------------|------------|----------|----------|------------|----------|---------------------------------|----------|------------|
| OUTPUT                | OUTPUT NUMBER  | CH1   | CH2        | CH3      | CH1          | CH2        | CH3      | CH1      | CH2        | CH3      | CH1                             | CH2      | CH3        |
|                       | DC VOLTAGE   | 5V  | 12V        | -5V      | 5V           | 12V        | -12V     | 5V       | 15V        | -15V     | 5V                              | 12V      | 24V        |
|                       | RATED CURRENT  | 5.5A  | 2.5A       | 0.5A     | 5.5A         | 2.5A       | 0.5A     | 5.5A     | 2A         | 0.5A     | 4A                              | 2A       | 1A         |
|                       | CURRENT RANGE  | 0.4 ~ 7A  | 0.2 ~ 3.2A | 0 ~ 0.7A | 0.4 ~ 7A     | 0.2 ~ 3.2A | 0 ~ 0.7A | 0.4 ~ 7A | 0.2 ~ 2.6A | 0 ~ 0.7A | 0.5 ~ 5A                        | 0.2 ~ 4A | 0.2 ~ 1.3A |
|                       | RATED POWER  | 60W   |            |          | 63.5W        |            |          | 65W      |            |          | 68W                             |          |            |
|                       | OUTPUT POWER (max.)  | Rated output power for convection; 72W with 18CFM min. Forced air                       |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | RIPPLE & NOISE (max.) Note.2   | 50mVp-p   | 120mVp-p   | 50mVp-p  | 50mVp-p      | 120mVp-p   | 100mVp-p | 50mVp-p  | 120mVp-p   | 100mVp-p | 50mVp-p                         | 100mVp-p | 200mVp-p   |
|                       | VOLTAGE ADJ. RANGE   | CH1:4.75 ~ 5.5V   |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | VOLTAGE TOLERANCE Note.3   | ±4.0%   | ±7.0%      | ±5.0%    | ±4.0%        | ±7.0%      | ±5.0%    | ±4.0%    | ±7.0%      | ±5.0%    | ±4.0%                           | ±6.0%    | ±6.0%      |
|                       | LINE REGULATION  | ±1.0%   | ±2.0%      | ±1.0%    | ±1.0%        | ±2.0%      | ±1.0%    | ±1.0%    | ±2.0%      | ±1.0%    | ±1.0%                           | ±2.0%    | ±3.0%      |
|                       | LOAD REGULATION  | ±3.0%   | ±4.0%      | ±1.0%    | ±3.0%        | ±4.0%      | ±1.0%    | ±3.0%    | ±4.0%      | ±1.0%    | ±2.0%                           | ±5.0%    | ±5.0%      |
|                       | SETUP, RISE TIME   | 800ms, 20ms at full load  |            |          |              |            |          |          |            |          |                                 |          |            |
| HOLD UP TIME (Typ.)   | 60ms at full load  |   |            |          |              |            |          |          |            |          |                                 |          |            |
| INPUT                 | VOLTAGE RANGE  | 90 ~ 264VAC   |            |          | 127 ~ 370VDC |            |          |          |            |          |                                 |          |            |
|                       | FREQUENCY RANGE  | 47 ~ 440Hz  |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | EFFICIENCY(Typ.)   | 76%   |            |          | 77%          |            |          | 77%      |            |          | 79%                             |          |            |
|                       | AC CURRENT (Typ.)  | 1.5A/115VAC   |            |          | 0.9A/230VAC  |            |          |          |            |          |                                 |          |            |
|                       | INRUSH CURRENT (Typ.)  | COLD START 20A/115VAC   |            |          | 40A/230VAC   |            |          |          |            |          |                                 |          |            |
|                       | LEAKAGE CURRENT  | <0.75mA   |            |          |              |            |          |          |            |          |                                 |          |            |
| PROTECTION            | OVERLOAD   | 73 ~ 95W rated output power   |            |          |              |            |          |          |            |          | 74.8 ~ 98.6W rated output power |          |            |
|                       |  | Protection type : Hiccup mode, recovers automatically after fault condition is removed. |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | OVER VOLTAGE   | 5.75 ~ 6.75VDC on CH1   |            |          |              |            |          |          |            |          |                                 |          |            |
|                       |  | Protection type : Hiccup mode, recovers automatically after fault condition is removed. |            |          |              |            |          |          |            |          |                                 |          |            |
| ENVIRONMENT           | WORKING TEMP.  | -10 ~ +60°C (Refer to "Derating Curve")   |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | WORKING HUMIDITY   | 20 ~ 90% RH non-condensing  |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | STORAGE TEMP., HUMIDITY  | -20 ~ +85°C, 10 ~ 95% RH  |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | TEMP. COEFFICIENT  | ±0.04%/°C (0 ~ 50°C) on +5V output  |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | VIBRATION  | 10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes                 |            |          |              |            |          |          |            |          |                                 |          |            |
| SAFETY & EMC (Note 4) | SAFETY STANDARDS   | UL60950-1, TUV EN60950-1 approved   |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | WITHSTAND VOLTAGE  | I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC 1min.                                       |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | ISOLATION RESISTANCE   | I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH                              |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | EMC EMISSION   | Compliance to EN55022 (CISPR22) Class B, EN61000-3-2,-3                                 |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | EMC IMMUNITY   | Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, light industry level, criteria A       |            |          |              |            |          |          |            |          |                                 |          |            |
| OTHERS                | MTBF   | 277.2K hrs min. MIL-HDBK-217F (25°C)  |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | DIMENSION  | 127*76*42mm (L*W*H)   |            |          |              |            |          |          |            |          |                                 |          |            |
|                       | PACKING  | 0.25Kg; 54pcs/15.9Kg/1.35CUFT   |            |          |              |            |          |          |            |          |                                 |          |            |
| NOTE                  | <ol style="list-style-type: none"> <li>1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.</li> <li>2. Ripple &amp; noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf &amp; 47uf parallel capacitor.</li> <li>3. Tolerance : includes set up tolerance, line regulation and load regulation.</li> <li>4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on <a href="http://www.meanwell.com">http://www.meanwell.com</a>)</li> <li>5. Mounting holes M1 and M2 should be grounded for EMI purposes.</li> <li>6. Heat Sink HS1,HS2 can not be shorted.</li> </ol> |   |            |          |              |            |          |          |            |          |                                 |          |            |

**Mechanical Specification**

Unit:mm



AC Input Connector (CN1) : Molex 5277-02 or equivalent

| Pin No. | Assignment | Mating Housing           | Terminal                 |
|---------|------------|--------------------------|--------------------------|
| 1       | AC/N       | Molex 5195 or equivalent | Molex 5194 or equivalent |
| 2       | AC/L       |                          |                          |


⚠ HS1,HS2 can not be shorted

DC Output Connector (CN2) : Molex 5273-06 or equivalent


| Pin No. | Assignment | Mating Housing           | Terminal                 |
|---------|------------|--------------------------|--------------------------|
| 1       | V2         | Molex 5195 or equivalent | Molex 5194 or equivalent |
| 2,3     | +5V        |                          |                          |
| 4,5     | COM        |                          |                          |
| 6       | V3         |                          |                          |

※PIN2:+5V PIN3,4,5:COM only for PT-65D

**Block Diagram**



**Derating Curve**



**Output Derating VS Input Voltage**

