

To English


Able reducer
Specification sheet

Reducer model

EVL-090B-10-K6-19EB19**(Shaft with key)**

1.Reducer specification

| | |
|--|-------------------------|
| Ratio | 10 |
| Backlash | 6 arc-min |
| Allowable nominal torque | 45 Nm |
| Allowable maximum torque | 65 Nm |
| Allowable average input speed | 3000 rpm |
| Allowable maximum input speed | 6000 rpm |
| Allowable radial load (Applied to the output shaft center.) | 1200 N |
| Allowable axial load (Applied to the output side bearing.) | 1600 N |
| Approx. weight | 4.9 kg |
| Moment of inertia | 2.02 kg·cm ² |
| Lubrication type | Grease |
| Color of the paint | Silver |



*The actual appearance might be different.