





**Part no.: 50130290**  
**TK 100 x100-Set**  
**Reflector**

Figure can vary

## Contents

- Set consists of
- Technical data
- Dimensioned drawings

## Set consists of

	Quantity	Part no.	Designation	Article	Description
	2	50009419	BT 910M	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Metal
	1	50003192	TK 100x100	Reflector	Design: Rectangular Reflective surface: 96 mm x 96 mm Triple reflector size: 4 mm Material: Plastic Base material: Plastic Chemical designation of the material: PMMA8N Fastening: Adhesive

## Technical data

<b>Mechanical data</b>	
Design	Rectangular
Mounting dimension, width	99.4 mm
Reflection surface width	96 mm
Mounting dimension, height	99.4 mm
Reflection surface height	96 mm
Mounting dimension, thickness	8.7 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	61 g
Type of fastening	Adhesive Supplied mounting bracket

<b>Environmental data</b>	
Ambient temperature, operation	-40 ... 65 °C

<b>Certifications</b>	
Degree of protection	IP 67

<b>Classification</b>	
Customs tariff number	39269097
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

