


Part number

CX 01 YM



Brief description:

male insert, 1 pole, crimp connections, 200A 1000V, 8kV, 3, 200A male crimp contacts, 2 modules, modular units series MIXO




Product description		Approvals / Standards	
Model	male insert	Reference standard	EN 61984:2009-06
Version	Crimp connection	Quality mark	 DNV GL, BV, EAC
Product type	200A male crimp contacts	Conformity	CQC, CE
Family	MIXO series, customizable inserts	General ordering information	
Size	2 modules	EAN13 code	8015747168069
N. of poles	1 pole	Tariff number	85369095
Technical data		Packaging Information	
Current	200 A (A.C. and D.C.)	Packaging length	112,00 mm
Voltage	1000 V	Packaging height	95,00 mm
Rated impulse withstand voltage	8 kV	Packaging width	117,00 mm
Pollution degree	3	Packaging weight	0,20 kg
Operating temperature range (min, max)	-40°C ... +125°C	Packaging volume	1,24 dm ³
IP degree of protection	IP20 without enclosure, IP65/IP66/IP68/IP69 with enclosure	Packaging description	Carton box
Further technical details		Packaging quantity	5 Pcs
Characteristics according to EN 61984	200A 1000V 8kV 3; 200A 920/1600V 8kV 2	Packaging EAN code	8015747168380
Insulation resistance	≥ 10 GΩ	Sub-packaging weight	0,04 kg
Rated voltage according to UL/CSA	600V	Sub-packaging description	Plastic bag
UL 94 flammability rating	V-0	Sub-packaging quantity	1 Pcs
Weight	31,00 g	Sub-packaging EAN barcode	8015747168397

Part number

CX 01 YM



Catalogue drawings



Notes

CX 01 Y inserts:

- characteristics according to EN 61984:
(200A 1000V 8kV 3)
- 2 frame slots

- rated voltage according to UL/CSA: 600V
- insulation resistance: > 10 GOhm
- ambient temperature limit: -40 °C ... +125 °C
- are made of self-extinguishing thermoplastic resin UL 94 V0
- mechanical life: > 500 cycles

- contact resistance: < 0,2 mOhm

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support
