

Cabinet workbench, series V 1500, wheeled

Universal coating 1500 mm, 3 drawers with full extension, 1 door, 2 guide rollers and 2 fixed wheels for transporting



Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 3 drawers with 100% full extension on the left, front height 180 mm, 1 door, height 540 mm on the right



Art. no.	50201 503
Brand	ANKE
Manufacturer Part Number	999.001.1227
Working height	850 mm
Worktop width	1500 mm
Number of drawers	3 PCS
Worktop height	50 mm
Number of doors	1 PCS
Worktop depth	700 mm
Pullout type	Full extension
On castors	Yes
Colour of front	Gentian blue RAL 5010
Cabinet colour	Light grey RAL 7035
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Surface	Powder-coated
Load-carrying capacity	600 kg
Levelling	No
Lock type	DOM® locking system
Material of worktop	Universal covering
Drawer front height	3 x 180 mm
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Central locking	Yes
Gross Weight	120.429 kg
Product Group	502

EAN

4014641079963