



FXx*1)P1GY*2)

e.g. F25P1G1

*1) xx No. of contacts 09, 15, 25 or 37
 *2) y for performance classes 1, 2 or 3
 (contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]	*E [mm]
09	30.8	16.9	25	
15	39.1	25.2	33.3	
25	53	38.9	47.04	ø1
37	69.3	55.3	63.5	

RoHS compliant

*PCB hole patterns, øE on supplement AM0023

3	xx	Signal contact	P1 / Brass	G1/G2/G3
2	1	Shell	Steel	fin plated
1	1	Insulator	PBT (-55°C - +125°C)	white
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	

REV.	DATE	CH.-NO.	DWG.NO.	REPLACEMENT FOR:	PAGES
1			FxxP1Gy	FxxP1Gy/a	1

D-Sub Miniature Connector

Measurement without tolerance occ. to ISO 2768-m
 NAME / DATE
 schref
 02-09-2002
 Flößmann
 02-09-2002



SCALE 2:1
 ORIGINAL DIN A3 DRAWING AS A FILE