

## Multi-functional table trolley

3 load areas, load capacity 125 kg

**LUXOR**  
PROFESSIONAL WORKSPACE PRODUCT SOLUTIONS

### Application:

This popular all-purpose trolley safely stores and transports your valuable electronic devices from room to room.

### Execution:

- The steel construction and the robot-welded trays guarantee a long service life even in harsh environments
- Textured mats and an all-round stop edge keep the contents of the trays securely in place
- This height-adjustable multi-functional trolley is easy to manoeuvre thanks to the four fully swivelling castors
- Can be quickly stabilised if necessary with the two installed locking brakes
- The height is adjustable in increments of 50 mm
- Height adjustment range: 610-1070 mm

### Advantage:

- Height-adjustable
- Agile
- Durable
- Low-noise, ball-bearing swivel castors

### Delivery:

Supplied disassembled - easy assembly



<b>Art. no.</b>	<b>50311 028</b>
<b>Brand</b>	LUXOR
<b>Manufacturer Part Number</b>	SEAVJ42
<b>Load-carrying capacity</b>	125 kg
<b>Height</b>	1070 mm
<b>Length</b>	610 mm
<b>Number of loading surfaces</b>	3
<b>Load-carrying capacity of loading surfaces</b>	45 kg
<b>Length x width x height</b>	610 x 460 x 1070 mm
<b>Width</b>	460 mm
<b>Surface</b>	Powder-coated
<b>Wheel diameter</b>	100 mm
<b>Material of wheel</b>	PP - Polypropylene
<b>Number of steering rollers</b>	4
<b>Adjustable in height</b>	Yes
<b>Min. height adjustment</b>	610 mm
<b>Max. height adjustment</b>	1070 mm
<b>Min./max. height adjustment</b>	610-1070mm
<b>With wheel lock</b>	Yes
<b>Gross Weight</b>	21.000 kg
<b>Product Group</b>	5AQ

### EAN

4260563729602