



DRY+LOCK

SIZE	ART. NO.	EAN NO.
36	3778-36	6408487437434
37	3778-37	6408487437441
38	3778-38	6408487437458
39	3778-39	6408487437465
40	3778-40	6408487437472
41	3778-41	6408487437489
42	3778-42	6408487437496
43	3778-43	6408487437502
44	3778-44	6408487437519
45	3778-45	6408487437526
46	3778-46	6408487437533
47	3778-47	6408487437540

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

JALAS® 3778 DRYLOCK

EN ISO 20345:2011, S3 HRO WR SRB

PROPERTIES

Highest level of protection, excellent grip, perfect fit, extra comfortable, extremely warm, excellent shock absorption

SPECIFICATION

TYPE OF SHOE Safety footwear, boots

NAIL PROTECTION MATERIAL Steel

FITTING Regular

SIZE RANGE 36-47

COLLECTION Drylock

PLATFORM Grip

UPPER MATERIAL Full-grain leather

UPPER MATERIAL THICKNESS 1.6-1.8

PRONOSE MATERIAL PU

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester fur, Drylock membrane

SOLE MATERIAL PU midsole, rubber outsole

INSOLE FX2 Winter

INSOLE MATERIAL Textile, aluminium foil, soft EVA, polyester-based conductive thread, merino wool, double shock absorption zones in Poron® XRD®

FASTENING Zipper

CLOUR Black, grey

1(3)

JALAS® 3778 DRYLOCK

FEATURES

Waterproof Drylock-membrane, ProNose toe reinforcement, heat-resistant outsole, oil-resistant outsole, anti-static properties, padded boot shaft, pull loops, snow lock, zipper, waterproof, reflector, double shock absorption zones, conforms with IEC 61340-5-1 (ESD)

PRIMARY PROTECTION

Prevents risk of: toe injuries, nail penetration, antistatic, contact with cold, wet feet

PRIMARY ENVIRONMENTS OF USE

Outdoors, environments with risk for outsole penetration, cold environments, wet environments, harsh environments



CE



Aluminium toecap



Zipper



Nail protection in steel



Winter model



Heat-resistant outsole



Anti-static properties



Waterproof



ESD



Oil-resistant outsole



ProNose toe reinforcement



Ergo-Shock Absorption System

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-09-30

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

JALAS® 3778 DRYLOCK

COMPLIANCE
EN ISO 20345:2011

COMPLIANCE DESCRIPTION

SB: Footwear with toe protection tested with 200 J impact and 15kN compression force (includes oil resistant outsole)

S1: Footwear made from leather and other materials excluding all-rubber or all-polymeric footwear + closed seat region + SB + A + E

S2: S1 + WRU

S3: S2 + P

WR: Water-resistant footwear

WRU: Water-resistant upper

P: Penetration-resistant outsole

HRO: Heat-resistant outsole compound tested at 300°C

A: Electrical resistance (between 0.1-1000 Mega Ohms)

E: Energy absorption in the heel area (tested at 20 Joules)

SRB: Slip-resistance on steel floor with glycerol

IEC 61340-5-1: Electrostatic Discharge (ESD) resistance below 35 megaohm

BGR 191: Orthopedic footwear adjustment according to German BGR 191. Footwear is tested with adjusted orthopedic insoles in accordance with EN ISO 20345 standard



CE



Aluminium toecap



Zipper



Nail protection in steel



Winter model



Heat-resistant outsole



Anti-static properties



Waterproof



ESD



Oil-resistant outsole



ProNose toe reinforcement



Ergothon Shock Absorption System

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-09-30

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com