

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 21/04/2015

Revision date:

Version: 1.0

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name : RADIANT SENSE MB3000  
Product code : 800333  
Vaporizer : Aerosol  
SKU # : R0260040

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use  
Use of the substance/mixture : Air care products  
Odour agents

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Supplier

Newell Europe sàrl  
10 chemin de Blandonnet  
1214 Vernier - Switzerland  
T +44(0)870 5686824  
[SDS.RCP@newellco.com](mailto:SDS.RCP@newellco.com)

##### Other

Newell Poland Services Sp. z o.o.  
Plac Andersa 7  
61-894 Poznań - Poland  
T +44(0)870 5686824  
[www.rubbermaid.eu/contact](http://www.rubbermaid.eu/contact)

#### 1.4. Emergency telephone number

Emergency number : +44(0)870 5686824

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol 1 H222;H229

Full text of H-phrases: see section 16

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

Signal word (CLP) :

Danger

Hazard statements (CLP) :

H222 - Extremely flammable aerosol  
H229 - Pressurised container: May burst if heated

Precautionary statements (CLP) :

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P251 - Do not pierce or burn, even after use  
P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

EUH phrases :

EUH208 - Contains TETRAMETHYL ACETYLOCTAHYDRONAPHTHALENES, 2,4-DIMETHYL-3-CYCLOHEXENE CARBOXYALDEHYDE. May produce an allergic reaction

#### 2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### SECTION 3: Composition/information on ingredients

#### 3.1. Substance

Not applicable

#### 3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Alcohol	(CAS No) 64-17-5 (EC no) 200-578-6 (EC index no) 603-002-00-5 (REACH-no) 01-2119457610-43	10 - 20	Flam. Liq. 2, H225 Eye Irrit. 2, H319
ISOPROPYL ALCOHOL	(CAS No) 67-63-0 (EC no) 200-661-7 (EC index no) 603-117-00-0 (REACH-no) 01-2119457558-25	1 - 10	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
TETRAMETHYL ACETYLOCTAHYDRONAPHTHALENES	(CAS No) 54464-57-2 (EC no) 259-174-3 915-730-3 (REACH-no) 01-2119489989-04	0,1 - 1	Aquatic Chronic 2, H411 Skin Irrit. 2, H315 Skin Sens. 1, H317
2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE	(CAS No) 68039-49-6 (EC no) 268-264-1	0,1 - 1	Eye Irrit. 2, H319 Skin Irrit. 2, H315 Skin Sens. 1, H317 Aquatic Chronic 3, H412

#### Specific concentration limits:

Name	Product identifier	Specific concentration limits
Alcohol	(CAS No) 64-17-5 (EC no) 200-578-6 (EC index no) 603-002-00-5 (REACH-no) 01-2119457610-43	(C >= 50) Eye Irrit. 2, H319

Full text of H-phrases: see section 16

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

- First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
- First-aid measures after inhalation : Cough. Allow breathing of fresh air. Allow the victim to rest.
- First-aid measures after skin contact : Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
- First-aid measures after eye contact : Direct contact with the eyes is likely to be irritating. Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persist.
- First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

#### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : Shortness of breath.

#### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

- Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
- Unsuitable extinguishing media : Do not use a heavy water stream.

#### 5.2. Special hazards arising from the substance or mixture

- Fire hazard : Extremely flammable aerosol.
- Explosion hazard : Heat may build pressure, rupturing closed containers, spreading fire and increasing risk of burns and injuries.

#### 5.3. Advice for firefighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire-fighting water from entering environment. DO NOT fight fire when fire reaches explosives. Evacuate area.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : No open flames. No smoking. Isolate from fire, if possible, without unnecessary risk. Remove ignition sources. Use special care to avoid static electric charges.

##### 6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

##### 6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area.

#### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

#### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Additional hazards when processed : Hazardous waste due to potential risk of explosion. Pressurized container: Do not pierce or burn, even after use.

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Do not spray on an open flame or other ignition source.

#### 7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Comply with applicable regulations.

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Direct sunlight, Heat sources, Ignition sources. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Incompatible products : Strong bases. Strong acids.

Incompatible materials : Sources of ignition. Direct sunlight. Heat sources.

#### 7.3. Specific end use(s)

No additional information available

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

Alcohol (64-17-5)		
United Kingdom	Local name	Ethanol
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	1920 mg/m <sup>3</sup>
United Kingdom	WEL TWA (ppm)	1000 ppm
ISOPROPYL ALCOHOL (67-63-0)		
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	999 mg/m <sup>3</sup>
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m <sup>3</sup> )	1250 mg/m <sup>3</sup>
United Kingdom	WEL STEL (ppm)	500 ppm

#### 8.2. Exposure controls

Personal protective equipment : Avoid all unnecessary exposure.

Hand protection : Wear protective gloves

Eye protection : None under normal use

Respiratory protection : None under normal use

Other information : Do not eat, drink or smoke during use.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state : Liquid

Appearance : Clear Transparent Liquid.

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Colour	: colourless to slightly yellow.
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: Not applicable
Flash point	: No data available
Auto-ignition temperature	: None
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol
Vapour pressure	: 3,5 - 4,5 bar
Relative vapour density at 20 °C	: No data available
Relative density	: 0,619 - 0,645
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: 1,8 - 19 vol %

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No additional information available

### 10.2. Chemical stability

Extremely flammable aerosol. Contains gas under pressure; may explode if heated. Extreme risk of explosion by shock, friction, fire or other sources of ignition.

### 10.3. Possibility of hazardous reactions

Not established.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Heat. Sparks. Open flame. Overheating.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity : Not classified

<b>2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE (68039-49-6)</b>	
LD50 oral rat	4000 mg/kg
LD50 oral	2830 mg/kg
LD50 dermal	> 2000 mg/kg bodyweight
<b>Alcohol (64-17-5)</b>	
LD50 oral rat	7060 mg/kg
LD50 oral	10470 mg/kg bodyweight
LD50 dermal rabbit	> 16000 mg/kg
LD50 dermal	15800 mg/kg bodyweight
LC50 inhalation rat (mg/l)	> 20 mg/l/4h
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 99,999 mg/l/4h
<b>ISOPROPYL ALCOHOL (67-63-0)</b>	
LD50 oral rat	2000 mg/kg

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

ISOPROPYL ALCOHOL (67-63-0)	
LD50 oral	4396 mg/kg bodyweight
LD50 dermal rat	2000 mg/kg
LD50 dermal	12800 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	46,6 mg/l/4h

Skin corrosion/irritation	: Not classified Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Not classified Based on available data, the classification criteria are not met
Respiratory or skin sensitisation	: Not classified Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified Based on available data, the classification criteria are not met
Specific target organ toxicity (single exposure)	: Not classified Based on available data, the classification criteria are not met
Specific target organ toxicity (repeated exposure)	: Not classified Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified Based on available data, the classification criteria are not met

RADIANT SENSE MB3000	
Vaporizer	Aerosol

Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.
---	---

## SECTION 12: Ecological information

### 12.1. Toxicity

Alcohol (64-17-5)	
LC50 fish 1	13000 mg/l
EC50 Daphnia 1	9300 mg/l
EC50 other aquatic organisms 1	275 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	5012 mg/l IC50 algae (72 h) mg/l

ISOPROPYL ALCOHOL (67-63-0)	
LC50 fish 1	100 mg/l
EC50 Daphnia 1	100 mg/l
EC50 other aquatic organisms 1	> 1000 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	13299 mg/l IC50 algae (72 h) mg/l

### 12.2. Persistence and degradability

RADIANT SENSE MB3000	
Persistence and degradability	Not established.

Alcohol (64-17-5)	
Persistence and degradability	Not established.

### 12.3. Bioaccumulative potential

RADIANT SENSE MB3000	
Bioaccumulative potential	Not established.

Alcohol (64-17-5)	
Bioaccumulative potential	Not established.

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

RADIANT SENSE MB3000	
This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII	

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### RADIANT SENSE MB3000

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

#### 12.6. Other adverse effects

Additional information : Avoid release to the environment

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods






Waste disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Container under pressure. Do not drill or burn even after use.

Additional information : Flammable vapours may accumulate in the container.

Ecology - waste materials : Avoid release to the environment.

### SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
1950	1950	1950	1950	1950
<b>14.2. UN proper shipping name</b>				
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
<b>Transport document description</b>				
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1			
<b>14.3. Transport hazard class(es)</b>				
2.1	2.1	2.1	2.1	2.1
				
<b>14.4. Packing group</b>				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
<b>14.5. Environmental hazards</b>				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

#### 14.6. Special precautions for user

##### - Overland transport

Classification code (ADR) : 5F  
Special provisions (ADR) : 190, 327, 344, 625  
Limited quantities (ADR) : 11  
Excepted quantities (ADR) : E0  
Packing instructions (ADR) : P207, LP02  
Special packing provisions (ADR) : PP87, RR6, L2  
Mixed packing provisions (ADR) : MP9  
Transport category (ADR) : 2  
Special provisions for carriage - Packages (ADR) : V14  
Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12  
Special provisions for carriage - Operation (ADR) : S2  
Tunnel restriction code (ADR) : D

##### - Transport by sea

Special provisions (IMDG) : 63, 190, 277, 327, 344, 959  
Limited quantities (IMDG) : SP277  
Excepted quantities (IMDG) : E0  
Packing instructions (IMDG) : P207, LP02

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Special packing provisions (IMDG)	: PP87, L2
EmS-No. (Fire)	: F-D
EmS-No. (Spillage)	: S-U
Stowage category (IMDG)	: None
Stowage and segregation (IMDG)	: Protected from sources of heat For AEROSOLS with a maximum capacity of 1 litre: Category A. Segregation as for class 9 but 'Separated from' class 1 except division 1.4. For AEROSOLS with a capacity above 1 litre: Category B. Segregation as for the appropriate sub-division of class 2. For WASTE AEROSOLS: Category C. Clear of living quarters. Segregation as for the appropriate sub-division of class 2.

### - Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167
ERG code (IATA)	: 10L

### - Inland waterway transport

Classification code (ADN)	: 5F
Special provisions (ADN)	: 19, 327, 344, 625
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E0
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01, VE04
Number of blue cones/lights (ADN)	: 1
Carriage prohibited (ADN)	: No
Not subject to ADN	: No

### - Rail transport

Classification code (RID)	: 5F
Special provisions (RID)	: 190, 327, 344, 625
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP02
Special packing provisions (RID)	: PP87, RR6, L2
Mixed packing provisions (RID)	: MP9
Transport category (RID)	: 2
Special provisions for carriage – Packages (RID)	: W14
Special provisions for carriage - Loading, unloading and handling (RID)	: CW9, CW12
Colis express (express parcels) (RID)	: CE2
Hazard identification number (RID)	: 23
Carriage prohibited (RID)	: No

### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

IBC code	: Not applicable.
----------	-------------------

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no substances with Annex XVII restrictions  
Contains no substance on the REACH candidate list  
Contains no REACH Annex XIV substances

#### 15.1.2. National regulations

No additional information available

# RADIANT SENSE MB3000

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-phrases:

Aerosol 1	Aerosol, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Sensitisation — Skin, category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H222	Extremely flammable aerosol
H225	Highly flammable liquid and vapour
H229	Pressurised container: May burst if heated
H315	Causes skin irritation
H317	May cause an allergic skin reaction
H319	Causes serious eye irritation
H336	May cause drowsiness or dizziness
H411	Toxic to aquatic life with long lasting effects
H412	Harmful to aquatic life with long lasting effects
EUH208	Contains . May produce an allergic reaction

SDS EU ANNEX II NEWELL

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*