



Figure similar

OUTPUT CHOKE; PHASES:3; UN1(V):460; ITHMAX 1(A) / F1(HZ):6,1 /120; F TAKT(KHZ):3; I LN (A):5,5; LN(MH):3,47; UK(%):6; TA/ISOKL:40 /B; IP00; TYPE OF TERMINALS:SCREW/TAB CONNECTION; EN 61558-2-20 >UL/CSA-RECOGNIZED<

General technical data:

Product designation		output reactor
product brand name		SIDAC
Phase number		3
Type of voltage		AC
Operating voltage Rated value		
• maximum	V	460
Operating frequency Rated value		
• minimum	Hz	0
• maximum	Hz	120
Current		
• with AC		
— Rated value	A	5.5
— maximum	A	6.1
Inductivity Rated value	H	0.0035
Active power loss of the coil	W	49.6
Active power loss of the iron core	W	29.4
Clock frequency		
• Rated value	Hz	3 000

Mechanical data:

Type of electrical connection for main current circuit		screw-type terminals / tab terminals
Width	m	0.17
Height	m	0.15
Depth	m	0.1

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

Declaration of Conformity



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EP37013US00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP37013US00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EP37013US00&lang=en

last modified:

15.01.2015