## **Connection Line** M8 × 1; 3-pin



## S49-2M


Part Number




## **Technical Data**

Mechanical Data	
Connection 1	Socket, straight
Connection mode 1	M8 × 1, 3-pin
Connection 2	stripped
Torque	M8: 0,3 Nm
Cable Length	2 m
Cable Diameter	5 mm
Wire cross-section	0,34 mm <sup>2</sup>
Degree of Protection	IP67
Temperature Range	-2580 °C
Cable Jacket Material	PVC
Material Wire Insulation	PVC
Material Sleeve Nut	CuZn, nickel-plated
Packaging unit	1 Piece
Connection Diagram No.	S04
Connection Equipment No.	8

• Straight







Leger	lu	
+	Supply Voltage +	
-	Supply Voltage 0 V	
~	Supply Voltage (AC Voltage)	
А	Switching Output (NO)	
Ā	Switching Output (NC)	
٧	Contamination/Error Output (NO)	
V	Contamination/Error Output (NC)	
E	Input (analog or digital)	
Т	Teach Input	
Z	Time Delay (activation)	
S	Shielding	
RxD	Interface Receive Path	
TxD	Interface Send Path	
RDY	Ready	
GND	Ground	
CL	Clock	
E/A	Output/Input programmable	
0	IO-Link	
PoE	Power over Ethernet	
IN	Safety Input	
OSSD	Safety Output	
Signal	Signal Output	
BI_D+/-	- Ethernet Gigabit bidirect. data line (A-D)	
ENerse	2 Encoder 0-pulse 0-0 (TTL)	

	Platinum measuring resistor	ENARS422	Encoder A/Ā (TTL)
	not connected	ENBRS422	Encoder B/B (TTL)
	Test Input	ENa	Encoder A
	Test Input inverted	ENв	Encoder B
	Trigger Input	Amin	Digital output MIN
	Ground for the Trigger Input	Амах	Digital output MAX
	Analog Output	Аок	Digital output OK
	Ground for the Analog Output	SY In	Synchronization In
	Block Discharge	SY OUT	Synchronization OUT
	Valve Output	OLT	Brightness output
	Valve Control Output +	 м	Maintenance
	Valve Control Output 0 V	rsv	reserved
	Synchronization	Wire Co	olors according to DIN IEC 7
	Ground for the Synchronization	BK	Black
	Receiver-Line	 BN	Brown
	Emitter-Line	RD	Red
	Grounding	 OG	Orange
	Switching Distance Reduction	YE	Yellow
_	Ethernet Receive Path	GN	Green
_	Ethernet Send Path	BU	Blue
	Interfaces-Bus A(+)/B(-)	VT	Violet
	Emitted Light disengageable	GY	Grey
	Magnet activation	WH	White
	Input confirmation	PK	Pink
	Contactor Monitoring	GNYE	Green/Yellow

⊦/– E

Specifications are subject to change without notice

DIN IEC 757

## System Components and Software