

Wall-mounted swivelling crane Boy (BW) – with standard chain hoist

With retractable boom



Application:

The folding boom makes it ideal for loading machines or confined spaces

Execution:

- Classification in accordance with EN 13001 HC2 S2 HD2 for lightweight industrial applications in production halls
- Round cable power supply in the boom profiles right up to the boom tip
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with bracket suspension – two-stage lifting speed



Advantage:

- Folding boom
- Fast handling of workpieces
- Swivel resistance is adjusted manually as standard

Delivery:

Includes detailed documentation, electric chain hoist with bracket suspension

Art. no.	77110 002
Brand	VETTER
Manufacturer Part Number	BW1,25-4,0+SIXX1F
Model	Boy BW
Type	Console assembly A
Load-carrying capacity	125 kg
Overhang	4000 mm
Overhang 1	2100 mm
Overhang 2	1900 mm
Construction height	940 mm
Max. lift height	5 m
Design	With electric chain hoist
Lifting device design	With electric chain hoist SIXX-BL
Swivel range	180 Degree
Colour	Daffodil yellow RAL 1007
Surface	Lacquered
Operating voltage	400 V
Cable length	3.8 m
Weight	189 kg
Max. vertical force	4 kN
Max. horizontal force	14 kN
Gross Weight	211.000 kg
Product Group	7EL