

## Conductor markers TM 1/12 HF/HB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

### General ordering data

Type	TM 1/12 HF/HB
Order No.	<a href="#">1719780000</a>
Version	Conductor markers, 12 x 5.4 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.:
GTIN (EAN)	4008190353131
Qty.	1,000 pc(s).

## Conductor markers TM 1/12 HF/HB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	12 mm	Width	5.4 mm
Height	6.4 mm	Depth	6 mm
Net weight	0.159 g		

### General data

Colour	Transparent	Material	Polyethylene LD
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	HB		

### Conductor and cable markers

Conductor O.D., max.	2.5 mm	Conductor O.D., min.	1.8 mm
Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Halogen	No		

### Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

### Approvals

Approvals	
ROHS	Conform