

product type designation



SIPLUS NET SCALANCE X SFP991-1LD

SIPLUS NET SCALANCE X SFP991-1LD based on 6GK5991-1AF00-8AA0 with conformal coating, -40...+85 °C, SCALANCE X accessory; SFP991-1LD; 1x 100 Mbps LC port, optical; single-mode optical up to max. 26 km

interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 100 Mbit/s LC ports	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	1310 nm; Single-mode
connectable optical power relative to 1 mW	
<ul style="list-style-type: none"> of the transmitter output / minimum of the transmitter output / maximum of the receiver input / maximum 	-15 dB -8 dB -8 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-28 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 26 km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport note 	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> for emitted interference for interference immunity 	EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> CE marking 	Yes
MTBF	490 a

further information / internet links

internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

5/11/2022 