DC-Filter, single pole



Approvals and Compliances

Description

- Line-filter in standard version
- 1-stage
- standard attenuation

Characteristics

- Optimized for DC supplied applications
- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Other terminal combinations
- Version with wire connection

References

Alternative: Standard version

Weblinks

pdf datasheet, html-datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product, Microsite

_				_	
10	chi	nic	21	เาว	ta

Ratings IEC	5 - 30 A @ Ta 40 °C / 43/80 VDC
Ratings UL/CSA	5 - 30 A @ Ta 40 °C / 43/80 VDC
Dielectric Strength	> 1.7 kVDC between Vss-GND > 2.7 kVDC between Vss/GND-PE Test voltage (2 sec)
Allowable Operation Temperature	-25°C to 100°C
Climatic Category	25/100/21 acc. to IEC 60068-1
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	Quick connect and screw terminals
Material: Housing	Aluminum, UL 94V-0

Line Filter	Industrial Version, IEC 60939, UL 1283, CSA C22.2 no. 8
	Technical Details
MTBF	> 200'000h acc. to MIL-HB-217 F
•	

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FMEB

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40021953
c FU °us	UL Approvals	UL	UL File Number: E72928

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
<u>IEC</u>	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
<u>IEC</u>	Designed according to	IEC 60127-6	Miniature fuses. Part 6. Fuse-holders for miniature fuse-links
(N)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
(UL)	Designed according to	UL 1283	Electromagnetic interference filters
GB Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment. $ \label{eq:continuous} % \begin{subarray}{l} \end{subarray} %$


Compliances


The product complies with following Guide Lines


The product comp	nico Witi i foliowii ig dalao Eli ico		
Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
ROHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
©	China RoHS	SCHURTER AG	The law SJ $/$ T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]

Case 85-2










- 1) Line
- 2) Load
- 3) I/O connections torque 0.6...0.8 Nm

Case 86-2










- 1) Line
- 2) Load
- 3) I/O connections torque 0.6...0.8 Nm

Case 86-6









- 1) Line
- 2) Load
- 3) I/O connections torque 0.6...0.8 Nm

Terminal options



- 1) Quick connect terminals 6.3x0.8 (only up to 24A)
- 2) Screw clamp 4mm²
- 3) Flexible wires

Diagrams




1) Line

2) Load


Attenuation Loss

Standard version


5 A



10 A




15 A




20 A


- - - - 50Ω differential mode _____ 50Ω common mode



24 A



30 A



All Variants

Order Number	Packaging unit	Housings	Weight [g]	R [M Ω]	Cy (Y2) [nF]	Cx (X2) [nF]	L [mH]	Rated Current [A]
5500.2223	10	85-2	175 g	1	100	100	2 x 0.75	5
5500.2224	10	85-2	175 g	1	100	100	2 x 0.2	10
5500.2225	10	85-2	175 g	1	100	100	2 x 0.1	15
5500.2226	10	85-2	175 g	1	100	100	2 x 0.07	20
5500.2227	10	86-2	255 g	1	100	100	2 x 0.14	24
5500.2228	10	86-6	265 g	1	100	100	2 x 0.08	30

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER