

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

Date of issue: 15/12/2015

Revision date:

Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Use of the substance/mixture : Marking

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

LA-CO Industries Europe S.A.S.
Parc Industriel de la Plaine de
l'Ain - Allée des Combes.
01150.BLYES.France.
Phone: +33 (0)4 74 46 23 23
Fax: +33 (0)4 74 46 23 29
E-mail: info@eu.laco.com
Web: http://www.markal.com



1.4. Emergency telephone number

Emergency number : 24-hour emergency: CHEMTREC- U.S. : 1-800-424-9300 International: +1-703-527-3887

EU Member State	Officieel adviesorgaan	Adres	Noodnummer
AUSTRIA	Vergiftungsinformationszentrale (Poisons Information Centre)	Allgemeines Krankenhaus Waehringer Geurtel 18-20 1090 Wien	+43 1 406 43 43
BELARUS	The Belarus Republican Poisons Centre	Kizhevatova str. 58 Minsk 220115	+375 (0)17 201 9158
BELGIUM	Centre Anti-Poisons/Antigifcentrum c/o Hôpital Central de la Base - Reine Astrid	Rue Bruyn 1 B -1120 Bruxelles/Brussel	+32 70 245 245
BULGARIA	Национален токсикологичен информационен център National Clinical Toxicology Centre, Emergency Medical Institute "Pirogov"	21 Totleben Boulevard 1606 SOFIA	+359 2 9154 409
CROATIA	Poisons Control Centre Institute of Medical Research & Occupational Health	Ksaverska Cesta 2 P.O. Box 291 HR-10000 Zagreb	+385 1 234 8342
CZECH REPUBLIC	Toxikologické informační středisko Clinic For Occupational Medicine, 1st Medical Faculty, Charles University	Na Bojišti 1 120 00 Praha 2	+42 2 2491 9293 +42 2 2491 5402
DENMARK	Gifflinjen Bispebjerg Hospital	Bispebjerg Bakke 23, 60, 1 DK-2400 København NV	+45 82 12 12 12 +45 35 31 55 55
ESTONIA	Mürgistusteabekeskus	Gonsiori 29 15027 Tallinn	+372 626 93 90
FINLAND	Myrkytystietokeskus	P.O.B 340 (Haartmaninkatu 4) HUS SF - 00029 Helsinki	+358 9 471 977
FRANCE	ORFILA		+33 1 45 42 59 59
GERMANY	Berliner Betrieb für Zentrale Gesundheitliche Aufgaben	Oranienburger Strasse 285 13437 Berlin	+49 30 19240
GERMANY	Informations und Beratungszentrum für Vergiftungsfälle	Kirrberger Straße, Gebäude 9 D-66421 Homburg/Saar	+49 6841 19240
GERMANY	Beratungstelle bei Vergiftungen, Klinische Toxikologie und Beratungsstelle bei Vergiftungen	Langenbeckstrasse 1 55131 Mainz	+49 6131 19240
GREECE	Poisons Information Centre	11527 Athens	+30 10 779 3777
HUNGARY	Országos Kémiai Biztonsági Intézet (National Institute of Chemical Safety) Egészségügyi Toxikológiai Tájékoztató Szolgálat (Health Toxicological Information Service)	1437 Budapest PO Box 839 1097 Budapest, Nagyvárad tér 2	+36 80 20 11 99
ICELAND	Eitrunarmiðstöðin	Eitrunarmiðstöðin 108 Reykjavik	+354 543 22 22
IRELAND	National Poisons Information Centre	Beaumont Hospital PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2166

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

LATVIA	Valsts Toksikoloģijas centra Saindēšanās un zāļu informācijas centrs	2 Hipocrate Street LV 1038 Riga	+371 67 04 24 73
LITHUANIA	Apsinuodijimų kontrolės ir informacijos biuras	Siltnamiu 29 2043 Vilnius	+370 5 236 20 52/+370 687 53 378
MALTA	Medicines & Poisons Info Office	Mater Dei Hospital, Msida MSD 2090 Malta	25450000
NETHERLANDS	Nationaal Vergiftigingen Informatie Centrum National Institute for Public Health and the Environment, NB this service is only available to health professionals	Huispostnummer B.00.118, PO Box 85500 3508 GA Utrecht	+31 30 274 88 88
PORTUGAL	Centro de Informação Antivenenos Instituto Nacional de Emergência Médica (INEM)	Rua Almirante Barroso, 36 1000-013 Lisboa	808 250 143 (for use only in Portugal), +351 21 330 3284
ROMANIA	Biroul pentru Regulamentul Sanitar International si Informare Toxicologica	Str. Dr. Leonte Anastasievici Nr.1-3, Sector 5 50463 Bucuresti	+40 21 318 36 06
SLOVAKIA	Národné toxikologické informačné centrum University Hospital Bratislava	Limbová 5 833 05 Bratislava	+421 2 54 77 4 166
SPAIN	Servicio de Información Toxicológica Instituto Nacional de Toxicología, Departamento de Madrid	Calle Luis Cabrera 9 E-28002 Madrid	+34 91 562 04 20
SWEDEN	Giftinformationscentralen Swedish Poisons Information Centre, Karolinska Hospital	Box 60 500 SE-171 76 Stockholm	+46 8 33 12 31 (International) 112 (National)
SWITZERLAND	Centre Suisse d'Information Toxicologique	Freiestrasse 16 Postfach CH-8028 Zurich	+41 44 251 51 51 (International) 145 (National)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

EUH-statements

: EUH210 - Safety data sheet available on request

2.3. Other hazards

PBT: not yet assessed

vPvB: not yet assessed

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Paraffin waxes and Hydrocarbon waxes	(CAS No) 8002-74-2 (EC no) 232-315-6	70 – 90	Not classified
Carbon black	(CAS No) 1333-86-4 (EC no) 215-609-9	0 - 10	Carc. 2, H351 (bound)
titanium dioxide	(CAS No) 13463-67-7 (EC no) 236-675-5	0 - 10	Not classified

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: No special measures required.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Gently wash with plenty of soap and water.
First-aid measures after eye contact	: In case of contact, immediately flush eyes with plenty of water.
First-aid measures after ingestion	: Call a POISON CENTER or doctor/physician if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : None known.

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire.

Unsuitable extinguishing media : None known.

5.2. Special hazards arising from the substance or mixture

Fire hazard : No particular fire or explosion hazard.

5.3. Advice for firefighters

Firefighting instructions : Keep upwind.

Protection during firefighting : Wear a self contained breathing apparatus. Wear fire/flame resistant/retardant clothing. EN469.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : This product is not hazardous.

6.1.1. For non-emergency personnel

No additional information available

6.1.2. For emergency responders

No additional information available

6.2. Environmental precautions

Contains no substances known to be hazardous to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Contain and collect as any solid.

6.4. Reference to other sections

Section 7: safe handling.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin, eyes and clothing.

Hygiene measures : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

Storage area : Store in dry, cool, well-ventilated area.

7.3. Specific end use(s)

Marking.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Carbon black (1333-86-4)		
Belgium	Limit value (mg/m ³)	3.5 mg/m ³
Denmark	Grænseværdie (langvarig) (mg/m ³)	3.5 mg/m ³
Denmark	Anmærkninger (DK)	K
Finland	HTP-arvo (8h) (mg/m ³)	3.5 mg/m ³
Finland	HTP-arvo (15 min)	7 mg/m ³
France	VME (mg/m ³)	3.5 mg/m ³
Ireland	OEL (8 hours ref) (mg/m ³)	3.5 mg/m ³
Ireland	OEL (15 min ref) (mg/m ³)	7 mg/m ³
Spain	VLA-ED (mg/m ³)	3.5 mg/m ³
Sweden	nivågränsvärde (NVG) (mg/m ³)	3 mg/m ³
United Kingdom	Local name	Carbon black
United Kingdom	WEL TWA (mg/m ³)	3.5 mg/m ³
United Kingdom	WEL STEL (mg/m ³)	7 mg/m ³
Norway	Grenseverdier (AN) (mg/m ³)	3.5 mg/m ³

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

titanium dioxide (13463-67-7)		
Belgium	Remark (BE)	(dioxyde de)
Denmark	Grænseværdie (kortvarig) (mg/m ³)	12 mg/m ³
France	Note (FR)	inhalable aerosol
Ireland	OEL (8 hours ref) (mg/m ³)	10 mg/m ³ total inhalable dust 4 mg/m ³ respirable dust
Slovakia	NPHV (priemerná) (mg/m ³)	5 mg/m ³
Spain	VLA-ED (mg/m ³)	10 mg/m ³
Spain	Notes	inhalable aerosol
Sweden	nivågränsvärde (NVG) (mg/m ³)	5 mg/m ³
Sweden	Anmärkning (SE)	total dust, 1
United Kingdom	WEL TWA (mg/m ³)	10 mg/m ³ inhalable aerosol 4 mg/m ³ respirable aerosol
Switzerland	Remark (CH)	(respirable aerosol)
Paraffin waxes and Hydrocarbon waxes (8002-74-2)		
Belgium	Limit value (mg/m ³)	2 mg/m ³
Belgium	Remark (BE)	(cire de) (fumées)
Denmark	Grænseværdie (langvarig) (mg/m ³)	2 mg/m ³
Finland	HTP-arvo (8h) (mg/m ³)	1 mg/m ³
France	VME (mg/m ³)	2 mg/m ³
Ireland	OEL (8 hours ref) (mg/m ³)	2 mg/m ³
Ireland	OEL (15 min ref) (mg/m ³)	6 mg/m ³
Poland	NDS (mg/m ³)	2 mg/m ³
Poland	Remark (PL)	dymy
Slovakia	NPHV (priemerná) (mg/m ³)	2 mg/m ³
Spain	VLA-ED (mg/m ³)	2 mg/m ³
United Kingdom	WEL TWA (mg/m ³)	2 mg/m ³
United Kingdom	WEL STEL (mg/m ³)	6 mg/m ³
United Kingdom	Remark (WEL)	(fume)
Norway	Grenseverdier (AN) (mg/m ³)	2 mg/m ³
Switzerland	VME (mg/m ³)	2 mg/m ³
Switzerland	Remark (CH)	(alveolengängiger Staub)

8.2. Exposure controls

Appropriate engineering controls	: None known.
Hand protection	: None under normal use.
Eye protection	: None under normal use.
Respiratory protection	: None under normal use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: A solid crayon-like marker.
Colour	: Variable.
Odour	: odourless.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butyl acetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: insoluble in water.
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

VOC content : 0 %

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reactions known.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

Carbon black (1333-86-4)	
LD50 oral rat	> 8000 mg/kg
LC50 inhalation rat (mg/l)	> 4.6 mg/m ³ 4 h

titanium dioxide (13463-67-7)	
LD50 oral rat	> 5000 mg/kg
LC50 inhalation rat (mg/l)	> 6.82 mg/l/4h

Paraffin waxes and Hydrocarbon waxes (8002-74-2)	
LD50 oral rat	> 5000 mg/kg No mortality observed
LD50 dermal rat	> 2000 mg/kg No mortality observed

Skin corrosion/irritation : Not classified

Serious eye damage/irritation : Not classified

Respiratory or skin sensitisation : Not classified

Germ cell mutagenicity : Not classified

Carcinogenicity : Not classified.

titanium dioxide (13463-67-7)	
NOAEL (chronic, oral, animal/male, 2 years)	5 mg/kg bodyweight rat

Reproductive toxicity : Not classified

Specific target organ toxicity (single exposure) : Not classified

Specific target organ toxicity (repeated exposure) : Not classified

Aspiration hazard : Not classified

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

SECTION 12: Ecological information

12.1. Toxicity

Paraffin waxes and Hydrocarbon waxes (8002-74-2)

LC50 fish 1 > 1000 mg/l

12.2. Persistence and degradability

Carbon black (1333-86-4)

Persistence and degradability Not readily biodegradable.

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

PBT: not yet assessed

vPvB: not yet assessed

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

European List of Waste (LoW) code : For disposal within the EC, the appropriate code according to the European Waste Catalogue (EWC) should be used

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

Not considered a dangerous good for transport regulations

14.2. UN proper shipping name

Proper Shipping Name (ADR) :

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable

14.5. Environmental hazards

Other information : No supplementary information available.

14.6. Special precautions for user

14.6.1. Overland transport

No additional information available

14.6.2. Transport by sea

No additional information available

14.6.3. Inland waterway transport

Carriage prohibited (ADN) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

VOC content : 0 %

Markal CHINA MARKER White, Yellow, Red, Black, Blue, Green

Safety Data Sheet

according to Regulation (EU) 2015/830

15.1.2. National regulations

Germany

Water hazard class (WGK) : 3 - severe hazard to waters

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

according to Regulation (EU) 2015/830

Abbreviations and acronyms:

	ATE: Acute Toxicity Estimate
	CAS (Chemical Abstracts Service) number
	CLP: Classification, Labelling, Packaging.
	EC50: Environmental Concentration associated with a response by 50% of the test population.
	GHS: Globally Harmonized System (of Classification and Labeling of Chemicals).
	LD50: Lethal Dose for 50% of the test population
	OSHA: Occupational Safety & Health Administration
	PBT: Persistent, Bioaccumulative, Toxic
	TWA: Time Weighted Average
	TSCA: Toxic Substances Control Act

Data sources : ESIS (European chemical Substances Information System; accessed at: <http://esis.jrc.ec.europa.eu/index.php?PGM=cla>.
European Chemicals Agency (ECHA) C&L Inventory database. Accessed at <http://echa.europa.eu/web/guest/information-on-chemicals/cl-inventory-database>.
Kristen Forsberg and S.Z. Mansdorf, "Quick Selection Guide to Chemical Protective Clothing", Fifth Edition.
National Fire Protection Association. Fire Protection Guide to Hazardous Materials; 10th edition.
REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of R-, H- and EUH-statements:

Carc. 2	Carcinogenicity, Category 2
H351	Suspected of causing cancer
EUH210	Safety data sheet available on request

LA-CO EU CLP SDS

SDS Prepared by: The Redstone Group, LLC
6077 Frantz Rd.
Suite 206
Dublin, OH USA 43016
T 614-923-7472
www.redstonegrp.com

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product