

• 802.11g WIFI

- Infrastructure mode
- softAP mode
- Ad hoc mode
- Microchip PIC 24FJ256GB206 16 bit processor
- WiFi Transceiver
 Microchip MRF24WG0MA/MB
 PCB Antenna or uFL connector
- · Connectivity Services
- Web server (customizable)
- TCP
- FTP
- UDP
- SNTP
- SMTP
- FOTA: Firmware upgrade over Internet
- 16Mbit Flash Memory for web server and FOTA
- EEPROM
- USB OTG
- RTCC
- Remappable pins at runtime
- · Digital I/Os, PWM
- 10 Analog Inputs (10 bits ADC and precise voltage reference)
- 4 UARTs, 1 SPI, 2 I2C
- Serial bootloader onboard

Applications

- Webserver based user interfaces to the embedded
- Sensors and automation
- Internet of Things
- · Audio over IP
- Building automation and remote control
- Industrial/process management

FlyportPRO Wi-Fi 802.11G


System on module

Introduction

FLYPORTPRO Wi-Fi is a miniature **web server module** featuring a fully integrated 802.11g Wi-Fi interface and several interfaces to the 'real world'.

The module integrates a powerful **16 bit processor** which runs custom applications and a **Wi-Fi certified transceiver** which handles the connectivity. 2 versions are available: one with PCB antenna and the other with uFL connector for an external antenna.

The module provides the embedded world with a powerful 'Internet engine' to a browser-based interface over Internet, in a small footprint, at low power and low cost. Real time data can be both displayed and/or updated from a standard web browser, even on smartphone or tablets, because FLYPORTPRO supports dynamic web pages.



The module form factor is identical to FlyportPRO Ethernet and FlyportPRO GPRS and compatible pinout.

FLYPORT is powered by openPicus framework based on FreeRTOS. The free IDE allows to create applications, to import web pages and to compile and download code to the module.

Features

16 Bit Processor PIC24FJ256GB206 - 256K Flash - 96K Ram - 16 Mips

Transceiver MRF24WG0MA/MB 802.11g Wi-Fi certified

Antenna PCB antenna or uFL connector for external antenna

Power Supply 3,3V

Low power Hibernation 20mA and Sleep 180uA

USB On the Go (OTG)

Integrated RTC 32,768 Khz quartz onboard

Digital I/O up to ..., remappable at Runtime

Analog In 10 channels - 10bits ADC - Voltage ref onboard 2,048V


Communication up to 4 UARTs, SPI, I2C

Flash 16 Mbit

Eeprom 64 Kbit

Connectors 2*30 ways, pitch 1.27mm female pin header

Dimensions 34 x 34 x 9 mm, 10 grams





Introduction

FLYPORTPRO Wi-Fi is powered by openPicus framework and mounts a 256K Flash 16bit processor from Microchip that runs the Wireless Stack and the application layer. This means that you have full control of the connectivity (extremely important for energy saving) and the application (for ex. the PIC microcontroller onboard can process data coming from an analog sensor and display these data on the integrated webserver, or send by email or save to a remote FTP server). FLYPORT has an extra 16Mbit Flash memory onboard to store web server pages and for Firmware upgrade over Internet.





FLYPORT Wi-Fi works in 3 ways:

Infrastructure mode softAP
Ad Hoc
Flyport connects to a Wi-Fi network (to access points or routers)
Flyport itself acts like an access point. It's limited to 1 client only
Point to point. Deprecated since not compatible with Android devices!

Available onboard:

SPI, I2C, UART and embedded Real Time clock.

I/O : analog and digital and PWM.

Remappable pinout:


Special functions such as SPI,UART,PWM and Interrupts can be assigned to any remappable pin at runtime.

Programming:

We provide the free IDEpro with each StarterKit.

C programming skills are needed. No expansive programmer is needed since the serial bootloader loaded on the module allows you to flash the firmware using just a serial cable.

On www.openpicus.com you can find examples, libraries and tools to start to develop immediately.





Electrical characteristics

VOLTAGE RATINGS

+3.3V DC Voltage input (pin 4) MIN:+3,0V MAX:+3,3V

CURRENT CONSUMPTION Power supply 3.3V, Ambient temperature 25°C

Wi-Fi not connected 35 mA Micro ON and Wi-Fi on but not connected

Wi-Fi connected 150 mA Micro ON and Wi-Fi infrastructure mode connected to an access point

Hibernate mode 20 mA Micro ON and Wi-Fi transceiver OFF Sleep mode 180 uA Micro OFF and Wi-Fi transceiver OFF

Wi-Fi 802.11g (Microchip transceiver MRF24WG0MA/MB)

Certifications FCC (USA), IC (Canada), ETSI (Europe)

For detailed info about the transceiver and related documention (FCC ID and more) please visit

http://ww1.microchip.com/downloads/en/DeviceDoc/70686B.pdf

Security WEP, WPA-PSK, WPA2-PSK Security

Frequency range 2412-2484 Mhz

Output power 16 dBm

Sensitivity RX min input level, 1Mbit, 8%PER: -95 dBm

RX min input level, 2Mbit, 8%PER: -88 dBm


Encryption AES128 RSSI Yes

Mechanical info

Dimensions 34*34*9 mm Weight 10 grams


Temperature range


Operating range MIN: -20°C MAX: +85°C





Block Diagram







J1 Connector

FLYPORT modules are based on Microchip PIC processor and offer **remappable pins function**. User can customize the hardware configuration by firmware.

Pin	Description	Special Function	5V tolerant	Remap
р1	GPIO	ADC #0	NO	YES
р2	RESET (active low)		NO	NO
р3	GPIO	ADC #1	NO	YES
р4	VDD (+3.3V input)		NO	NO
р5	GPIO	ADC #2	NO	NO
р6	GND		NO	NO
р7	GPIO	ADC #3	NO	YES
р8	GPIO (ICSP – PGD)	ADC #5	NO	YES
р9	GPIO		NO	NO
p10	GPIO (ICSP – PGC)	ADC #4	NO	YES
p11	GPIO		YES	NO
p12	GPIO	ADC #6	NO	YES
p13	GPIO		YES	YES
p14	GPIO		YES	YES
p15	GPIO	Interrupt #0	YES	YES
p16	GPIO	ADC #7	NO	NO
p17	GPIO		YES	YES
p18	GPIO	ADC #8	NO	NO
p19	GPIO	I2C #1 – SDA	YES	YES
p20	GPIO	ADC #9	NO	YES
p21	GPIO	I2C #1 – SCL	YES	YES
p22	UART #1 TX (output) – for programming		NO	YES
p23	UART #1 RX (input) – for programming		YES	YES
p24	I2C #2 – SDA signal (shared with onboard EEPROM)		NO	YES
p25	GPIO	USB D+	NO	NO
p26	I2C #2 – SCL signal (shared with onboard EEPROM)		NO	YES
p27	GPIO	USB D-	NO	NO
p28	GPIO	USBID	YES	YES
p29	USB Vusb		NO	NO
p30	GPIO	USB Vbus	YES	NO






J2 Connector

Pin	Description	Special function	5V tolerant	Remap
p31	GPIO		YES	NO
p32	GPIO		YES	NO
р33	GPIO		YES	NO
p34	GPIO		YES	NO
p35	GPIO		YES	NO
р36	GPIO		YES	NO
р37	GPIO		YES	NO
p38	GPIO		YES	NO
р39	Vref output (2,048V)		NO	NO
p40	Not connected		NO	NO
p41	Not connected		NO	NO
p42	Not connected		NO	NO
p43	Not connected		NO	NO
p44	Not connected		NO	NO
p45	Not connected		NO	NO
p46	Not connected		NO	NO
p47	Not connected		NO	NO
p48	Not connected		NO	NO
p49	Not connected		NO	NO
p50	Not connected		NO	NO
p51	Not connected		NO	NO
p52	Not connected		NO	NO
p53	Not connected		NO	NO
p54	Not connected		NO	NO
p55	Not connected		NO	NO
p56	Not connected		NO	NO
p57	Not connected		NO	NO
p58	Not connected		NO	NO
p59	GND		NO	NO
p60	VDD (+3.3V input)		NO	NO





Module overview




DON'T PLACE COMPONENTS, TRACKS OR COPPER UNDER THE NO FLY ZONE since the Wi-Fi performance may be affected!

Footprint and dimensions

On your carrier board we suggest to use 2*15 ways pitch 1.27mm Male pin header connectors such as:

TH: SAMTEC FTSH-115-04-F-D SMT: SAMTEC FTSH-115-04-F-DV

NOTE: The following view is made in transparency from TOP. On the right corner there's a triangle sign on the silkscreen to identify where is J1.





Ordering information

Buy online from our store or through our resellers and distributors.

Code OP014100 STARTERKIT PRO WIFI

1 Evaluation board and 1 FlyportPRO Wi-Fi

Code OP014001FLYPORTPRO Wi-Fi 802.11g (PCB Antenna)Code OP014001FLYPORTPRO Wi-Fi 802.11g (uFL connector)



How to start development

Contact us to receive the free IDEpro.

On www.openpicus.com you find a getting started guide, tutorials, libraries and code examples.

Each FLYPORT Module has a serial bootloader onboard.