
PRODUCT-DETAILS

316RU6

Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, straight, 3P+E



General Information

Extended Product Type	316RU6
Product ID	2CMA193178R1000
EAN	7392696931786
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, straight, 3P+E
Long Description	Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416626
E-Number (Finland)	2421238
E-Number (Norway)	2416626
EAN	7392696931786
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	75 mm
Product Net Height	87 mm

Product Net Length	88 mm
Product Net Depth / Length	88 mm
Product Net Weight	0.21 kg

Container Information

Package Level 1 Width	138 mm
Package Level 1 Depth / Length	158 mm
Package Level 1 Height	345 mm
Package Level 1 Gross Weight	2.1 kg
Package Level 1 EAN	7392696661782
Package Level 1 Units	box 10 piece
Package Level 2 Units	660 piece

Technical UL/CSA

Ampere Rating UL/CSA	16 A
Tightening Torque UL/CSA	7.1 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	13 ... 17 mm
Color	Red
Connection Type	Screw
Degree of Protection	IP44
Enclosure Material	Thermoplastic
Frequency (f)	50 Hz 60 Hz
Function	Panel mounted socket
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#316RU6
Material	Plastic

Mounting Holes	60-61x60-61
Mounting Type	Unified straight flange
Number of Poles	4
Order Multiple	10 piece
Product Main Type	ERU
Product Name	Panel mounted socket
Protection Type	Splashproof
Rated Current (I_n)	16 A
Rated Frequency (f)	50...60 Hz
Rated Voltage (U_r)	380 ... 415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Socket Outlets for Panel Mounting
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700002D0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440504
UNSPSC	39121406

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Socket Outlets for Panel Mounting

