

Note: This datasheet may be out of date

Please download the latest datasheet of BLM18DN151SH1# from the official website of Murata Manufacturing
Co. Ltd.

https://www.murata.com/en-eu/products/productdetail?partno=BLM18DN151SH1%23

## BLM18DN151SH1#

"#" indicates a package specification code.










< List of part numbers with package codes >

BLM18DN151SH1D BLM18DN151SH1J BLM18DN151SH1B



### Appearance & Shape







Chip ferrite beads for high frequency noise suppression over a wide frequency range.

#### Features

- High impedance characteristic in 1GHz or higher frequency
- 2. High impedance characteristic over a wide frequency band range of 100MHz to 6GHz
- 3. Low DC Resistance enables large Rated Current

### **Applications**

1. Noise suppression for Automotive LED Lighting.

# Applications

Automotive Usage	Powertrain/Safety
---------------------	-------------------



### Packaging Information

Packaging	Specifications	Minimum Order Quantity
D	180mm Paper Tape	4000
J	330mm Paper Tape	10000
В	Bulk(Bag)	1000

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/08/30



Co., Ltd. https://www.murata.com/en-eu/products/productdetail?partno=BLM18DN151SH1%23

 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ BLM18DN151SH1\# \ from \ the \ official \ website \ of \ Murata \ Manufacturing } }$ 

0.004g

Mass(typ.)

Number of Circuit

### BLM18DN151SH1#

"#" indicates a package specification code.

Note: This datasheet may be out of date



Shape	SMD
Size Code (in mm)	1608
Size Code (in inch)	0603
Length	1.6mm
Length Tolerance	±0.15mm
Width	0.8mm
Width Tolerance	±0.15mm
Thickness	0.8mm
Thickness Tolerance	±0.15mm
Impedance (at 100MHz)	150Ω
Impedance (at 100MHz) Tolerance	±25%
Impedance (at 1GHz)	400Ω
Impedance (at 1GHz) Tolerance	±30%
Rated Current (at 85°C)	1.4A
Rated Current (at 125°C)	900mA
DC Resistance(max.)	0.12Ω
Operating Temperature Range	-55℃ to 125℃

2 of 3

#### Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/


Last updated :2019/08/30

<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

### BLM18DN151SH1#

"#" indicates a package specification code.






In operating temperature exceeding +85°C, derating of current is necessary for this series.


Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics





**Equivalent Circuit** 

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/