multicomp PRO

Features

- · Enclosed Switches are with High Breaking Capacity and High Durability
- Two mount methods include side and diagonal side.
- Terminals face the front when the cover is removed for easy connection
- Approved by EN(TUV), UL, CSA, CCC.

Characteristics

	IP65		
	IEC 60947-5-1	250V AC / 10A	
Rating		480V AC / 15A	
	UL508	0.5A / 125V DC, 0.25A / 250V DC	
	UL300	1/8HP/120V AC, 1/4HP/240V AC, 1/2HP / 480V AC	
	Mechanical	10,000,000 operations min.	
Durability	Electrical	5,000,000 operations min. for 15A 250V AC resistive load	
	0.01mm/s~0.5m/s Plunger Type 0.02~0.5m/s Lerverf Type		
	Mechanical	120 operations /min.	
Operating Frequency	Electrical	20 operations /min.	
	50/60Hz		
	100MΩ min. (at 500V DC)		
	15mΩ max (initial value)		
	50°C max.		
Dielectric Strength	Between terminals of same polarity	1,000V AC 50/60Hz for 1min	
	Between current-carrying metal parts and ground	2,000V AC 50/60Hz for 1min	
	Between each terminal and non-current-carrying metal part	2,000V AC 50/60Hz for 1min	
D	Degree of protection against electric shock		
Vibration Resistance	Malfunction	10~55Hz 1.5mm double amplitude	
	Destruction	1,000m/s ² min.	
Shock Resistance	Malfunction	100m/s² min. 50m/s² min.	
	-10°C ~ +80°C with no icing		
	Ambient operating humidity range	35% ~ 85% RH	

Notes:

- 1. Above values of these characteristics are initial values.
- 2. Above values of these characteristics may are depending on different models.
- 3. Above durability is for an ambient temperature of 5 to 35° and ambient humidity of 40% to 70%.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Operating Characteristics

Part Number	Operating Force (Max.)	Release Force (Min.)	Pre Travel (Max.)	Over Travel (Min.)	Movement Differential (Max.)	Operating Position
MC002416	2.45 ~ 3.43N	1.12N	0.4mm	5.5mm	0.05mm	38.2 ± 0.8mm
MC002417	7.85N	2.35N	2mm	5mm	0.1mm	45.8 ± 0.8mm
MC002418	2.45 ~ 3.43N	1.12N	0.5mm	3.6mm	0.05mm	49.7 ± 1mm
MC002419	2.45 ~ 3.43N	1.12N	0.5mm	3.6mm	0.05mm	49.7 ± 1mm
MC002420	6.28N	2.26N	5mm	6mm	0.4mm	-

Standard Plunger







Weight: 158g

Sealed Plunger








MC002418

-25.5040.39-



6

Weight: 181.6g

Weight: 166.6g

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Standard Crossroller Plunger




Weight: 164.8g

Roller Arm Lever



MC002420



Weight: 249.2g

Dimensions : Millimetres

Part Number Table

Description		
General Purpose Enclosed Switch (IP65), Standard Plunger, Screw Terminal	MC002416	
General Purpose Enclosed Switch (IP65), Sealed Plunger, Screw Terminal	MC002417	
General Purpose Enclosed Switch (IP65), Standard Roller Plunger, Screw Terminal	MC002418	
General Purpose Enclosed Switch (IP65), Standard Crossroller Plunger, Screw Terminal	MC002419	
General Purpose Enclosed Switch (IP65), Roller Arm Lever, Screw Terminal	MC002420	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

