

Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts of boreholes and aligning workpieces.

Execution:


- Rotating dial
- Anti-magnetic components
- Automatic switching of callipers direction
- Measuring mechanism on ruby bearings
- Housing made from one piece, brushed chromium-plated
- Gauge slide with hard chrome-plated ball

Advantage:

- 3 dovetail mounting surfaces

Delivery:

Measuring probe with 2 mm ball diameter, clamping shaft diameter 8 mm, key disc, in plastic case



Art. no.	33345 110
Brand	TESA
Manufacturer Part Number	S18001695
Length measuring range	0.2 mm
Scale value	0.001 mm
Measurement force	0.15 N
Length of measuring sensor from centre of ball	12.5 mm
Ball diameter	2 mm
Pivot range of measuring sensor	240 Degree
Diameter	38 mm
Connection thread	M1.4
DIN	2270
Calibration Group	L
Gross Weight	0.098 kg
Product Group	362

EAN

7630041121537