

3-point internal micrometer

IMICRO with extension 150 mm



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning
- 150 mm extension

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

In wooden case



Art. no.	31695 300
Brand	TESA
Manufacturer Part Number	00813104
Min./max. length measuring range	275-300 mm
Measuring depth	81 mm
Error limit	8 µm
Vernier scale	0.01 mm
Measuring spindle increments	0.5 mm
Calibration Group	I, AC
DIN	863
Calibration Group Description	Internal micrometers (3 point)
Gross Weight	3.300 kg
Product Group	362

EAN

7630041108316