

## Autogen welding and cutting equipment set, with pressure reducers and hose

**ewo**  
Since 1929

With handle and welding inserts from 0–9 mm and lever cutting insert

### Application:

For welding and cutting using acetylene/oxygen flame up to 3100°C.

### Version:

- Gripping piece with hose nozzles
- Cutting nozzle with lever and block nozzles for 3-100 mm material thickness
- With key and gas igniter
- In sheet steel box
- With 5 0-9-mm welding torch nozzles, 2 oxygen and acetylene pressure reducers and flame arresters for oxygen and acetylene and 10 m twin hose, ready-made.

<b>Art. no.</b>	<b>54031 030</b>
<b>Suitable for min./max. material thickness</b>	0-9 mm
<b>Suitable for max. material thickness</b>	9 mm
<b>Number of pieces in assortment/set</b>	16 PCS

### EAN-Code

4030875111668

