



Elektrotechnik Karl-Heinz Mauz GmbH

GM25-385-M28N-34-14.5D10 (Artikel-Nr. 860528)

EKULIT

SPECIFICATIONS:

Item	Unit	Specification
Rated voltage	VDC	12.0
Gear Ratio		1/34
Rotation		CW&CCW
Motor Position		All position in horizontal
Temperature	°C	0~30
Humidity	%	30~95
• Performance of Motor		
No-load Speed	rpm	4.300±10%
No-load Current	mA	95 (max.)
Stall Current	mA	1.500 (max.)
Stall Torque	g.cm	230
• Performance of Gear motor		
Output Speed	rpm	125±10%
No-load Current	mA	110 (max.)
Stall Current	mA	1.500 (max.)
Stall Torque	kg.cm	6.5
Rated Torque	g.cm	2.000
Rated Current	mA	480 (max.)
Noise	dB	52
• The Dimension		
The Outside Shaft Length	mm	14.5
Shaft End Play	mm	0.05-0.50
Screw Size		M3.0
Dia of Shaft	mm	Ø4.0*D10mm

Adresse: Felix-Wankel-Str. 35 • 73760 Ostfildern/Nellingen

Tel: +49-711/3414023

Fax: +49-711/3414024

E-mail: info@ekulit.de Web site: www.EKULIT.de


Elektrotechnik Karl-Heinz Mauz GmbH

GM25-385-M28N-34-14.5D10 (Artikel-Nr. 860528)


EKULIT

DIMENSIONS :

(Unit: mm)



Curve drawings:



Adresse: **Felix-Wankel-Str. 35 • 73760 Ostfildern/Nellingen**

Tel: **+49-711/3414023**

Fax: **+49-711/3414024**

E-mail: **info@ekulit.de** Web site: **www.EKULIT.de**