

# **Specification**

Part No. : **MA412.A.BI.003** 

Product Name : MA412 Storm 2in1 Screwmount Antenna

LTE MIMO 2in1

Features : 2\* LTE MIMO 698 to 960MHz/1710 to 2170MHz/

2490 to 2690MHz Antenna

Screw-Mount [Permanent Mount]

Worldwide 4G Bands including 3G and 2G

Aerodynamic, Super Low-profile Vandal Resistant

Housing

IP67 Enclosure

Dims: 216.24\*93.25\*30.95mm

3M CFD-200 with SMA connectors as standard

Custom Cables and Connectors Available

Product conforms to the EMC directive 2014/30/EU.

**RoHS Compliant** 





# 1. Introduction

The Storm MA412 LTE MIMO antenna is a low profile, heavy-duty, fully IP67 waterproof external M2M antenna for use in worldwide telematics applications which require best in class LTE performance.

At only 31mm high, the Storm is the world's lowest profile global telematics antenna solution. It delivers powerful worldwide 4G LTE MIMO antenna technology while also covering the 3G and 2G bands.

Typical applications

- -HD Video over LTE
- -First Responder and Emergency Services
- -Intelligent Transport Systems
- -Internet of Things (IoT market)
- -High Definition Video Broadcast Systems
- -Wireless LTE MIMO M2M Devices
- -Digital Signage

LTE 4G applications demand high speed data uplink and downlink. High efficiency and high gain MIMO antennas are necessary to achieve the required signal to noise ratio and throughput required to solve these challenges. Taoglas also takes care to have high isolation between the two MIMO antennas to prevent self-interference. The MA412 does not require a ground plane. Low loss cables are used to keep efficiency high over long cable lengths. In contrast, smaller MIMO antennas with poorer quality thinner cables will have much reduced efficiency and isolation, which would lead to a large drop in system throughput or drops, and may indeed not make a system connection at all.



We have a version with Fakra connectors also as standard MA412.A.BI.001. Cable length and connector types are customizable. Conformity is declared under the following standard:

Conformity is declared under the following standard: EN55022 Class B

This is to declare that the product listed above conform to the EMC directive 2014/30/EU.

Product conforms to the EMC directive 2014/30/EU. Contact your regional Taoglas sales office for support.



# 2. Specification

4G/3G/2G MIMO1 Antenna									
Frequency (MHz)		LTE700	GSM850	GSM900	DCS	PCS	UMTS1	LTE2600	LTE3500
		698~803	824~894	880~960	1710~1880	1850~1990	1920~2170	2490~2690	3300~3600
Efficiency (%)									
On the 50*50cm	30cm	62.06	41.76	49.16	44.93	59.56	59.39	55.42	37.39
	1M	59.27	39.88	46.95	40.98	54.46	54.71	50.55	33.33
	2M	55.31	36.93	42.81	36.86	48.53	48.56	43.53	27.99
ground plane	3M	51.62	34.20	39.76	32.65	42.73	42.47	36.84	23.59
plane	5M	44.25	28.85	33.36	25.50	32.98	32.90	28.22	16.96
	30cm	65.08	48.08	55.44	49.41	57.62	59.92	54.98	38.19
To Con-	1M	62.15	45.91	52.95	45.06	52.69	55.18	50.14	34.83
In free	2M	58.00	42.54	48.29	40.62	46.96	48.99	43.17	29.65
space	3M	54.13	39.46	44.80	35.92	41.31	42.84	36.53	24.66
	5M	46.39	33.24	37.60	28.10	31.89	33.19	27.99	19.14
				Ave	rage Gain(dBi)				
<b>.</b>	30cm	-2.22	-3.98	-3.20	-3.55	-2.27	-2.27	-2.57	-4.36
On the	1M	-2.42	-4.18	-3.40	-3.95	-2.66	-2.63	-2.97	-4.86
50*50cm	2M	-2.72	-4.51	-3.80	-4.40	-3.16	-3.14	-3.62	-5.61
ground plane	3M	-3.02	-4.84	-4.13	-4.94	-3.72	-3.73	-4.35	-6.36
platte	5M	-3.70	-5.58	-4.88	-6.00	-4.84	-4.84	-5.50	-7.79
	30cm	-2.02	-3.19	-2.60	-3.11	-2.42	-2.23	-2.62	-4.25
T 6	1M	-2.22	-3.39	-2.80	-3.51	-2.81	-2.59	-3.02	-4.65
In free	2M	-2.52	-3.72	-3.20	-3.97	-3.31	-3.10	-3.67	-5.35
space	3M	-2.82	-4.05	-3.52	-4.50	-3.86	-3.69	-4.39	-6.15
	5M	-3.50	-4.79	-4.28	-5.57	-4.98	-4.80	-5.55	-7.25
				Pe	ak Gain(dBi)				
0.5 11	30cm	5.37	3.66	4.35	6.24	7.04	7.11	7.91	6.46
On the 50*50cm ground plane	1M	5.17	3.46	4.15	5.84	6.64	6.81	7.51	5.96
	2M	4.87	3.06	3.75	5.34	6.14	6.31	6.91	5.16
	3M	4.57	2.76	3.45	4.84	5.64	5.71	6.21	4.46
	5M	3.87	2.06	2.65	3.74	4.44	4.61	5.11	4.82
In free space	30cm	3.54	4.07	4.13	4.67	6.57	6.69	8.11	6.27
	1M	3.34	3.87	3.93	4.27	6.17	6.35	7.71	5.87
	2M	3.04	3.47	3.53	3.77	5.67	5.79	7.11	5.17
	3M	2.74	3.17	3.23	3.27	5.07	5.19	6.41	4.37
	5M	2.04	2.37	2.43	2.17	3.97	4.09	5.31	3.27



4G/3G/2G MIMO2 Antenna									
Frequency (MHz)		LTE700	GSM850	GSM900	DCS	PCS	UMTS1	LTE2600	LTE3500
		698~803	824~894	880~960	1710~1880	1850~1990	1920~2170	2490~2690	3300~3600
Efficiency (%)									
On the 50*50cm	30cm	64.02	46.23	45.95	66.28	61.93	55.94	67.23	32.20
	1M	61.13	44.15	43.91	60.45	56.58	51.48	61.32	28.70
	2M	57.05	40.91	40.05	54.37	50.43	45.69	52.80	24.24
ground plane	3M	53.25	37.91	37.20	48.10	44.46	39.97	44.69	20.32
platte	5M	45.57	31.95	31.19	37.61	34.31	30.95	34.23	14.73
	30cm	55.35	40.93	43.23	62.98	59.12	53.24	67.13	31.79
	1M	52.86	39.09	41.29	57.44	54.01	49.00	61.23	28.99
In free	2M	49.33	36.19	37.65	51.67	48.14	43.49	52.73	24.68
space	3M	46.04	33.55	34.96	45.71	42.45	38.04	44.63	20.53
	5M	39.41	28.29	29.34	35.75	32.75	29.46	34.18	15.93
				Aver	rage Gain(dBi)				
	30cm	-2.17	-3.38	-3.48	-1.84	-2.17	-2.57	-1.73	-5.25
On the 50*50cm ground plane	1M	-2.37	-3.58	-3.68	-2.24	-2.56	-2.93	-2.13	-5.75
	2M	-2.67	-3.91	-4.08	-2.69	-3.06	-3.44	-2.78	-6.50
	3M	-2.97	-4.23	-4.41	-3.23	-3.62	-4.03	-3.50	-7.25
	5M	-3.64	-4.98	-5.17	-4.29	-4.74	-5.14	-4.66	-8.68
In free space	30cm	-2.87	-3.93	-3.71	-2.04	-2.39	-2.80	-1.73	-5.28
	1M	-3.07	-4.13	-3.91	-2.44	-2.78	-3.16	-2.13	-5.68
	2M	-3.37	-4.46	-4.31	-2.90	-3.28	-3.67	-2.78	-6.38
	3M	-3.67	-4.79	-4.63	-3.43	-3.84	-4.26	-3.51	-7.18
	5M	-4.35	-5.53	-5.39	-4.50	-4.96	-5.37	-4.67	-8.28
				Pe	ak Gain(dBi)				
On 44 -	30cm	6.51	4.09	3.82	7.93	8.06	7.89	8.16	5.48
On the 50*50cm ground plane	1M	6.31	3.89	3.62	7.53	7.66	7.49	7.76	4.98
	2M	6.01	3.59	3.22	7.03	7.16	6.99	7.16	4.28
	3M	5.71	3.19	2.92	6.53	6.66	6.49	6.46	3.48
	5M	5.01	2.49	2.22	5.43	5.46	5.29	5.36	2.18
In free space	30cm	5.21	2.85	3.16	7.48	7.48	7.29	8.13	5.37
	1M	5.01	2.65	2.96	7.08	7.08	6.89	7.73	4.97
	2M	4.71	2.25	2.56	6.58	6.58	6.39	7.13	4.27
эрасс	3M	4.41	1.95	2.26	6.08	6.08	5.88	6.43	3.47
	5M	3.71	1.15	1.46	4.98	4.98	4.69	5.33	2.37



ELECTRICAL							
Impedance	$50\Omega$						
Polarization	Linear						
VSWR	< 3.5						
Cable	3 meter CFD200 Standard, Fully Customizable						
Connector	SMA(M) Standard Connector, Fully Customizable						
MECHANICAL							
Antenna Dimensions	216.24*93.25*30.95mm						
Casing	ABS+PC						
Base and thread	Nickel Plated Aluminum						
Weight	620g						
Ingress Protection Rating	IP67						
Flame Retardant	UL-94 HB						
Maximum Assembly Torque	39.2 N-m						
ENVIRONMENTAL							
Operation Temperature	-40°C to 85°C						
Storage Temperature	-40°C to 90°C						
Humidity	Non-condensing 65°C 95% RH						



		LTE BANDS							
Band Number	nd Number   LTE / LTE-Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA								
	Uplink	Downlink	MIMO 1	MIMO 2					
1	UL: 1920 to 1980	DL: 2110 to 2170	✓	✓					
2	UL: 1850 to 1910	DL: 1930 to 1990	✓	✓					
3	UL: 1710 to 1785	DL: 1805 to 1880	✓	✓					
4	UL: 1710 to 1755	DL: 2110 to 2155	✓	✓					
5	UL: 824 to 849	DL: 869 to 894	✓	✓					
7	UL: 2500 to 2570	DL:2620 to 2690	✓	✓					
8	UL: 880 to 915	DL: 925 to 960	✓	✓					
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	✓	✓					
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	×	×					
12	UL: 699 to 716	DL: 729 to 746	✓	✓					
13	UL: 777 to 787	DL: 746 to 756	✓	✓					
14	UL: 788 to 798	DL: 758 to 768	✓	✓					
17	UL: 704 to 716	DL: 734 to 746 (LTE only)	✓	✓					
18	UL: 815 to 830	DL: 860 to 875 (LET only)	✓	✓					
19	UL: 830 to 845	DL: 875 to 890	✓	✓					
20	UL: 832 to 862	DL: 791 to 821	×	✓					
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	×	×					
22	UL: 3410 to 3490	DL: 3510 to 3590	×	×					
23	UL:2000 to 2020	DL: 2180 to 2200 (LTE only)	✓	✓					
24	UL:1625.5 to 1660.5	DL: 1525 to 1559 (LTE only)	✓	✓					
25	UL: 1850 to 1915	DL: 1930 to 1995	✓	✓					
26	UL: 814 to 849	DL: 859 to 894	×	✓					
27	UL: 807 to 824	DL: 852 to 869 (LTE only)	×	✓					
28	UL: 703 to 748	DL: 758 to 803 (LTE only)	✓	✓					
29	UL: -	DL: 717 to 728 (LTE only)	✓	✓					
30	UL: 2305 to 2315	DL: 2350 to 2360 (LTE only)	✓	✓					
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5 (LTE only)	×	×					
32	UL: -	DL: 1452 - 1496	×	×					
35	1850	to 1910	✓	✓					
38	2570	to 2620	✓	✓					
39	1880	to 1920	✓	✓					
40	2300	to 2400	✓	✓					
41	2496	to 2690	✓	✓					
42	3400	to 3600	×	×					
43	3600	to 3800	×	×					

<sup>\*</sup>Covered bands represent an efficiency greater than 20%




# 3. Antenna Characteristics

# 3.1. LTE MIMO Antenna

### 3.1.1. Test Setup



In free space





on the 50\*50cm ground plane



#### 3.1.2. LTE Antenna Return Loss and Isolation

### Setup on the 50\*50cm ground plane with 3 meter cable length









### 3.1.3. LTE Antenna Efficiency

### Setup on the 50\*50cm ground plane with 3 meter cable length









#### 3.1.4. LTE Antenna Peak Gain

Setup on the 50\*50cm ground plane with 3 meter cable length









### 3.1.5. LTE Antenna Average gain


Setup on the 50\*50cm ground plane with 3 meter cable length








# 3.1.6 Test Setup For Antenna Radiation Pattern (ETS Anechoic chamber)



On the 50\*50cm ground plane




# 3.1.7 2D Radiation pattern (MIMO1 with 3M cable length on the 50\*50 ground plane)







# 3.1.8 3D Radiation pattern (MIMO1 with 3M cable length on the 50\*50 ground plane)




#### 704MHz




1710MHz






960MHz




2170MHz



3500MHz




# 3.1.9 2D Radiation pattern (MIMO2 with 3M cable length on the 50\*50 ground plane






# 3.1.10 3D Radiation pattern (MIMO2 with 3M cable length on the 50\*50 ground plane

Azimuth = 15.0 Elevation = -30.0 Roll = -15.0







Total

704MHz


960MHz






1710MHz


2170MHz








# 3.1.11 Test Setup For Antenna Radiation Pattern (ETS Anechoic chamber)



In free space




# 3.1.12 2D Radiation pattern (MIMO1 with 3M cable length in free space)







# 3.1.13 3D Radiation pattern (MIMO1 with 3M cable length in free space)









960MHz




1710MHz



2170MHz






SPE-15-8-041/E/EW




### 3.1.14 2D Radiation pattern (MIMO2 with 3M cable length in free space)






### 3.1.15 2D Radiation pattern (MIMO2 with 3M cable length in free space)



704MHz




Response (dB)


Total

Azimuth = 15.0 Elevation = -30.0 Roll = -15.0


2690MHz



960MHz




2170MHz



SPE-15-8-041/E/EW




# 4. Mechanical Drawing





# 5. Installation



Recommended torque for mounting is 29.4 N.m Maximum torque for mounting is 39.2 N.m




# 6. Packaging


#### MA412.A.BI.003

### **Packaging Specifications**


1pc MA412.A.BI.003 per small box Box Dimensions - 325x125x106mm Weight - 820g



9 small boxes in one carton Carton Dimensions - 360x360x400mm Weight - 8.28Kg



Pallet Dimensions 1080x720x1350mm 15 Cartons per Pallet 5 Cartons per layer 3 Layers






# 7. Application Note (LTE MIMO Antenna)


The MA412 antenna performance with different cable lengths and different environments is shown below.

# 7.1. On the 50\*50cm ground plane

#### 7.1.1. Return Loss (MIMO\_1 on the 50\*50cm ground plane)




#### 7.1.2. Return Loss (MIMO\_2 on the 50\*50cm ground plane)






### 7.1.3. Insertion Loss (on the 50\*50cm ground plane)




### 7.1.4. Efficiency (MIMO\_1 on the 50\*50cm ground plane)






### 7.1.5. Efficiency (MIMO\_2 on the 50\*50cm ground plane)




# 7.1.6. Average Gain (MIMO\_1 on the 50\*50cm ground plane)






### 7.1.7. Average Gain (MIMO\_2 on the 50\*50cm ground plane)




### 7.1.8. Peak Gain (MIMO\_1 on the 50\*50cm ground plane)






### 7.1.9. Peak Gain (MIMO\_2 on the 50\*50cm ground plane)




### 7.2. In free space

### 7.2.1. Return Loss (MIMO\_1 in free space)






### 7.2.2. Return Loss (MIMO\_2 in free space)




### 7.2.3. Insertion Loss (in free space)






# 7.2.4. Efficiency (MIMO\_1 in free space)




### 7.2.5. Efficiency (MIMO\_2 in free space)






### 7.2.6. Average Gain (MIMO\_1 in free space)




### 7.2.7. Average Gain (MIMO\_2 in free space)






### 7.2.8. Peak Gain (MIMO\_1 in free space)



### 7.2.9. Peak Gain (MIMO\_2 in free space)





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas