



ANNEX

EU TYPE EXAMINATION CERTIFICATE Nr. 032/2021/1344

1. Applicant

Ansell Healthcare Europe NV/SA
Riverside Business Park
Block J Boulevard International 55
1070 Brussels
Belgium

2. Description

EN ISO 374-1 / Type B



J K T

EN ISO 374-5:2016



VIRUS

3. Materials and accessories

Gloves

- TouchNTuff® 92-670, 92-665



4. Technical documentation

Summary test results

EN ISO 21420:2020

Gloves

TouchNTuff® 92-670, 92-665

Method	Description	Result	Class
ISO 3071	pH - textile	PASS	
EN 14362-1	AZO dyes for colored gloves	PASS	
ISO/TS 16190	Polycyclic aromatic hydrocarbons (PAHs)	PASS	
EN 16778	Dimethylformamide (DMFa)	/	/
EN ISO 21420 length	Length	PASS	
1149-1 / 1149-2 / 1149-3 or EN 16350	Electrostatic properties	/	/
EN ISO 21420 6.2 dexterity	Dexterity	PASS	Level 5
ISO 14268 leather / ISO 11092 textile	Water vapour transmission	/	/
ISO 20344:2011 leather	Water vapour absorption	/	/

EN ISO 374-1:2016

Gloves

TouchNTuff® 92-670, 92-665

Method	Description	Result	Class
EN 374-2	Penetration	PASS	
EN 374-2	Penetration	PASS	
EN 16523-1	Permeation J	PASS	Level 6
EN 16523-1	Permeation K	PASS	Level 6
EN 16523-1	Permeation T	PASS	Level 6
EN 374-4	Degradation J	PASS	
EN 374-4	Degradation K	PASS	
EN 374-4	Degradation T	PASS	
Type of glove		PASS	Type B

EN ISO 374-5:2016

Gloves

TouchNTuff® 92-670, 92-665

Method	Description	Result	Class
EN 374-2	Penetration	PASS	
EN 374-2	Penetration	PASS	
ISO 16604 Proc. B	Protection against viruses	PASS	

Description/Picture of article

Article **The Gloves TouchNTuff® 92-670, 92-665**



The above picture is a general picture of the article. Possible variations of the above article can be present in the technical file.

Note :

Any modification in material, design, or other technical features must be brought to the attention of the Notified Body.