

ACMS-Q4526C

Request Samples



Check Inventory (>)



4.5 x 3.2 x 2.55 mm **RoHS/RoHS II Compliant** MSL Level = 1

Features

- AEC-Q200 compliant, Grade 1
- PPAP ready and supported
- Manufactured in TS/IATF 16949 production lines
- Excellent impedance characteristics

Applications

- Differential signal line common mode noise suppression.
- Multimedia devices
- Automotive applications such as ADAS, Infotainment, Sensing, TCU
- Automotive CAN bus

Electrical Specifications

Part Number	Inductance (μH) (+50%/-30%)	DCR (mΩ)	Rated Current (A) Max	Rated Voltage (Vdc) Max	Insulation Resistance (MΩ) Min
ACMS-Q4526C-110	11	500	0.36	50	10
ACMS-Q4526C-220	22	800	0.31	50	10
ACMS-Q4526C-510	51	1000	0.23	50	10
ACMS-Q4526C-101	100	2000	0.20	50	10

Rated Current is based on an Irms temperature rise of 20°C

Inductance Test Conditions: 100KHz/0.1V

ACMS-Q4526C is AEC-Q200 Automotive certified

ACMS-Q4526C Series is RoHS Compliant and Pb free

Operating Temperature: -40°C to +150°C (Including self-heating)

Storage Temperature (on PCB): -40°C to +150°C Storage (in original packaging): <40°C, <70% RH





ACMS-Q4526C

Request Samples




Check Inventory (>)



4.5 x 3.2 x 2.55 mm **RoHS/RoHS II Compliant** MSL Level = 1

Electrical Specifications







ACMS-Q4526C

Request Samples (>)





Check Inventory (>)




4.5 x 3.2 x 2.55 mm RoHS/RoHS II Compliant MSL Level = 1

Mechanical Specifications





A	В	C	D	E	
4.5 ± 0.2	3.2 ± 0.2	2.55 ± 0.2	0.7	0.8	



Recommended Layout

Dimensions: mm



5101 Hidden Creek Ln, Spicewood TX 78669 Phone: 512-371-6159 Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION Initial Release 3/31/2022

ABRACON IS ISO9001-2015 CERTIFIED



ACMS-Q4526C

Request Samples (>)




Check Inventory (>)




4.5 x 3.2 x 2.55 mm **RoHS/RoHS II Compliant** MSL Level = 1

Schematic




Materials



	Description	Specification		
a	Upper Plate	Ni-Zn Ferrite		
ь	Core	Ni-Zn Ferrite		
С	Wire	Enameled copper wire		
d	Electrode	Ag/Ni/Sn		

Part Identification





5101 Hidden Creek Ln, Spicewood TX 78669 Phone: 512-371-6159 Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION Initial Release 3/31/2022

ABRACON IS ISO9001-2015 CERTIFIED



ACMS-Q4526C

Request Samples (>)




Check Inventory (>)



4.5 x 3.2 x 2.55 mm RoHS/RoHS II Compliant MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times	
1	Preheat	$\begin{split} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{split}$	$60 \sim 120 \text{ sec.}$	
2	Reflow	T _L 220°C	60 ~ 90 sec.	
3	Peak heat	T _P 260°C MAX	10 sec. MAX	





ACMS-Q4526C

Request Samples




Check Inventory (>)




4.5 x 3.2 x 2.55 mm **RoHS/RoHS II Compliant** MSL Level = 1


Packaging

Tape & Reel: 2000pcs/reel





Series	Series A		С	D	
ACMS-Q4526C	13.0 ± 0.5	100.0 ± 2.0	13.0 ± 0.5	330	



W	P	E	F	P0	P2	Bo	Ao	Ko	D	t
12.0	8.0	1.75	5.5	8.0	4.0	4.82	3.51	3.05	1.5	0.4
± 0.30	± 0.10	5+0.10/-0	± 0.05							

Dimensions: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

