Note: This datasheet may be out of date

Please download the latest datasheet of BLM18KG471WH1# from the official website of Murata Manufacturing

Co., Ltd.

https://www.murata.com/en-us/products/productdetail?partno=BLM18KG471WH1%23

### BLM18KG471WH1#

"#" indicates a package specification code.










< List of part numbers with package codes >

BLM18KG471WH1J BLM18KG471WH1D BLM18KG471WH1B



### Appearance & Shape







The chip ferrite beads BLM series is designed to function nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted.

BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.

BLMDDK series can be used in high current circuits due to its low DC resistance. It can match power lines to a maximum of 2ADC.

BLM18A\_WH series is designed for conductive glue mounting method, not for normal soldering method. Please contact us for applicable mounting method for BLM18A\_WH series.



Automotive
Usage

Powertrain/Safety



## **Packaging Information**

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000
В	Bulk(Bag)	1000

1 of 3

#### Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

<sup>2.</sup> This datasheet has only typical specifications because there is no space for detailed specifications.

 $\underline{ Please \ download \ the \ latest \ datasheet \ of \ BLM18KG471WH1\# \ from \ the \ of ficial \ website \ of \ Murata \ Manufacturing } }$ Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=BLM18KG471WH1%23

# BLM18KG471WH1#

"#" indicates a package specification code.

Number of Circuit

Note: This datasheet may be out of date



Shape	SMD
Size Code (in mm)	1608
Size Code (in inch)	0603
Length	1.6mm
Length Tolerance	±0.15mm
Width	0.8mm
Width Tolerance	±0.15mm
Thickness	0.8mm
Thickness Tolerance	±0.15mm
Impedance (at 100MHz)	470Ω
Impedance (at 100MHz) Tolerance	±25%
Rated Current (at 85°C)	1.1A
Rated Current (at 125°C)	1.1A
Rated Current (at 150°C)	600mA
DC Resistance(max.)	0.16Ω
Operating Temperature Range	-55°C to 150°C
Mass(typ.)	0.005g

2 of 3

### Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/12/11

<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.


### Note: This datasheet may be out of date $\underline{ Please \ download \ the \ latest \ datasheet \ of \ BLM18KG471WH1\# \ from \ the \ of ficial \ website \ of \ Murata \ Manufacturing } }$

https://www.murata.com/en-us/products/productdetail?partno=BLM18KG471WH1%23

# BLM18KG471WH1#


"#" indicates a package specification code.






In operating temperature exceeding +125°C, derating of current is necessary for BLM18KG\_WH1 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics





**Equivalent Circuit** 

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/