

30°, 45°, 60° chamfer cutters

for milling inserts TCMT 1102.., TCMT 16T3..


ATORN®

Application

Universal use for chamfering and deburring.

Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



Art. No.	16107 425
Chamfer angle	60 Degree
Max. cutting edge diameter	26 mm
Min. cutting edge diameter	15.8 mm
Clearance length	35 mm
Length	90 mm
Shaft diameter	20 mm
Number of cutting edges	1 PCS
Suitable indexable insert no.	1
Suitable for indexable inserts	TC.. 1102..

EAN-Code

4050293111774