

**Z-series
ZRH 1.5N/2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

| | |
|------------|----------------------------|
| Type | ZRH 1.5N/2 |
| Order No. | 1632130000 |
| Version | Z-series, Reducing sleeve |
| GTIN (EAN) | 4008190487348 |
| Qty. | 1,000 pc(s). |

**Z-series
ZRH 1.5N/2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 4.85 mm | Width (inches) | 0.191 inch |
| Height | 49.3 mm | Height (inches) | 1.941 inch |
| Depth | 3.95 mm | Depth (inches) | 0.156 inch |
| Net weight | 0.05 g | | |

Temperatures

| | | | |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max. | 40 °C | Storage temperature, min. | 10 °C |
| Storage temperature | 10 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------|
| Material | Wemid | Colour | grey |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | Plugged | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000897 | ETIM 4.0 | EC000897 |
| ETIM 5.0 | EC000897 | ETIM 6.0 | EC002848 |
| UNSPSC | 30-21-18-11 | eClass 5.1 | 27-14-11-45 |
| eClass 6.2 | 27-14-92-14 | eClass 7.1 | 27-14-92-14 |
| eClass 8.1 | 27-14-92-14 | eClass 9.0 | 27-14-11-92 |
| eClass 9.1 | 27-14-11-92 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|-------------------------------------|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | STEP |