

3-axis machine vices, complete set 3 AX 100

Mechanical/mechanical clamping system

ATORN[®]

Application

For clamping unmachined parts, machined parts, round and irregularly shaped parts.

Version


- Movable and fixed clamping jaw
- Clamping width adjustable via extension shaft, threaded spindle and spindle nut
- Form-fit clamping without pre-stamping
- Any clamping width possible, restricted only by the size of the machine table
- Clamping depth 3 mm with support strips, ref. no. 28758 196

Advantage

- Allows extremely high cutting forces thanks to extremely rigid design

Delivery

Supplied complete, without stop set



Art. No.	28758 014
Jaws width	100 mm
Min./max. clamping width	22-440 mm
Tension force	22 kN
Groove width	14 mm

EAN-Code

4050293645682