

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 33_SMA-Q50-0-4/1-9_N



Description

Adaptor plug/jack
SMA plug (male) / SMA jack (female)

Interface standards
IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	18 GHz		
Frequency range	DC to 5 GHz	5 to 16 GHz	16 to 18 GHz
Return loss	≥ 29 dB	≥ 20 dB	≥ 18 dB

Mechanical Data

Number of matings	500
Weight	0.0044 kg

Environmental Data

Operating Temperature	-65 °C to 165 °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts (SMA)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Stainless Steel
Insulator	PFA / PTFE

Surface Plating

Hard Au min. 0.1 µm over NiP min. 2 µm
SUCOPRO Plating

Piece Parts (SMA)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Stainless Steel
Insulator	PFA / PTFE

Surface Plating

SUCOPRO Plating
SUCOPRO Plating

Related Documents

Outline drawing	DOU-00013650
-----------------	--------------

Ordering Information

Single package	33_SMA-Q50-0-4/1-9_NE
----------------	-----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!
It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions