



MASTER Actinic BL TL-D

MASTER Actinic BL TL-D 18W/10 1SL/25

The Philips MASTER Actinic BL TL-D(-K) family is an ideal choice for insect traps. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment. Optionally, for extra safety you can apply a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	18 W
Light Technical		Lamp Current (Nom)	0.36 A
Color Code	10	Voltage (Nom)	59 V
Color Designation	Actinic	Voltage (Nom)	59 V
Chromaticity Coordinate X (Nom)	220	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	200	Bulb Shape	T26 [T 26mm]


MASTER Actinic BL TL-D

Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg

Product Data	
Full product code	872790092708500
Order product name	MASTER Actinic BL TL-D 18W/10 1SL/25
Order code	928044601003


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material number (12NC)	928044601003
Full product name	MASTER Actinic BL TL-D 18W/10 1SL/25
EAN/UPC - Case	8727900927092

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER Actinic BL TL-D 18W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - MASTER Actinic BL TL-D 18W/10 1SL/25

