


Direct Operated 2 Port Solenoid Valve **New**



Air



Medium vacuum



Water



Oil



Steam

* Can be used with heated water.



Large flow rate

Flow rate

20% More flow*

(Size 1)

Compact

Height

10% Smaller*

(Size 1)

Lightweight

Weight

30% Lighter*

(Size 1, Aluminium body)

* Comparison with SMC conventional model

Body material

Air
Aluminium, Resin

**Water/Oil/
Medium vacuum/Steam**
C37 (Brass),
Stainless steel

With one-touch fittings
(Resin body)



Bracket
Standard
equipment

Conventional model **New VX**



Enclosure

IP65*

* Electrical entry "Faston" type terminal is IP40.

Power consumption

4.5 W (Size 1)

7 W (Size 2)

10.5 W (Size 3)

(DC/N.C. valve)

Manifold

Material

- Body/PPS
- Base/Aluminium
- Seal/NBR, FKM

Solenoid coil type

- Insulation type Class B/H
- Fluid temperature Class B/Max. 60°C
- Class H/Max. 183°C

Valve type

N.C. N.O.

Series VX21/22/23



CAT.EUS70-44B-UK

Direct Operated 2 Port Solenoid Valve



Air



Medium vacuum



Water



Oil



Steam

* Can be used with heated water.

Enclosure
IP65


Flame resistance
UL94V-0 conformed

Low-noise
construction

Metal noise reduced by the rubber bumper

Piping variations

Thread piping, One-touch fitting



Clearance

By providing a bumper and clearance, we reduced the collision sound of the core when ON (when the valve is open). Because of the clearance, when using highly viscous fluids such as oil, the armature does not get stuck and the responsiveness when OFF (when the valve is closed) is improved.

Power consumption

* DC/Class B, N.C. valve

4.5 W (Size 1)

7 W (Size 2)

10.5 W (Size 3)

Improved armature durability

Body material

Air Aluminium, Resin

Water/Oil/Medium vacuum/Steam C37 (Brass), Stainless steel

Full-wave rectifier type (AC specification: Insulation type Class B/H)

Improved durability

Service life is extended by the special construction. (compared with current shading coil)

Reduced buzz noise

Rectified to DC by the full-wave rectifier, resulting in a buzz noise reduction.

Reduced apparent power * Class B, N.C. valve

10 VA → **7 VA** (Size 1) 20 VA → **9.5 VA** (Size 2)

32 VA → **12 VA** (Size 3)

Improved OFF response

Specially constructed to improve the OFF response when operated with a higher viscosity fluid such as oil.

Low-noise construction

Specially constructed to reduce the metal noise during operation.




Size	Orifice diameter							Port size
	2 mmø	3 mmø	4 mmø	5 mmø	7 mmø	8 mmø	10 mmø (Note)	
Size 1	●	●	—	●	—	—	—	1/8, 1/4 One-touch fitting: ø6, ø8
Size 2	—	—	●	—	●	—	—	1/4, 3/8 One-touch fitting: ø8, ø10
Size 3	—	—	—	●	—	●	●	1/4, 3/8, 1/2 One-touch fitting: ø10, ø12

Note) N.C. only

INDEX

Direct Operated 2 Port Solenoid Valve Series VX21/22/23



Single Unit/Manifold: Specifications.....	2
Common Specifications	3
Selection Steps	4



For Air

Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	5, 6
How to Order (Single Unit)	7
Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage	8
How to Order (Solenoid Valve for Manifold, Manifold Base), Blanking Plate Assembly Part No., How to Order Manifold Assembly (Example) ...	9



For Medium Vacuum

Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	10
How to Order (Single Unit)	11
Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	12
How to Order (Solenoid Valve for Manifold, Manifold Base), Blanking Plate Assembly Part No., How to Order Manifold Assembly (Example) ...	13



For Water

Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	14
How to Order (Single Unit)	15



For Oil

Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	16
How to Order (Single Unit)	17



For Steam * Can be used with heated water.

Model/Valve Specifications, Fluid and Ambient Temperature, Valve Leakage ...	18
How to Order (Single Unit)	19

Construction

Single Unit.....	20
Manifold.....	21

Dimensions (Single Unit) Body material: Aluminium	22
Body material: Resin	23
Body material: C37 (brass), Stainless steel ..	25
(Manifold) Base material: Aluminium	28

Glossary of Terms	29
-------------------------	----

Solenoid Valve Flow-rate Characteristics	30
--	----

Flow-rate Characteristics	35
---------------------------------	----

Replacement Parts.....	36
------------------------	----

Specific Product Precautions	37
------------------------------------	----

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Direct Operated 2 Port Solenoid Valve

Series VX21/22/23

For Air, Medium Vacuum, Water, Oil and Steam

Single Unit (For Air, Medium Vacuum, Water, Oil and Steam)



Valve type

Normally Closed (N.C.)
Normally Open (N.O.)

Solenoid coil type

Insulation type: Class B, Class H

Rated voltage

100 V/200 V/110 V/230 VAC
(220 V/240 V/48 V/24 VAC)
24 V/12 VDC

Voltage in () indicates special voltage.

Material

Body — Aluminium, Resin, C37 (Brass), Stainless steel
Seal — NBR, FKM*

* Refer to individual pages for details of each fluid.

Electrical entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal
- Faston terminal

Normally Closed (N.C.)

Normally Open (N.O.)

Size		Size 1	Size 2	Size 3
Orifice diameter	2 mmø	●	—	—
	3 mmø	●	—	—
	4 mmø	—	●	—
	5 mmø	●	—	●
	7 mmø	—	●	—
	8 mmø	—	—	●
	10 mmø	—	—	●*
Port size		1/8, 1/4 ø6, ø8	1/4, 3/8 ø8, ø10	1/4, 3/8, 1/2 ø10, ø12

* N.C. only

Manifold (For Air, Medium Vacuum)



Valve type

Normally Closed (N.C.)
Normally Open (N.O.)

Manifold type

Common SUP type
Individual SUP type

Solenoid coil type

Insulation type: Class B

Rated voltage

100 V/200 V/110 V/230 VAC
(220 V/240 V/48 V/24 VAC)
24 V/12 VDC

Voltage in () indicates special voltage.

Material

Body — Resin
Base — Aluminium
Seal — NBR, FKM

Electrical entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal
- Faston terminal

Manifold

Size		Size 1	Size 2	Size 3
Orifice diameter	2 mmø	●	—	—
	3 mmø	●	—	—
	4 mmø	—	●	—
	5 mmø	●	—	●
	7 mmø	—	●	●
Port size	Common SUP type (Air)	IN	3/8	
		OUT	1/8, 1/4	
	Individual SUP type (Medium vacuum)	IN	1/8, 1/4	
		OUT	3/8	

Series VX21/22/23

Common Specifications

Standard Specifications

Valve specifications	Valve construction		Direct operated poppet
	Withstand pressure		2.0 MPa (Resin body type 1.5 MPa)
	Body material		Aluminium, Resin, C37 (Brass), Stainless steel
	Seal material ^{Note 2)}		NBR, FKM
	Enclosure		Dust-tight, Water-jet-proof type (IP65) ^{Note 1)}
	Environment		Location without corrosive or explosive gases
Coil specifications	Rated voltage	AC	24 VAC, 48 VAC, 100 VAC, 110 VAC, 200 VAC, 220 VAC, 230 VAC, 240 VAC
		DC	12 VDC, 24 VDC
	Allowable voltage fluctuation		±10% of rated voltage
	Allowable leakage voltage	AC	10% or less of rated voltage
		DC	2% or less of rated voltage
	Coil insulation type		Class B, Class H

Note 1) Electrical entry "Faston" type terminal is IP40.

Note 2) For seal material/EPDM, please contact SMC.

⚠ Be sure to read "Specific Product Precautions" before handling.

Solenoid Coil Specifications

Normally Closed (N.C.)

DC Specification

Size	Power consumption [W] ^{Note 1)}	Temperature rise [°C] ^{Note 2)}
Size 1	4.5	50
Size 2	7	55
Size 3	10.5	65

Note 1) Power consumption, Apparent power: The value at ambient temperature of 20°C and when the rated voltage is applied. (Variation: ±10%)

Note 2) The value at ambient temperature of 20°C and when the rated voltage is applied. The value depends on the ambient environment. This is for reference.

AC Specification (Built-in Full-wave Rectifier Type) Class B

Size	Apparent power [VA] ^{Note 1) 2)}	Temperature rise [°C] ^{Note 3)}
Size 1	7	60
Size 2	9.5	70
Size 3	12	70

Class H

Size	Apparent power [VA] ^{Note 1) 2)}	Temperature rise [°C] ^{Note 3)}
Size 1	9	100
Size 2	12	100
Size 3	15	100

Note 1) Power consumption, Apparent power: The value at ambient temperature of 20°C and when the rated voltage is applied. (Variation: ±10%)

Note 2) There is no difference in the frequency and the inrush and energized apparent power, since a rectifying circuit is used in the AC.

Note 3) The value at ambient temperature of 20°C and when the rated voltage is applied. The value depends on the ambient environment. This is for reference.

Normally Open (N.O.)

DC Specification

Size	Power consumption [W] ^{Note 1)}	Temperature rise [°C] ^{Note 2)}
Size 1	7.5	60
Size 2	8.5	70
Size 3	12.5	70

Note 1) Power consumption, Apparent power: The value at ambient temperature of 20°C and when the rated voltage is applied. (Variation: ±10%)

Note 2) The value at ambient temperature of 20°C and when the rated voltage is applied. The value depends on the ambient environment. This is for reference.

AC Specification (Built-in Full-wave Rectifier Type) Class B

Size	Apparent power [VA] ^{Note 1) 2)}	Temperature rise [°C] ^{Note 3)}
Size 1	9	60
Size 2	10	70
Size 3	14	70

Class H

Size	Apparent power (VA) ^{Note 1) 2)}	Temperature rise [°C] ^{Note 3)}
Size 1	9	100
Size 2	12	100
Size 3	15	100

Note 1) Power consumption, Apparent power: The value at ambient temperature of 20°C and when the rated voltage is applied. (Variation: ±10%)

Note 2) There is no difference in the frequency and the inrush and energized apparent power, since a rectifying circuit is used in the AC.

Note 3) The value at ambient temperature of 20°C and when the rated voltage is applied. The value depends on the ambient environment. This is for reference.

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction


Dimensions

Series VX21/22/23


Selection Steps

Selection Steps


Step 1 Select the fluid.



Step 2 Select "Body material", "Port size" and "Orifice diameter" from "Flow rate — Pressure" of each fluid.



Step 3 Select electrical specification.



Step 4 For other options, refer to each "How to Order".




For Air Single Unit

Specifications

Model/Valve Specifications

N.C.

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.



For Air

For Medium Vacuum

Aluminum Body Type

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv		
1	1/8, 1/4	2	VX210	0.63	0.63	0.23	1.0	220
		3		1.05	0.68	0.41	0.6	220
		5		2.20	0.39	0.62	0.2	220
2	1/4, 3/8	4	VX220	1.90	0.52	0.62	1.0	340
		7		3.99	0.44	1.08	0.15	340
3	1/4, 3/8	5	VX230	1.96	0.55	0.75	1.0	450
		8		5.67	0.33	1.58	0.3	450
		10		5.74	0.64	2.21	0.1	450
	1/2	8.42		0.39	2.21	0.1	470	

For Water

For Oil

Resin Body Type (Built-in One-touch Fittings)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv		
1	ø6	2	VX210	0.82	0.44	0.23	1.0	220
		3		1.25	0.34	0.35	0.6	220
		5		1.45	0.43	0.40	0.2	220
	ø8	2		0.82	0.44	0.23	1.0	220
		3		1.81	0.40	0.41	0.6	220
		5		2.11	0.32	0.56	0.2	220
2	ø8	4	VX220	1.69	0.40	0.47	1.0	340
		7		3.14	0.34	0.84	0.15	340
	ø10	4		1.68	0.49	0.50	1.0	340
		7		3.54	0.36	0.90	0.15	340
3	ø10	5	VX230	2.50	0.44	0.70	1.0	460
		8		2.77	0.82	1.22	0.3	460
		10		5.69	0.46	1.54	0.1	460
	ø12	5		2.50	0.44	0.70	1.0	460
		8		2.56	0.88	1.38	0.3	460
		10		5.69	0.64	1.76	0.1	460

For Steam

Construction

Dimensions

Note) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal type, 60 g for conduit terminal type respectively.

• Refer to "Glossary of Terms" on page 29 for details on the maximum operating pressure differential.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
-10 ^{Note)} to 60	-20 to 60

Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material ^{Note2)}	Leakage rate (Air) ^{Note1)}
NBR (FKM)	1 cm ³ /min or less (Aluminium body type) 15 cm ³ /min or less (Resin body type)

External Leakage

Seal material ^{Note2)}	Leakage rate (Air) ^{Note1)}
NBR (FKM)	1 cm ³ /min or less (Aluminium body type) 15 cm ³ /min or less (Resin body type)

Note 1) Leakage is the value at ambient temperature 20°C.

Note 2) For seal material/FKM, refer to "Other options".

Series VX21/22/23




For Air Single Unit

Model/Valve Specifications

N.O.

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.

Aluminium Body Type

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv		
1	1/8, 1/4	2	VX240	0.63	0.63	0.23	0.9	240
		3		1.05	0.68	0.41	0.45	240
		5		2.20	0.39	0.62	0.2	240
2	1/4, 3/8	4	VX250	1.90	0.52	0.62	0.8	370
		7		3.99	0.44	1.08	0.15	370
3	1/4, 3/8	5	VX260	1.96	0.55	0.75	0.8	490
		8		5.67	0.33	1.58	0.3	490

Resin Body Type (Built-in One-touch Fittings)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv		
1	ø6	2	VX240	0.82	0.44	0.23	0.9	240
		3		1.25	0.34	0.35	0.45	240
		5		1.45	0.43	0.40	0.2	240
	ø8	2		0.82	0.44	0.23	0.9	240
		3		1.81	0.40	0.41	0.45	240
		5		2.11	0.32	0.56	0.2	240
2	ø8	4	VX250	1.69	0.40	0.47	0.8	370
		7		3.14	0.34	0.84	0.15	370
	ø10	4		1.68	0.49	0.50	0.8	370
		7		3.54	0.36	0.90	0.15	370
3	ø10	5	VX260	2.50	0.44	0.70	0.8	500
		8		2.77	0.82	1.22	0.3	500
	ø12	5		2.50	0.42	0.70	0.8	500
		8		2.56	0.88	1.38	0.3	500

Note) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal type, 60 g for conduit terminal type respectively.

• Refer to "Glossary of Terms" on page 29 for details on the maximum operating pressure differential.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
-10 ^{Note)} to 60	-20 to 60

Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material ^{Note2)}	Leakage rate (Air) ^{Note1)}
NBR (FKM)	1 cm ³ /min or less (Aluminium body type)
	15 cm ³ /min or less (Resin body type)

External Leakage

Seal material ^{Note2)}	Leakage rate (Air) ^{Note1)}
NBR (FKM)	1 cm ³ /min or less (Aluminium body type)
	15 cm ³ /min or less (Resin body type)

Note 1) Leakage is the value at ambient temperature 20°C.

Note 2) For seal material/FKM, refer to "Other options".



How to Order (Single Unit)

VX2 1 0 A A A

Fluid ●

0 Air

● Other option

Symbol	Seal material *2	Oil-free	Port thread
—	NBR	—	Standard (Rc)*1
A	NBR	—	G
B	NBR	—	NPT
C	FKM	—	Standard (Rc)*1
D	NBR	○	G
E	NBR	○	NPT
F	FKM	—	G
G	FKM	—	NPT
H	NBR	○	Standard (Rc)*1
K	FKM	○	G
L	NBR	○	NPT
Z	NBR	○	Standard (Rc)*1

*1 When the body is resin, one-touch fittings are equipped as standard. Resin body is only applicable to C, H and Z options.

*2 For low concentration ozone resistant, select seal material FKM.

● Coil size/Valve type

Size	Symbol	Valve type
Size 1	1	N.C.
	4	N.O.

● Body material/Port size/Orifice diameter

Symbol	Body material	Port size	Orifice diameter
A	Aluminium	1/8	2
B			3
C			5
D		1/4	2
E			3
F			5
H	Resin*	ø6	2
J			3
K			5
L		ø8	2
M			3
N			5

Size	Symbol	Valve type
Size 2	2	N.C.
	5	N.O.

Symbol	Body material	Port size	Orifice diameter
A	Aluminium	1/4	4
B			7
D			4
E	Resin*	ø8	7
H			4
J			7
L	ø10	4	7
M			7

Size	Symbol	Valve type
Size 3	3	N.C.
	6	N.O.

Symbol	Body material	Port size	Orifice diameter
A	Aluminium	1/4	5
B			8
C			10 (N.C. only)
D		3/8	5
E			8
F			10 (N.C. only)
G	1/2	10 (N.C. only)	
H	Resin*	ø10	5
J			8
K			10 (N.C. only)
L		ø12	5
M			8
N			10 (N.C. only)

* One-touch fittings are attached to the resin body type.

● Voltage/Electrical entry (coil insulation type: Class B)

Symbol	Voltage	Electrical entry	Symbol	Voltage	Electrical entry
A	24 VDC	Grommet	Z2A	24 VDC	DIN terminal (With surge voltage suppressor, with light)
B	100 VAC	Grommet (With surge voltage suppressor)	Z2B	100 VAC	
C	110 VAC		Z2C	110 VAC	
D	200 VAC		Z2D	200 VAC	
E	230 VAC		Z2E	230 VAC	
F	24 VDC	DIN terminal (With surge voltage suppressor)	Z2F	48 VAC	
G	24 VDC		Z2G	220 VAC	
H	100 VAC		Z2H	240 VAC	
J	110 VAC		Z2V	24 VAC	
K	200 VAC	Conduit terminal (With surge voltage suppressor)	Z2J	12 VDC	
L	230 VAC		Z2K	24 VDC	
M	24 VDC		Z2L	100 VAC	
N	100 VAC		Z2M	110 VAC	
P	110 VAC	Conduit terminal (With surge voltage suppressor, with light)	Z2N	200 VAC	
Q	200 VAC		Z2P	230 VAC	
R	230 VAC		Z2Q	48 VAC	
S	24 VDC		Z2R	220 VAC	
T	100 VAC	Conduit (With surge voltage suppressor)	Z2S	240 VAC	
U	110 VAC		Z2W	24 VAC	
V	200 VAC		Z2T	12 VDC	
W	230 VAC		Z3A	24 VDC	
Y	24 VDC	Faston terminal	Z3B	100 VAC	DIN terminal (With surge voltage suppressor, without DIN connector)
Z1A	48 VAC	Grommet (With surge voltage suppressor)	Z3C	110 VAC	
Z1B	220 VAC		Z3D	200 VAC	
Z1C	240 VAC		Z3E	230 VAC	
Z1U	24 VAC		Z3F	48 VAC	
Z1D	12 VDC	Grommet (With surge voltage suppressor)	Z3G	220 VAC	
Z1E	12 VDC		Z3H	240 VAC	
Z1F	48 VAC		Z3V	24 VAC	
Z1G	220 VAC		Z3J	12 VDC	
Z1H	240 VAC	DIN terminal (With surge voltage suppressor)			
Z1V	24 VAC				
Z1J	12 VDC				
Z1K	48 VAC				
Z1L	220 VAC	Conduit terminal (With surge voltage suppressor)			
Z1M	240 VAC				
Z1W	24 VAC				
Z1N	12 VDC				
Z1P	48 VAC	Conduit (With surge voltage suppressor)			
Z1Q	220 VAC				
Z1R	240 VAC				
Z1Y	24 VAC				
Z1S	12 VDC				
Z1T	12 VDC	Faston terminal			

Note) Select brass (C37), in the type "for water" when interchangeable product is necessary for air.

Dimensions → Page 22 (Single unit)

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Series VX21/22/23




For Air Manifold

* For the fluid other than air and medium vacuum, please contact SMC.

Model/Valve Specifications

N.C.

Passage symbol




Common SUP type



N.O.

Passage symbol



Common SUP type

Refer to "Glossary of Terms" on page 29 for passage symbols.

Normally Closed (N.C.)

Size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]
			C [dm ³ /(s·bar)]	b	Cv	
1	2	VX2A0	0.63	0.63	0.23	1.0
	3		1.05	0.68	0.41	0.6
	5		2.20	0.39	0.62	0.2
2	4	VX2B0	1.90	0.52	0.62	1.0
	7		3.99	0.44	1.08	0.15
3	5	VX2C0	1.96	0.55	0.75	1.0
	7		3.99	0.44	1.08	0.3

Normally Open (N.O.)

Size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]
			C [dm ³ /(s·bar)]	b	Cv	
1	2	VX2D0	0.63	0.63	0.23	0.9
	3		1.05	0.68	0.41	0.45
	5		2.20	0.39	0.62	0.2
2	4	VX2E0	1.90	0.52	0.62	0.8
	7		3.99	0.44	1.08	0.15
3	5	VX2F0	1.96	0.55	0.75	0.8
	7		3.99	0.44	1.08	0.3

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
-10 ^{Note)} to 60	-20 to 60

Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material ^{Note 2)}	Leakage rate ^{Note 1)}
NBR (FKM)	1 cm ³ /min or less

External Leakage

Seal material ^{Note 2)}	Leakage rate ^{Note 1)}
NBR (FKM)	1 cm ³ /min or less

Note 1) Leakage is the value at ambient temperature 20°C.

Note 2) For seal material/FKM, refer to "Other options".



How to Order (Solenoid Valve for Manifold)

VX2 A 0 A A A

Fluid
0 Air

Coil size/Valve type

Size	Symbol	Valve type
Size 1	A	N.C.
	D	N.O.

Body material/Orifice diameter

Symbol	Body material	Orifice diameter
A	Resin	2
B		3
C		5

Other option

Symbol	Seal material *1	Oil-free
—	NBR	—
C	FKM	—
H		○
Z	NBR	○

*1 For low concentration ozone resistant, select seal material FKM.

Size 2

Size	Symbol	Valve type	Symbol	Body material	Orifice diameter
Size 2	B	N.C.	A	Resin	4
	E	N.O.	B		7

Size 3

Size	Symbol	Valve type	Symbol	Body material	Orifice diameter
Size 3	C	N.C.	A	Resin	5
	F	N.O.	B		7

Voltage/Electrical entry (coil insulation type: Class B)

Symbol	Voltage	Electrical entry	Symbol	Voltage	Electrical entry	
A	24 VDC	Grommet	Z2A	24 VDC	DIN terminal (With surge voltage suppressor, with light)	
B	100 VAC	Grommet (With surge voltage suppressor)	Z2B	100 VAC		
C	110 VAC		Z2C	110 VAC		
D	200 VAC		Z2D	200 VAC		
E	230 VAC		Z2E	230 VAC		
F	24 VDC		Z2F	48 VAC		
G	24 VDC		DIN terminal (With surge voltage suppressor)	Z2G		220 VAC
H	100 VAC	Z2H		240 VAC		
J	110 VAC	Z2V		24 VAC		
K	200 VAC	Z2J		12 VDC		
L	230 VAC	Conduit terminal (With surge voltage suppressor, with light)	Z2K	24 VDC		
M	24 VDC		Z2L	100 VAC		
N	100 VAC		Z2M	110 VAC		
P	110 VAC		Z2N	200 VAC		
Q	200 VAC		Z2P	230 VAC		
R	230 VAC		Z2Q	48 VAC		
S	24 VDC		Conduit (With surge voltage suppressor)	Z2R	220 VAC	
T	100 VAC			Z2S	240 VAC	
U	110 VAC			Z2W	24 VAC	
V	200 VAC			Z2T	12 VDC	
W	230 VAC	Faston terminal	Z3A	24 VDC		
Y	24 VDC		Z3B	100 VAC		
Z1A	48 VAC		Grommet (With surge voltage suppressor)	Z3C	110 VAC	
Z1B	220 VAC			Z3D	200 VAC	
Z1C	240 VAC			Z3E	230 VAC	
Z1U	24 VAC			Z3F	48 VAC	
Z1D	12 VDC		Grommet (With surge voltage suppressor)	Z3G	220 VAC	
Z1E	12 VDC			Z3H	240 VAC	
Z1F	48 VAC			DIN terminal (With surge voltage suppressor, without DIN connector)	Z3V	24 VAC
Z1G	220 VAC				Z3J	12 VDC
Z1H	240 VAC	DIN terminal (With surge voltage suppressor)				
Z1V	24 VAC					
Z1J	12 VDC		Conduit terminal (With surge voltage suppressor)			
Z1K	48 VAC					
Z1L	220 VAC					
Z1M	240 VAC	Conduit (With surge voltage suppressor)				
Z1W	24 VAC					
Z1N	12 VDC					
Z1P	48 VAC		Conduit (With surge voltage suppressor)			
Z1Q	220 VAC					
Z1R	240 VAC					
Z1Y	24 VAC	Faston terminal				
Z1S	12 VDC					
Z1T	12 VDC					

Manifold Base/How to Order

VVX2 1 0 A 02

Fluid
0 Air

Coil size

Size	Symbol
Size 1	1
Size 2	2
Size 3	3

Base material/Port size/Base type

Symbol	Base material	Individual port size	Base type
A	Aluminium	1/8	Common
B		1/4	SUP

Common port size: 3/8 (1N port)

Stations

Symbol	Stations
02	2 stations
03	3 stations
04	4 stations
05	5 stations
06	6 stations
07	7 stations
08	8 stations
09	9 stations
10	10 stations

Special thread

Symbol	Oil-free	Special thread
—	—	Rc
A	—	G
B	—	NPT
D	○	G
E	○	NPT
Z	○	Rc

Blanking Plate Assembly Part No.

For size 1 VVX021S - 4A - N

For size 2 VVX022S - 4A - N

For size 3 VVX023S - 4A - N

When mounting a blanking plate assembly, if the solenoid valve for the manifold is ozone resistant, (Seal material: FKM), please select FKM.

Seal material

N	NBR
F	FKM

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions


Series VX21/22/23



For Medium Vacuum Single Unit

Model/Valve Specifications


Passage symbol (Application example)



Refer to "Glossary of Terms" on page 29 for passage symbols.



Passage symbol (Application example)



Refer to "Glossary of Terms" on page 29 for passage symbols.



Normally Closed (N.C.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Operating pressure range		Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv	① Used with vacuum (Pa-abs)	② Used with pressure (MPa-G)	
1	1/8, 1/4	2	VX214	0.63	0.63	0.23	0.1 to atmospheric pressure	0 to 1.0	300
		3		1.05	0.68	0.41		0 to 0.6	300
		5		2.20	0.39	0.62		0 to 0.2	300
2	1/4, 3/8	4	VX224	1.90	0.52	0.62		0 to 1.0	460
		7		3.99	0.44	1.08		0 to 0.15	460
3	1/4, 3/8	5	VX234	1.96	0.55	0.75		0 to 1.0	580
		8		5.67	0.33	1.58		0 to 0.3	580
		10		5.74	0.64	2.21		0 to 0.1	580
	1/2	10		8.42	0.39	2.21		0 to 0.1	630

Normally Open (N.O.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Operating pressure range		Weight [g] ^{Note)}
				C [dm ³ /(s·bar)]	b	Cv	① Used with vacuum (Pa-abs)	② Used with pressure (MPa-G)	
1	1/8, 1/4	2	VX244	0.63	0.63	0.23	0.1 to atmospheric pressure	0 to 0.9	320
		3		1.05	0.68	0.41		0 to 0.45	320
		5		2.20	0.39	0.62		0 to 0.2	320
2	1/4, 3/8	4	VX254	1.90	0.52	0.62		0 to 0.8	490
		7		3.99	0.44	1.08		0 to 0.15	490
3	1/4, 3/8	5	VX264	1.96	0.55	0.75		0 to 0.8	620
		8		5.67	0.33	1.58		0 to 0.3	620

Note) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal type, 60 g for conduit terminal type respectively.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
1 to 60 ^{Note)}	-20 to 60

Note) With no freezing

Valve Leakage

Internal Leakage

Seal material	Leakage rate ^{Note)}
FKM	10 ⁻⁶ Pa·m ³ /sec or less

External Leakage

Seal material	Leakage rate ^{Note)}
FKM	10 ⁻⁶ Pa·m ³ /sec or less

Note) Leakage (10⁻⁶ Pa·m³/sec) is the value at differential pressure 0.1 MPa and ambient temperature 20°C.



How to Order (Single Unit)

VX2 1 4 A A A

Common Specifications

Seal material	FKM
Oil-free	
Non-leak	



Coil size/Valve type

Size	Symbol	Valve type
Size 1	1	N.C.
	4	N.O.

Body material/Port size/Orifice diameter

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/8	2
B			3
C			5
D		1/4	2
E			3
F			5
H	Stainless steel	1/8	2
J			3
K			5
L		1/4	2
M			3
N			5

Size	Symbol	Valve type
Size 2	2	N.C.
	5	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	4
B			7
D		3/8	4
E	7		
H	Stainless steel	1/4	4
J			7
L		3/8	4
M			7

Size	Symbol	Valve type
Size 3	3	N.C.
	6	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	5
B			8
C			10 (N.C. only)
D		3/8	5
E			8
F			10 (N.C. only)
G	1/2	10 (N.C. only)	
H	Stainless steel	1/4	5
J			8
K			10 (N.C. only)
L		3/8	5
M			8
N			10 (N.C. only)
P	1/2	10 (N.C. only)	

Bracket interchangeable with an old type

Size	Port size	Orifice diameter [mmø]	Bracket interchangeable with an old type
1	1/8, 1/4	2	○ (Interchangeable)
		3	○ (Interchangeable)
		5	○ (Interchangeable)
2	1/4, 3/8	4	○ (Interchangeable)
		7	○ (Interchangeable)
3	1/4, 3/8	5	○ (Interchangeable)
		8	× (Not interchangeable)*1
		10	× (Not interchangeable)*1
		1/2	—*1

*1 When the orifice is ø8, ø10, and when the body port size is 1/4 or 3/8, use a foot type bracket. (The old VX series is not compatible. If the body port size is 1/2, there are no XB settings (Refer to the following).)

*2 On the bottom side of the standard body, there are no mounting holes. Please be careful because the bracket cannot be retrofit. (Please inquire separately regarding mounting holes on the bottom side of the body.)

Interchangeable with existing bracket

—	No
XB	Yes

Note) For more information, please see table below.

Other option

Symbol	Port thread
—	Standard (Rc)
A	G
B	NPT

Voltage/Electrical entry (coil insulation type: Class B)

Symbol	Voltage	Electrical entry	Symbol	Voltage	Electrical entry				
A	24 VDC	Grommet	Z1P	48 VAC	Conduit (With surge voltage suppressor)				
B	100 VAC	Grommet (With surge voltage suppressor)	Z1Q	220 VAC					
C	110 VAC		Z1R	240 VAC					
D	200 VAC	Z1Y	24 VAC						
E	230 VAC	DIN terminal (With surge voltage suppressor)	Z1S	12 VDC	Faston terminal				
F	24 VDC		Z1T	12 VDC					
G	24 VDC	DIN terminal (With surge voltage suppressor)	Z2A	24 VDC	DIN terminal (With surge voltage suppressor, with light)				
H	100 VAC		Z2B	100 VAC					
J	110 VAC		Z2C	110 VAC					
K	200 VAC		Z2D	200 VAC					
L	230 VAC		Z2E	230 VAC					
M	24 VDC		Z2F	48 VAC					
N	100 VAC	Conduit terminal (With surge voltage suppressor)	Z2G	220 VAC		Conduit terminal (With surge voltage suppressor, with light)			
P	110 VAC		Z2H	240 VAC					
Q	200 VAC	Conduit (With surge voltage suppressor)	Z2V	24 VAC			DIN terminal (With surge voltage suppressor, without DIN connector)		
R	230 VAC		Z2J	12 VDC					
S	24 VDC	Faston terminal	Z2K	24 VDC	DIN terminal (With surge voltage suppressor, without DIN connector)				
T	100 VAC		Z2L	100 VAC					
U	110 VAC	Conduit (With surge voltage suppressor)	Z2M	110 VAC				DIN terminal (With surge voltage suppressor, without DIN connector)	
V	200 VAC		Z2N	200 VAC					
W	230 VAC	Faston terminal	Z2P	230 VAC					DIN terminal (With surge voltage suppressor, without DIN connector)
Y	24 VDC		Z2Q	48 VAC					
Z1A	48 VAC	Grommet (With surge voltage suppressor)	Z2R	220 VAC		DIN terminal (With surge voltage suppressor, without DIN connector)			
Z1B	220 VAC		Z2S	240 VAC					
Z1C	240 VAC	Conduit terminal (With surge voltage suppressor)	Z2W	24 VAC			DIN terminal (With surge voltage suppressor, without DIN connector)		
Z1U	24 VAC		Z2T	12 VDC					
Z1D	12 VDC	Grommet (With surge voltage suppressor)	Z3A	24 VDC	DIN terminal (With surge voltage suppressor, without DIN connector)				
Z1E	12 VDC		Z3B	100 VAC					
Z1F	48 VAC	DIN terminal (With surge voltage suppressor)	Z3C	110 VAC				DIN terminal (With surge voltage suppressor, without DIN connector)	
Z1G	220 VAC		Z3D	200 VAC					
Z1H	240 VAC	Conduit terminal (With surge voltage suppressor)	Z3E	230 VAC					DIN terminal (With surge voltage suppressor, without DIN connector)
Z1V	24 VAC		Z3F	48 VAC					
Z1J	12 VDC	Conduit terminal (With surge voltage suppressor)	Z3G	220 VAC		DIN terminal (With surge voltage suppressor, without DIN connector)			
Z1K	48 VAC		Z3H	240 VAC					
Z1L	220 VAC	Conduit terminal (With surge voltage suppressor)	Z3V	24 VAC			DIN terminal (With surge voltage suppressor, without DIN connector)		
Z1M	240 VAC		Z3J	12 VDC					
Z1W	24 VAC	Conduit terminal (With surge voltage suppressor)			DIN terminal (With surge voltage suppressor, without DIN connector)				
Z1N	12 VDC								

Dimensions → Page 25 (Single unit)

Specifications

For Air

For Medium Vacuum

For Water


For Oil

For Steam

Construction

Dimensions

Series VX21/22/23




For Medium Vacuum Manifold

* For the fluid other than air and medium vacuum, please contact SMC.

Model/Valve Specifications

N.C.

Passage symbol




Individual SUP type



N.O.

Passage symbol



Individual SUP type

Refer to "Glossary of Terms" on page 29 for passage symbols.

Normally Closed (N.C.)

Size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]
			C [dm ³ /(s·bar)]	b	Cv	
1	2	VX2A4	0.63	0.63	0.23	1.0
	3		1.05	0.68	0.41	0.6
	5		2.20	0.39	0.62	0.2
2	4	VX2B4	1.90	0.52	0.62	1.0
	7		3.99	0.44	1.08	0.15
3	5	VX2C4	1.96	0.55	0.75	1.0
	7		3.99	0.44	1.08	0.3

Normally Open (N.O.)

Size	Orifice diameter [mmø]	Model	Flow-rate characteristics			Maximum operating pressure differential [MPa]
			C [dm ³ /(s·bar)]	b	Cv	
1	2	VX2D4	0.63	0.63	0.23	0.9
	3		1.05	0.68	0.41	0.45
	5		2.20	0.39	0.62	0.2
2	4	VX2E4	1.90	0.52	0.62	0.8
	7		3.99	0.44	1.08	0.15
3	5	VX2F4	1.96	0.55	0.75	0.8
	7		3.99	0.44	1.08	0.3

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
1 to 60 ^{Note)}	-20 to 60

Note) With no freezing

Valve Leakage

Internal Leakage

Seal material	Leakage rate ^{Note)}
FKM	10 ⁻⁶ Pa·m ³ /sec or less

External Leakage


Seal material	Leakage rate ^{Note)}
FKM	10 ⁻⁶ Pa·m ³ /sec or less

Note) Leakage (10⁻⁶Pa·m³/sec) is the value at differential pressure 0.1 MPa and ambient temperature 20°C.



How to Order (Solenoid Valve for Manifold)

VX2 A 4 A A




Common Specifications

Seal material	FKM
Oil-free	
Non-leak	

Voltage/Electrical entry (coil insulation type: Class B)

Symbol	Voltage	Electrical entry	Symbol	Voltage	Electrical entry
A	24 VDC	Grommet	Z2A	24 VDC	DIN terminal (With surge voltage suppressor, with light)
B	100 VAC	Grommet (With surge voltage suppressor)	Z2B	100 VAC	
C	110 VAC		Z2C	110 VAC	
D	200 VAC		Z2D	200 VAC	
E	230 VAC		Z2E	230 VAC	
F	24 VDC	DIN terminal (With surge voltage suppressor)	Z2F	48 VAC	
G	24 VDC		Z2G	220 VAC	
H	100 VAC		Z2H	240 VAC	
J	110 VAC		Z2V	24 VAC	
K	200 VAC	Conduit terminal (With surge voltage suppressor)	Z2J	12 VDC	
L	230 VAC		Z2K	24 VDC	
M	24 VDC		Z2L	100 VAC	
N	100 VAC		Z2M	110 VAC	
P	110 VAC	Conduit (With surge voltage suppressor)	Z2N	200 VAC	
Q	200 VAC		Z2P	230 VAC	
R	230 VAC		Z2Q	48 VAC	
S	24 VDC		Z2R	220 VAC	
T	100 VAC	DIN terminal (With surge voltage suppressor, without DIN connector)	Z2S	240 VAC	
U	110 VAC		Z2W	24 VAC	
V	200 VAC		Z2T	12 VDC	
W	230 VAC		Z3A	24 VDC	
Y	24 VDC	Faston terminal	Z3B	100 VAC	
Z1A	48 VAC	Grommet (With surge voltage suppressor)	Z3C	110 VAC	
Z1B	220 VAC		Z3D	200 VAC	
Z1C	240 VAC		Z3E	230 VAC	
Z1U	24 VAC		Z3F	48 VAC	
Z1D	12 VDC	Grommet (With surge voltage suppressor)	Z3G	220 VAC	
Z1E	12 VDC		Z3H	240 VAC	
Z1F	48 VAC		Z3V	24 VAC	
Z1G	220 VAC		Z3J	12 VDC	
Z1H	240 VAC	DIN terminal (With surge voltage suppressor)			
Z1V	24 VAC				
Z1J	12 VDC				
Z1K	48 VAC				
Z1L	220 VAC	Conduit terminal (With surge voltage suppressor)			
Z1M	240 VAC				
Z1W	24 VAC				
Z1N	12 VDC				
Z1P	48 VAC	Conduit (With surge voltage suppressor)			
Z1Q	220 VAC				
Z1R	240 VAC				
Z1Y	24 VAC				
Z1S	12 VDC	Faston terminal			
Z1T	12 VDC				

Manifold Base/How to Order



Blanking Plate Assembly Part No.

For size 1 VVX021S - 4A - F

For size 2 VVX022S - 4A - F

For size 3 VVX023S - 4A - F

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions


Series VX21/22/23



For Water Single Unit


Model/Valve Specifications

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.

Normally Closed (N.C.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX212	5.5	0.23	1	300
		3		10.0	0.42	0.6	300
		5		15.0	0.63	0.2	300
2	1/4, 3/8	4	VX222	15.0	0.63	1	460
		7		26.0	1.08	0.15	460
3	1/4, 3/8	5	VX232	18.0	0.75	1	580
		8		38.0	1.58	0.3	580
		10		53.0	2.21	0.1	580
	1/2	10		53.0	2.21	0.1	630

Normally Open (N.O.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX242	5.5	0.23	0.9	320
		3		10.0	0.42	0.45	320
		5		15.0	0.63	0.2	320
2	1/4, 3/8	4	VX252	15.0	0.63	0.8	490
		7		26.0	1.08	0.15	490
3	1/4, 3/8	5	VX262	18.0	0.75	0.8	620
		8		38.0	1.58	0.3	620

Note) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal type, 60 g for conduit terminal type respectively.

• Refer to "Glossary of Terms" on page 29 for details on the maximum operating pressure differential.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
1 to 60 ^{Note)}	-20 to 60

Note) With no freezing

Valve Leakage

Internal Leakage

Seal material ^{Note 2)}	Leakage rate (Water) ^{Note 1)}
NBR (FKM)	0.1 cm ³ /min or less

External Leakage

Seal material ^{Note 2)}	Leakage rate (Water) ^{Note 1)}
NBR (FKM)	0.1 cm ³ /min or less

Note 1) Leakage is the value at ambient temperature 20°C.

Note 2) For seal material/FKM, refer to "Other options".

Series VX21/22/23




For Oil Single Unit

⚠ When the fluid is oil.

The kinematic viscosity must not exceed 50 mm²/s. The special construction of the armature adopted in the built-in full-wave rectifier type gives an improvement in OFF response by providing clearance on the absorbed surface when it is switched ON.


Model/Valve Specifications

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.

Passage symbol



Refer to "Glossary of Terms" on page 29 for passage symbols.

Normally Closed (N.C.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX213	5.5	0.23	1	300
		3		10.0	0.42	0.6	300
		5		15.0	0.63	0.2	300
2	1/4, 3/8	4	VX223	15.0	0.63	1	460
		7		26.0	1.08	0.15	460
3	1/4, 3/8	5	VX233	18.0	0.75	1	580
		8		38.0	1.58	0.3	580
		10		53.0	2.21	0.1	580
	1/2	10		53.0	2.21	0.1	630

Normally Open (N.O.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX243	5.5	0.23	0.9	320
		3		10.0	0.42	0.45	320
		5		15.0	0.63	0.2	320
2	1/4, 3/8	4	VX253	15.0	0.63	0.8	490
		7		26.0	1.08	0.15	490
3	1/4, 3/8	5	VX263	18.0	0.75	0.8	620
		8		38.0	1.58	0.3	620

Note) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal type, 60 g for conduit terminal type respectively.

• Refer to "Glossary of Terms" on page 29 for details on the maximum operating pressure differential.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
-5 ^{Note)} to 60	-20 to 60

Note) Kinematic viscosity: 50 mm²/s or less

Valve Leakage

Internal Leakage

Seal material	Leakage rate (Oil) ^{Note)}
FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage rate (Oil) ^{Note)}
FKM	0.1 cm ³ /min or less

Note) Leakage is the value at ambient temperature 20°C.

Direct Operated 2 Port Solenoid Valve Series VX21/22/23

For Oil Single Unit



How to Order

VX2 1 3 A A A

Common Specifications

Seal material	FKM
---------------	-----



Coil size/Valve type

Size	Symbol	Valve type
Size 1	1	N.C.
	4	N.O.

Body material/Port size/Orifice diameter

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/8	2
B			3
C			5
D		1/4	2
E			3
F			5
H	Stainless steel	1/8	2
J			3
K			5
L		1/4	2
M			3
N			5

Interchangeable with existing bracket

—	No
XB	Yes

Note) For more information, please see table below.

Other option

Symbol	Oil-free	Port thread
—	—	Standard (Rc)
A	—	G
B	—	NPT
D	—	G
E	○	NPT
Z	—	Standard (Rc)

Size	Symbol	Valve type
Size 2	2	N.C.
	5	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	4
B			7
D		3/8	4
E	7		
H	Stainless steel	1/4	4
J			7
L			4
M		3/8	4
			7
			7

Size	Symbol	Valve type
Size 3	3	N.C.
	6	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	5
B			8
C			10 (N.C. only)
D		3/8	5
E			8
F			10 (N.C. only)
G	1/2	10 (N.C. only)	
H	Stainless steel	1/4	5
J			8
K			10 (N.C. only)
L		3/8	5
M			8
N			10 (N.C. only)
P	1/2	10 (N.C. only)	

Bracket interchangeable with an old type

Size	Port size	Orifice diameter [mmø]	Bracket interchangeable with an old type
1	1/8, 1/4	2	○ (Interchangeable)
		3	○ (Interchangeable)
		5	○ (Interchangeable)
2	1/4, 3/8	4	○ (Interchangeable)
		7	○ (Interchangeable)
3	1/4, 3/8	5	○ (Interchangeable)
		8	× (Not interchangeable)*1
		10	× (Not interchangeable)*1
		1/2	10

*1 When the orifice is ø8, ø10, and when the body port size is 1/4 or 3/8, use a foot type bracket. (The old VX series is not compatible. If the body port size is 1/2, there are no XB settings (Refer to the following).)

*2 On the bottom side of the standard body, there are no mounting holes. Please be careful because the bracket cannot be retrofit. (Please inquire separately regarding mounting holes on the bottom side of the body.)

Voltage/Electrical entry (coil insulation type: Class B)

Symbol	Voltage	Electrical entry	Symbol	Voltage	Electrical entry
A	24 VDC	Grommet	Z1P	48 VAC	Conduit (With surge voltage suppressor)
B	100 VAC	Grommet (With surge voltage suppressor)	Z1Q	220 VAC	
C	110 VAC		Z1R	240 VAC	
D	200 VAC		Z1Y	24 VAC	
E	230 VAC	DIN terminal (With surge voltage suppressor)	Z1S	12 VDC	Faston terminal
F	24 VDC		Z1T	12 VDC	
G	24 VDC		Z2A	24 VDC	
H	100 VAC	DIN terminal (With surge voltage suppressor)	Z2B	100 VAC	DIN terminal (With surge voltage suppressor, with light)
J	110 VAC		Z2C	110 VAC	
K	200 VAC		Z2D	200 VAC	
L	230 VAC	Z2E	230 VAC		
M	24 VDC	Conduit terminal (With surge voltage suppressor)	Z2F	48 VAC	
N	100 VAC		Z2G	220 VAC	
P	110 VAC		Z2H	240 VAC	
Q	200 VAC	Conduit (With surge voltage suppressor)	Z2V	24 VAC	Conduit terminal (With surge voltage suppressor, with light)
R	230 VAC		Z2J	12 VDC	
S	24 VDC		Z2K	24 VDC	
T	100 VAC	Conduit (With surge voltage suppressor)	Z2L	100 VAC	
U	110 VAC		Z2M	110 VAC	
V	200 VAC		Z2N	200 VAC	
W	230 VAC	Faston terminal	Z2P	230 VAC	
Y	24 VDC		Z2Q	48 VAC	
Z1A	48 VAC		Grommet (With surge voltage suppressor)	Z2R	220 VAC
Z1B	220 VAC	Z2S		240 VAC	
Z1C	240 VAC	Z2W		24 VAC	
Z1U	24 VAC	Grommet	Z2T	12 VDC	DIN terminal (With surge voltage suppressor, without DIN connector)
Z1D	12 VDC		Z3A	24 VDC	
Z1E	12 VDC		Grommet (With surge voltage suppressor)	Z3B	
Z1F	48 VAC	Z3C		110 VAC	
Z1G	220 VAC	Z3D		200 VAC	
Z1H	240 VAC	DIN terminal (With surge voltage suppressor)	Z3E	230 VAC	
Z1V	24 VAC		Z3F	48 VAC	
Z1J	12 VDC		Z3G	220 VAC	
Z1K	48 VAC	Conduit terminal (With surge voltage suppressor)	Z3H	240 VAC	
Z1L	220 VAC		Z3V	24 VAC	
Z1M	240 VAC		Z3J	12 VDC	
Z1W	24 VAC	Grommet			
Z1N	12 VDC				

Dimensions → Page 25 (Single unit)

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Series VX21/22/23




For Steam Single Unit

* Can be used with heated water.

Model/Valve Specifications


Passage symbol

N.C.



Passage symbol

N.O.



Refer to "Glossary of Terms" on page 29 for passage symbols.

Normally Closed (N.C.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX215	5.5	0.23	1	300
		3		10.0	0.42	0.6	300
		5		15.0	0.63	0.2	300
2	1/4, 3/8	4	VX225	15.0	0.63	1	460
		7		26.0	1.08	0.15	460
3	1/4, 3/8	5	VX235	18.0	0.75	1	580
		8		38.0	1.58	0.3	580
		10		53.0	2.21	0.1	580
	1/2	10		53.0	2.21	0.1	630

Normally Open (N.O.)

Size	Port size	Orifice diameter [mmø]	Model	Flow-rate characteristics		Maximum operating pressure differential [MPa]	Weight [g] ^{Note)}
				AV (x 10 ⁻⁶ m ²)	Conversion Cv		
1	1/8, 1/4	2	VX245	5.5	0.23	0.9	320
		3		10.0	0.42	0.45	320
		5		15.0	0.63	0.2	320
2	1/4, 3/8	4	VX255	15.0	0.63	0.8	490
		7		26.0	1.08	0.15	490
3	1/4, 3/8	5	VX265	18.0	0.75	0.8	620
		8		38.0	1.58	0.3	620

Note) Weight of grommet type. Add 10 g for conduit type, 60 g for conduit terminal type respectively.

Fluid and Ambient Temperature

Fluid temperature [°C]	Ambient temperature [°C]
Steam: 183 or less	-20 to 60
Heated water: 99 or less	

Valve Leakage

Internal Leakage

Fluid	Seal material	Leakage rate
Steam	FKM for high temperature	1.0 cm ³ /min or less
Heated water		0.1 cm ³ /min or less

External Leakage

Fluid	Seal material	Leakage rate
Steam	FKM for high temperature	1.0 cm ³ /min or less
Heated water		0.1 cm ³ /min or less

Direct Operated 2 Port Solenoid Valve Series VX21/22/23



For Steam Single Unit

* Can be used with heated water.



How to Order (Single Unit)

VX2 1 5 A B A

Common Specifications

Seal material FKM for high temperature

Interchangeable with existing bracket

—	No
XB	Yes

Note) For more information, please see table below.

Other option

Symbol	Oil-free	Port thread
—	—	Standard (Rc)
A	—	G
B	—	NPT
D	—	G
E	○	NPT
Z	—	Standard (Rc)

Coil size/Valve type

Size	Symbol	Valve type
Size 1	1	N.C.
	4	N.O.

Body material/Port size/Orifice diameter

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/8	2
B			3
C			5
D		1/4	2
E			3
F			5
H	Stainless steel	1/8	2
J			3
K			5
L		1/4	2
M			3
N			5

Size	Symbol	Valve type
Size 2	2	N.C.
	5	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	4
B			7
D		3/8	4
E	7		
H	Stainless steel	1/4	4
J			7
L		3/8	4
M			7

Size	Symbol	Valve type
Size 3	3	N.C.
	6	N.O.

Symbol	Body material	Port size	Orifice diameter
A	C37 (Brass)	1/4	5
B			8
C			10 (Only N.C.)
D		3/8	5
E			8
F			10 (Only N.C.)
G	1/2	10 (Only N.C.)	
H	Stainless steel	1/4	5
J			8
K			10 (Only N.C.)
L		3/8	5
M			8
N			10 (Only N.C.)
P	1/2	10 (Only N.C.)	

Voltage/Electrical entry (coil insulation type: Class H)

Symbol	Voltage	Electrical entry
B	100 VAC	Grommet (With surge voltage suppressor)
C	110 VAC	
D	200 VAC	
E	230 VAC	
N	100 VAC	
P	110 VAC	Conduit terminal (With surge voltage suppressor)
Q	200 VAC	
R	230 VAC	
T	100 VAC	Conduit (With surge voltage suppressor)
U	110 VAC	
V	200 VAC	
W	230 VAC	Grommet (With surge voltage suppressor)
Z1A	48 VAC	
Z1B	220 VAC	
Z1C	240 VAC	
Z1U	24 VAC	
Z1K	48 VAC	Conduit terminal (With surge voltage suppressor)
Z1L	220 VAC	
Z1M	240 VAC	
Z1W	24 VAC	Conduit (With surge voltage suppressor)
Z1P	48 VAC	
Z1Q	220 VAC	
Z1R	240 VAC	
Z1Y	24 VAC	
Z2L	100 VAC	Conduit terminal (With surge voltage suppressor, with light)
Z2M	110 VAC	
Z2N	200 VAC	
Z2P	230 VAC	
Z2Q	48 VAC	
Z2R	220 VAC	
Z2S	240 VAC	
Z2W	24 VAC	

* DIN terminal, Faston terminal or DC specification are not available.

Dimensions → Page 27 (Single unit)

Bracket interchangeable with an old type

Size	Port size	Orifice diameter [mmø]	Bracket interchangeable with an old type
1	1/8, 1/4	2	○ (Interchangeable)
		3	○ (Interchangeable)
		5	○ (Interchangeable)
2	1/4, 3/8	4	○ (Interchangeable)
		7	○ (Interchangeable)
3	1/4, 3/8	5	○ (Interchangeable)
		8	× (Not interchangeable)*1
		10	× (Not interchangeable)*1
		1/2	10

*1 When the orifice is ø8, ø10, and when the body port size is 1/4 or 3/8, use a foot type bracket. (The old VX series is not compatible. If the body port size is 1/2, there are no XB settings (Refer to the following).)

*2 On the bottom side of the standard body, there are no mounting holes. Please be careful because the bracket cannot be retrofit. (Please inquire separately regarding mounting holes on the bottom side of the body.)

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction


Dimensions

Series VX21/22/23

Construction/Single Unit

Normally Closed (N.C.)


Body material: Aluminium, C37(Brass),
Stainless steel



Component Parts

No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Core	Fe
3	Tube	Stainless steel
4	Spring	Stainless steel
5	Armature assembly	NBR, FKM, Stainless steel
6	Seal	NBR, FKM
7	Body	Aluminium, C37(Brass), Stainless steel

Body material: Resin




Component Parts

No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Core	Fe
3	Tube	Stainless steel
4	Spring	Stainless steel
5	Armature assembly	NBR, Stainless steel
6	Seal	NBR, FKM
7	Body	Resin (PBT)

Normally Open (N.O.)


Body material: Aluminium, C37(Brass),
Stainless steel



Component Parts

No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Sleeve assembly	Stainless steel, Resin (PPS)
3	Push rod assembly	Resin (PPS), Stainless steel, NBR, FKM
4	Spring	Stainless steel
5	O-ring A	NBR, FKM
6	O-ring B	NBR, FKM
7	Adapter	Resin (PPS)
8	O-ring C	NBR, FKM
9	Body	Aluminium, C37(Brass), Stainless steel

Body material: Resin




Component Parts


No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Sleeve assembly	Stainless steel, Resin (PPS)
3	Push rod assembly	Resin (PPS), Stainless steel, NBR, FKM
4	Spring	Stainless steel
5	O-ring A	NBR, FKM
6	O-ring B	NBR, FKM
7	Adapter	Resin (PPS)
8	O-ring C	NBR, FKM
9	Body	Resin (PBT)

Construction/Manifold

Normally Closed (N.C.) Common SUP type (for air)
Base material: Aluminium



Individual SUP type (for medium vacuum)




Component Parts


No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Core	Fe
3	Tube	Stainless steel
4	Spring	Stainless steel
5	Armature assembly	NBR, FKM, Stainless steel
6	Seal	NBR, FKM
7	Body	Resin (PPS)
8	Gasket	NBR, FKM
9	Base	Aluminium

Normally Open (N.O.)

Base material: Aluminium Common SUP type (for air)



Individual SUP type (for medium vacuum)



Component Parts

No.	Description	Material
1	Solenoid coil	Cu + Fe + Resin
2	Sleeve assembly	Stainless steel, Resin (PPS)
3	Push rod assembly	Resin (PPS), Stainless steel, NBR, FKM
4	Spring	Stainless steel
5	O-ring A	NBR, FKM
6	O-ring B	NBR, FKM

No.	Description	Material
7	Adapter	Resin (PPS)
8	O-ring C	NBR, FKM
9	Body	Resin (PPS)
10	Gasket	NBR, FKM
11	Base	Aluminium

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions


Series VX21/22/23




For Air

Dimensions/Body Material: Aluminium


Grommet (DC)




Grommet (with surge voltage suppressor)




DIN terminal




Conduit terminal



Conduit



Faston terminal




Size	Port size P	A	B	B ₁	C	D	E	F	Electrical entry			
									Grommet		Grommet (with surge voltage suppressor)	
									Q	R	Q	R
1	1/8, 1/4	19	43	21	61 (67)	30	9.5	20	27	42 (47.5)	30	28.5 (34)
2	1/4, 3/8	24	45	22.5	76 (84)	35	12	22	29.5	53.5 (61.5)	32.5	39.5 (47.5)
3	1/4, 3/8	24	45	22.5	81 (89)	40	12	24.5	32	58 (66.5)	35	44.5 (52.5)
	1/2	30	50	25	86.5	40	15	24.5	32	61	35	47.5

Size	Port size P	Electrical entry										
		DIN terminal			Conduit terminal				Conduit		Faston terminal	
		Q	R	S	Q	R	S	T	Q	R	Q	R
1	1/8, 1/4	64.5	34 (39.5)	52.5	99.5	36 (41.5)	68.5	77 (83)	47.5	36 (41.5)	23	42 (47.5)
2	1/4, 3/8	67	45 (53)	55	102	47 (55)	71	91 (99)	50	47 (55)	25.5	53.5 (61.5)
3	1/4, 3/8	69.5	50 (58)	57.5	104.5	52 (60)	73.5	96 (104)	52.5	52 (60)	28	58 (66.5)
	1/2	69.5	53	57.5	104.5	55	73.5	101.5	52.5	55	28	61

() : Denotes the Normally Open (N.O.) dimensions.


Terminal part Faston connector 250 Series






Dimensions/Body Material: Resin


Grommet




Grommet (with surge voltage suppressor)



DIN terminal



Conduit terminal



For information on handling one-touch fittings and appropriate tubing, refer to page 39 and KQ2 series one-touch fittings in KQ2's catalogue. The KQ2 series information can be downloaded from the following SMC website, <http://www.smc.eu>

Size	One-touch fitting P	B	B ₁	C	D	E	F	Mounting bracket dimensions					
								U	U ₁	W	X	X ₁	Y
1	ø6, ø8	53.5	29	65.5 (71.5)	30	13.5	20	45	22.5	22	52	26	30
2	ø8, ø10	66	36	76.5 (84.5)	35	15	22	53	26.5	27	62	31	35
3	ø10, ø12	68	37	84 (92)	40	16.5	24.5	58	29	31	67	33.5	40

Size	One-touch fitting P	Electrical entry											
		Grommet		Grommet (with surge voltage suppressor)		DIN terminal			Conduit terminal				
		Q	R	Q	R	Q	R	S	Q	R	S	T	
1	ø6, ø8	27	42.5 (48)	30	29 (34.5)	64.5	34.5 (40)	52.5	99.5	36.5 (42)	68.5	81.5 (87)	
2	ø8, ø10	29.5	51 (59)	32.5	37 (45)	67	43 (50.5)	55	102	45 (52.5)	71	91.5 (99.5)	
3	ø10, ø12	32	56.5 (65)	35	43 (51)	69.5	48.5 (56.5)	57.5	104.5	50.5 (58.5)	73.5	98.5 (106.5)	

() : Denotes the Normally Open (N.O.) dimensions.

Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Series VX21/22/23






For Air

Dimensions/Body Material: Resin

Conduit


Faston terminal



Size	One-touch fitting P	B	B ₁	C	D	E	F	Mounting bracket dimensions						Electrical entry			
														Conduit		Faston terminal	
								U	U ₁	W	X	X ₁	Y	Q	R	Q	R
1	ø6, ø8	53.5	29	65.5 (71.5)	30	13.5	20	45	22.5	22	52	26	30	47.5	36.5 (42)	23	42.5 (48)
2	ø8, ø10	66	36	76.5 (84.5)	35	15	22	53	26.5	27	62	31	35	50	45 (52.5)	25.5	51 (59)
3	ø10, ø12	68	37	84 (92)	40	16.5	24.5	58	29	31	67	33.5	40	52.5	50.5 (58.5)	28	56.5 (65)


(): Denotes the Normally Open (N.O.) dimensions.

Direct Operated 2 Port Solenoid Valve *Series VX21/22/23*




Dimensions/Body Material: C37(Brass), Stainless Steel


Grommet




Grommet (with surge voltage suppressor)



DIN terminal



Conduit terminal



Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Size	Port size P	A	B	B ₁	C	D	E	F	Mounting bracket dimensions				
									M	U	W	X	Y
1	1/8, 1/4	19	43	21	61 (67)	30	9.5	20	12.8	46	36	11	6
2	1/4, 3/8	22	45	22.5	74.5 (82.5)	35	10.5	22	19	56	46	13	7
3	1/4, 3/8	22	45	22.5	79 (88)	40	10.5	24.5	19	56	46	13	7
	1/2	29.5	50	25	85.5	40	14	24.5	—	—	—	—	—

Size	Port size P	Electrical entry											
		Grommet		Grommet (with surge voltage suppressor)		DIN terminal			Conduit terminal				
		Q	R	Q	R	Q	R	S	Q	R	S	T	
1	1/8, 1/4	27	42 (47.5)	30	28.5 (34)	64.5	34 (39.5)	52.5	99.5	36 (41.5)	68.5	77 (83)	
2	1/4, 3/8	29.5	53.5 (61.5)	32.5	39.5 (47.5)	67	45 (53)	55	102	47 (55)	71	89.5 (97.5)	
3	1/4, 3/8	32	57.5 (67)	35	44 (53)	69.5	49.5 (58.5)	57.5	104.5	51.5 (60.5)	73.5	94 (103)	
	1/2	32	61	35	47.5	69.5	53	57.5	104.5	55	73.5	100.5	

(): Denotes the Normally Open (N.O.) dimensions.

Series VX21/22/23










For Medium Vacuum, Water, Oil

Dimensions/Body Material: C37(Brass), Stainless Steel

Conduit

Faston terminal



Size	Port size P	A	B	B ₁	C	D	E	F	Mounting bracket dimensions				
									M	U	W	X	Y
1	1/8, 1/4	19	43	21	61 (67)	30	9.5	20	12.8	46	36	11	6
2	1/4, 3/8	22	45	22.5	74.5 (82.5)	35	10.5	22	19	56	46	13	7
3	1/4, 3/8	22	45	22.5	79 (88)	40	10.5	24.5	19	56	46	13	7
	1/2	29.5	50	25	85.5	40	14	24.5	—	—	—	—	—

Size	Port size P	Electrical entry			
		Conduit		Faston terminal	
		Q	R	Q	R
1	1/8, 1/4	47.5	36 (41.5)	23	42 (47.5)
2	1/4, 3/8	50	47 (55)	25.5	53.5 (61.5)
3	1/4, 3/8	52.5	51.5 (60.5)	28	57.5 (67)
	1/2	52.5	55	28	61

(): Denotes the Normally Open (N.O.) dimensions.









* Can be used with heated water.




Dimensions/Body Material: C37(Brass), Stainless Steel

Grommet

Conduit terminal



Conduit



Specifications

For Air

For Medium Vacuum

For Water

For Oil

For Steam

Construction

Dimensions

Size	Port size P	A	B	B ₁	C	D	E	F	Mounting bracket dimensions [mm]				
									M	U	W	X	Y
1	1/8, 1/4	19	43	21	61 (67)	30	9.5	20	12.8	46	36	11	6
2	1/4, 3/8	22	45	22.5	74.5 (82.5)	35	10.5	22	19	56	46	13	7
3	1/4, 3/8	22	45	22.5	79 (88)	40	10.5	24.5	19	56	46	13	7
	1/2	29.5	50	25	85.5	40	14	24.5	—	—	—	—	—

Size	Port size P	Electrical entry							
		Grommet		Conduit terminal			Conduit		
		Q	R	Q	R	S	T	Q	R
1	1/8, 1/4	27	42 (47.5)	108	36 (41.5)	77	77 (83)	47.5	36 (41.5)
2	1/4, 3/8	29.5	53.5 (61.5)	110.5	47 (55)	79.5	89.5 (97.5)	50	47 (55)
3	1/4, 3/8	32	57.5 (66)	113	51.5 (59.5)	82	94 (103)	52.5	51.5 (59.5)
	1/2	32	61	113	55	82	100.5	52.5	55

() : Denotes the Normally Open (N.O.) dimensions.


DIN terminal and Faston terminal are not available for valves for steam and heated water.

Series VX21/22/23



For Medium Vacuum, Air

Dimensions/Manifold/Base Material: Aluminium



* D side port does not have a plug.

[mm]

Size	Dimensions	n (stations)								
		2	3	4	5	6	7	8	9	10
1	L ₁	86	122	158	194	230	266	302	338	374
	L ₂	100	136	172	208	244	280	316	352	388
2	L ₁	90	126	162	198	234	270	306	342	378
	L ₂	108	144	180	216	252	288	324	360	396
3	L ₁	103	144	185	226	267	308	349	390	431
	L ₂	121	162	203	244	285	326	367	408	449

Size	A	B	C	D	E	F	H	J	K	M	N	P
1	38	15.5	10.5	11	25	32	20	12	7	6.5	50.5 (56.5)	36
2	49	18	13	13	30	36	22	15	9	8.5	60.5 (68.5)	36
3	49	20.5	13	13	30	40	24.5	15	9	8.5	65.5 (73.5)	41

Size	Grommet		Grommet (With surge voltage suppressor)		DIN terminal*			Conduit terminal				Conduit		Faston terminal	
	Q ₁	R ₁	Q ₂	R ₂	Q ₃	R ₃	S ₁	Q ₄	R ₄	S ₂	T	Q ₅	R ₅	Q ₆	R ₆
1	27	40.5 (46.5)	30	27 (33)	64.5	32.5 (38.5)	52.5	99.5	34.5 (40.5)	68.5	66.5 (72)	47.5	34.5 (40.5)	23	40.5 (46.5)
2	29.5	49.5 (57.5)	32.5	36 (44)	67	41.5 (49.5)	55	102	43.5 (51.5)	71	75.5 (83.5)	50	43.5 (51.5)	25.5	49.5 (57.5)
3	32	54.5 (63)	35	41 (49)	69.5	46.5 (55)	57.5	104.5	48.5 (57)	73.5	80.5 (89.5)	52.5	48.5 (57)	28	54.5 (63)

(): Denotes the Normally Open (N.O.) dimensions.

* When using a DIN terminal that faces downward, be careful of interference in the electrical wires and piping.

Series VX21/22/23

Glossary of Terms

Pressure Terminology

1. Maximum operating pressure differential

The maximum pressure differential (the difference between the inlet and outlet pressure) which is allowed for operation. When the outlet pressure is 0 MPa, this becomes the maximum operating pressure.

2. Minimum operating pressure differential

The minimum pressure differential (the difference between the inlet pressure and outlet pressure) required to keep the main valve fully opened.

3. Maximum system pressure

The maximum pressure that can be applied inside the pipelines (line pressure).

[The pressure differential in the solenoid valve portion must be less than the maximum operating pressure differential.]

4. Withstand pressure

The pressure in which the valve must be withstood without a drop in performance after holding for one minute under prescribed (static) pressure and returning to the operating pressure range. [value under the prescribed conditions]

Electrical Terminology

1. Surge voltage

A high voltage which is momentarily generated by shutting off the power in the shut-off area.

2. Enclosure

A degree of protection defined in the "JIS C 0920: Waterproof test of electric machinery/appliance and the degree of protection against the intrusion of solid foreign objects."

Verify the degree of protection for each product.



● First Characteristics:

Degrees of protection against solid foreign objects

0	Non-protected
1	Protected against solid foreign objects of 50 mm ϕ and greater
2	Protected against solid foreign objects of 12 mm ϕ and greater
3	Protected against solid foreign objects of 2.5 mm ϕ and greater
4	Protected against solid foreign objects of 1.0 mm ϕ and greater
5	Dust-protected
6	Dust-tight

● Second Characteristics:

Degrees of protection against water

0	Non-protected	—
1	Protected against vertically falling water drops	Dripproof type 1
2	Protected against vertically falling water drops when enclosure tilted up to 15°	Dripproof type 2
3	Protected against rainfall when enclosure tilted up to 60°	Rainproof type
4	Protected against splashing water	Splashproof type
5	Protected against water jets	Water-jet-proof type
6	Protected against powerful water jets	Powerful water-jet-proof type
7	Protected against the effects of temporary immersion in water	Immersible type
8	Protected against the effects of continuous immersion in water	Submersible type

Example) IP65: Dust-tight, Water-jet-proof type

"Water-jet-proof type" means that no water intrudes inside an equipment that could hinder from operating normally by means of applying water for 3 minutes in the prescribed manner. Take appropriate protection measures, since a device is not usable in an environment where a droplet of water is splashed constantly.

Others

1. Material

NBR: Nitrile rubber

FKM: Fluoro rubber – Trade names: Viton®, Dai-el®, etc.

2. Oil-free treatment

The degreasing and washing of wetted parts

3. Passage symbol

In the JIS symbol ($\square \square \square \square \square \square$) IN and OUT are in a blocked condition (\pm), but actually in the case of reverse pressure (OUT>IN), there is a limit to the blocking.

Faston Terminal

1. Faston™ is a trademark of Tyco Electronics Corp.

2. For electrical connection of the Faston terminal and molded coil, please use Tyco's "Amp/Faston connector/250 Series" or the equivalent.

Solenoid Valve Flow-rate Characteristics 1

(How to indicate flow-rate characteristics)

1. Indication of flow-rate characteristics

The flow-rate characteristics in equipment such as a solenoid valve, etc. are indicated in their specifications as shown in Table (1).

Table (1) Indication of Flow-rate Characteristics

Corresponding equipment	Indication by international standard	Other indications	Conformed standard
Pneumatic equipment	C, b	—	ISO 6358: 1989 JIS B 8390: 2000
	—	S	JIS B 8390: 2000 Equipment: JIS B 8373, 8374, 8375, 8379, 8381
		Cv	ANSI/(NFPA)T3.21.3: 1990
Process fluid control equipment	Av	—	IEC60534-2-3: 1997 JIS B 2005: 1995
	—	Cv	Equipment: JIS B 8471, 8472, 8473

2. Pneumatic equipment

2.1 Indication according to the international standards

(1) Conformed standard

ISO 6358: 1989 : Pneumatic fluid power—Components using compressible fluids—Determination of flow-rate characteristics

JIS B 8390: 2000 : Pneumatic fluid power—Components using compressible fluids—How to test flow-rate characteristics

(2) Definition of flow-rate characteristics

The flow-rate characteristics are indicated as a result of a comparison between sonic conductance **C** and critical pressure ratio **b**.

Sonic conductance **C** : Value which divides the passing mass flow rate of an equipment in a choked flow condition by the product of the upstream absolute pressure and the density in a standard condition.

Critical pressure ratio **b** : Pressure ratio (downstream pressure/upstream pressure) which will turn to a choked flow when the value is smaller than this ratio.

Choked flow : The flow in which the upstream pressure is higher than the downstream pressure and where sonic speed in a certain part of an equipment is reached. Gaseous mass flow rate is in proportion to the upstream pressure and not dependent on the downstream pressure.

Subsonic flow : Flow greater than the critical pressure ratio

Standard condition : Air in a temperature state of 20°C, absolute pressure 0.1 MPa (= 100 kPa = 1 bar), relative humidity 65%.

It is stipulated by adding the “(ANR)” after the unit depicting air volume. (standard reference atmosphere)

Conformed standard: ISO 8778: 1990 Pneumatic fluid power—Standard reference atmosphere, JIS B 8393: 2000: Pneumatic fluid power—Standard reference atmosphere

(3) Formula for flow rate

Described by the practical units as following.

When $\frac{P_2 + 0.1}{P_1 + 0.1} \leq b$, **choked flow**

$$Q = 600 \times C (P_1 + 0.1) \sqrt{\frac{293}{273 + t}} \dots\dots\dots(1)$$

When $\frac{P_2 + 0.1}{P_1 + 0.1} > b$, **subsonic flow**

$$Q = 600 \times C (P_1 + 0.1) \sqrt{1 - \left[\frac{P_2 + 0.1}{P_1 + 0.1} - b \right]^2} \sqrt{\frac{293}{273 + t}} \dots\dots\dots(2)$$

Q: Air flow rate [dm³/min (ANR)], dm³ (Cubic decimetre) of SI unit are allowed to be described by L (litre).
1 dm³ = 1 L

C : Sonic conductance [dm³/(s·bar)]

b : Critical pressure ratio [—]

P₁ : Upstream pressure [MPa]

P₂ : Downstream pressure [MPa]

t : Temperature [°C]

Note) Formula of subsonic flow is the elliptic analogous curve.

Flow-rate characteristics are shown in Graph (1) For details, please make use of SMC's "Energy Saving Program".

Example)


Obtain the air flow rate for **P₁** = 0.4 [MPa], **P₂** = 0.3 [MPa], **t** = 20 [°C] when a solenoid valve is performed in **C** = 2 [dm³/(s·bar)] and **b** = 0.3.

According to formula (1), the maximum flow rate = $600 \times 2 \times (0.4 + 0.1) \times \sqrt{\frac{293}{273 + 20}} = 600$ [dm³/min (ANR)]

$$\text{Pressure ratio} = \frac{0.3 + 0.1}{0.4 + 0.1} = 0.8$$

Based on Graph (1), the flow rate ratio will be 0.7 when the pressure ratio is 0.8 and **b** = 0.3.

Therefore, flow rate = Maximum flow rate x flow rate ratio = 600 x 0.7 = 420 [dm³/min(ANR)]



Graph (1) Flow-rate characteristics

(4) Test method

Attach a test equipment with the test circuit shown in Fig. (1) while maintaining the upstream pressure to a certain level which does not go below 0.3 MPa. Next, measure the maximum flow to be saturated in the first place, then measure this flow rate at 80%, 60%, 40%, 20% and the upstream and downstream pressure. And then, obtain the sonic conductance **C** from this maximum flow rate. Besides that, substitute each data of others for the subsonic flow formula to find **b**, then obtain the critical pressure ratio **b** from that average.




Fig. (1) Test circuit based on ISO 6358, JIS B 8390

Solenoid Valve Flow-rate Characteristics 2

(How to indicate flow-rate characteristics)

2.2 Effective area **S**

(1) Conformed standard

**JIS B 8390: 2000: Pneumatic fluid power—Components using compressible fluids—
How to test flow-rate characteristics**

Equipment standards: JIS B 8373: 2 port solenoid valve for pneumatics

JIS B 8374: 3 port solenoid valve for pneumatics

JIS B 8375: 4 port, 5 port solenoid valve for pneumatics

JIS B 8379: Silencer for pneumatics

JIS B 8381: Fittings of flexible joint for pneumatics

(2) Definition of flow-rate characteristics

Effective area **S**: The cross-sectional area having an ideal throttle without friction or without reduced flow. It is deduced from the calculation of the pressure changes inside an air tank when discharging the compressed air in a choked flow, from an equipment attached to the air tank. This is the same concept representing the “easy to run through” as sonic conductance **C**.

(3) Formula for flow rate

When $\frac{P_2 + 0.1}{P_1 + 0.1} \leq 0.5$, **choked flow**

$$Q = 120 \times S (P_1 + 0.1) \sqrt{\frac{293}{273 + t}} \dots\dots\dots(3)$$

When $\frac{P_2 + 0.1}{P_1 + 0.1} > 0.5$, **subsonic flow**

$$Q = 240 \times S \sqrt{(P_2 + 0.1) (P_1 - P_2)} \sqrt{\frac{293}{273 + t}} \dots\dots\dots(4)$$

Conversion with sonic conductance **C**:

$$S = 5.0 \times C \dots\dots\dots(5)$$

Q : Air flow rate [dm³/min(ANR)], dm³ (cubic decimetre) of SI unit are allowed to be described by L (litre).
1 dm³ = 1 L

S : Effective area [mm²]

P₁ : Upstream pressure [MPa]

P₂ : Downstream pressure [MPa]

t : Temperature [°C]

Note) Formula for subsonic flow (4) is only applicable when the critical pressure ratio **b** is unknown for equipment. In the formula (2) by the sonic conductance **C**, it is the same formula as when **b** = 0.5.

(4) Test method

Attach a test equipment with the test circuit shown in Fig. (2) in order to discharge air into the atmosphere until the pressure inside the air tank goes down to 0.25 MPa (0.2 MPa) from an air tank filled with the compressed air at a certain pressure level (0.5 MPa) which does not go below 0.6 MPa. At this time, measure the discharging time and the residual pressure inside the air tank which had been left until it turned to be the normal values to determine the effective area **S**, using the following formula. The volume of an air tank should be selected within the specified range by corresponding to the effective area of an equipment for test. In the case of JIS B 8373, 8374, 8375, 8379, 8381, the pressure values are in parentheses and the coefficient of the formula is 12.9.

$$S = 12.1 \frac{V}{t} \log_{10} \left(\frac{P_s + 0.1}{P + 0.1} \right) \sqrt{\frac{293}{T}} \dots\dots\dots(6)$$

S : Effective area [mm²]

V : Air tank capacity [dm³]

t : Discharging time [s]

P_s : Pressure inside air tank before discharging [MPa]

P : Residual pressure inside air tank after discharging [MPa]

T : Temperature inside air tank before discharging [K]




Fig. (2) Test circuit based on JIS B 8390

2.3 Flow coefficient C_v factor

The United States Standard ANSI/(NFPA)T3.21.3: 1990: Pneumatic fluid power—Flow rating test procedure and reporting method—For fixed orifice components

Defines the flow coefficient, C_v factor by the following formula which is based on the test conducted by the test circuit analogous to ISO 6358.

$$C_v = \frac{Q}{114.5 \sqrt{\frac{\Delta P (P_2 + P_a)}{T_1}}} \dots\dots\dots(7)$$

ΔP : Pressure drop between the static pressure tapping ports [bar]

P_1 : Pressure of the upstream tapping port [bar gauge]

P_2 : Pressure of the downstream tapping port [bar gauge]: $P_2 = P_1 - \Delta P$

Q : Flow rate [dm³/s standard condition]

P_a : Atmospheric pressure [bar absolute]

T_1 : Upstream absolute temperature [K]

Test conditions are $P_1 + P_a = 6.5 \pm 0.2$ bar absolute, $T_1 = 297 \pm 5$ K, $0.07 \text{ bar} \leq \Delta P \leq 0.14$ bar.

This is the same concept as effective area A which ISO 6358 stipulates as being applicable only when the pressure drop is smaller than the upstream pressure and the compression of air does not become a problem.

3. Process fluid control equipment

(1) Conformed standard

IEC60534-2-3: 1997: Industrial-process control valves. Part 2: Flow capacity, Section Three-Test procedures

JIS B 2005: 1995: How to test flow coefficient of a valve

Equipment standards: JIS B 8471: Solenoid valve for water

JIS B 8472: Solenoid valve for steam

JIS B 8473: Solenoid valve for fuel oil

(2) Definition of flow-rate characteristics

A_v factor: Value of the clean water flow rate represented by m³/s which runs through a valve (equipment for test) when the pressure differential is 1 Pa. It is calculated using the following formula.

$$A_v = Q \sqrt{\frac{\rho}{\Delta P}} \dots\dots\dots(8)$$

A_v : Flow coefficient [m²]

Q : Flow rate [m³/s]

ΔP : Pressure differential [Pa]

ρ : Fluid density [kg/m³]

(3) Formula for flow rate

Described by the practical units. Also, the flow-rate characteristics are shown in Graph (2).

In the case of liquid:

$$Q = 1.9 \times 10^6 A_v \sqrt{\frac{\Delta P}{G}} \dots\dots\dots(9)$$

Q : Flow rate [L/min]

A_v : Flow coefficient [m²]

ΔP : Pressure differential [MPa]

G : Specific gravity [water = 1]

In the case of saturated steam:

$$Q = 8.3 \times 10^6 A_v \sqrt{\Delta P (P_2 + 0.1)} \dots\dots\dots(10)$$

Q : Flow rate [kg/h]

A_v : Flow coefficient [m²]

ΔP : Pressure differential [MPa]

P_1 : Upstream pressure [MPa]: $\Delta P = P_1 - P_2$

P_2 : Downstream pressure [MPa]

Solenoid Valve Flow-rate Characteristics 3

(How to indicate flow-rate characteristics)

Conversion of flow coefficient:


$$Av = 28 \times 10^{-6} Kv = 24 \times 10^{-6} Cv \dots\dots\dots(11)$$

Here,

Kv factor : Value of the clean water flow rate represented by m³/h which runs through a valve at 5 to 40°C, when the pressure differential is 1 bar.

Cv factor (Reference values): Value of the clean water flow rate represented by US gal/min which runs through a valve at 60°F, when the pressure differential is 1 lbf/in² (psi).

Value is different from **Kv** and **Cv** factors for pneumatic purpose due to different test method.



Graph (2) Flow-rate characteristics

Example 1)

Obtain the pressure differential when water 15 [L/min] runs through a solenoid valve with an **Av** = 45 × 10⁻⁶ [m²]. Since **Qo** = 15/45 = 0.33 [L/min], according to Graph (2), if reading **ΔP** when **Qo** is 0.33, it will be 0.031 [MPa].

Example 2)

Obtain the saturated steam flow rate when **P1** = 0.8 [MPa], **ΔP** = 0.008 [MPa] with a solenoid valve with an **Av** = 1.5 × 10⁻⁶ [m²].

According to Graph (2), if reading **Qo** when **P1** is 0.8 and **ΔP** is 0.008, it is 0.7 [kg/h]. Therefore, the flow rate **Q** = 0.7 × 1.5 = 1.05 [kg/h].

(4) Test method

Attach a test equipment with the test circuit shown in Fig. (3). Next, pour water at 5 to 40°C, then measure the flow rate with a pressure differential of 0.075 MPa. However, the pressure differential needs to be set with a large enough difference so that the Reynolds number does not go below a range of 4 × 10⁴.

By substituting the measurement results for formula (8) to figure out **Av**.





Fig. (3) Test circuit based on IEC60534-2-3, JIS B 2005

Series VX21/22/23

Flow-rate Characteristics 1

Note) Use this graph as a guide. In the case of obtaining an accurate flow rate, refer to pages 30 through to 33.


For Air



How to read the graph

The sonic range pressure to generate a flow rate of 400 L/min (ANR) is $P_1 \approx 0.2$ MPa for a ø4 orifice and $P_1 \approx 0.58$ MPa for a ø3 orifice.

For Water



How to read the graph


When a water flow of 2 L/min is generated, $\Delta P \approx 0.013$ MPa for a valve with ø3 orifice.

Series VX21/22/23

Flow-rate Characteristics 2

Note) Use this graph as a guide. In the case of obtaining an accurate flow rate, refer to pages 32 through to 35.


For Saturated Steam



How to read the graph

The sonic range pressure to generate a flow rate of 15 kg/h is $P_1 \approx 0.55$ MPa for a $\phi 2$ orifice and $P_1 \approx 0.28$ MPa for a $\phi 3$ orifice. The amount of potential heat varies somewhat based on the pressure P_1 . At 15 kg/h, there will be approximately 9700 kcal/h of heat.


Replacement Parts For Air, Medium Vacuum, Water, Oil



• DIN Connector Part No.

Without electrical option **C18312G6GCU**

With electrical option (light) **GDM2A-L**



Electrical option L With light

• Rated voltage

1	100 VAC, 110 VAC
2	200 VAC, 220 VAC 230 VAC, 240 VAC
5	24 VDC, 24 VAC
6	12 VDC
15	48 VAC

• Gasket for DIN Connector

VCW20-1-29-1

• Lead Wire Assembly for Faston Terminal (Set of 2 pcs.)

VX021S-1-16FB



Series VX21/22/23 Specific Product Precautions 1

Be sure to read before handling.

Refer to back cover for Safety Instructions, "Handling Precautions for SMC Products" (M-E03-3) and the Operation Manual for 2 Port Solenoid Valves for Fluid Control Precautions. Please download it via our website, <http://www.smcworld.com>

Design

⚠ Design

- 1. Cannot be used as an emergency shutoff valve, etc.**
The valves presented in this catalogue are not designed for safety applications such as an emergency shutoff valve. If the valves are used in this type of system, other reliable safety assurance measures should also be adopted.
- 2. Extended periods of continuous energization**
The solenoid coil will generate heat when continuously energized. Avoid using in a tightly shut container. Install it in a well-ventilated area. Furthermore, do not touch it while it is being energized or right after it is energized.
- 3. Liquid rings**
In cases with a flowing liquid, provide a bypass valve in the system to prevent the liquid from entering the liquid seal circuit.
- 4. Actuator drive**
When an actuator, such as a cylinder, is to be driven using a valve, take appropriate measures to prevent potential danger caused by actuator operation.
- 5. Pressure (including vacuum) holding**
It is not usable for an application such as holding the pressure (including vacuum) inside of a pressure vessel because air leakage is entailed in a valve.
- 6. When the conduit type is used as equivalent to an IP65 enclosure, install a wiring conduit, etc.**
- 7. When an impact, such as water hammer, etc., caused by the rapid pressure fluctuation is applied, the solenoid valve may be damaged. Give an attention to it.**

Selection

⚠ Warning

- 1. Fluid**
 - 1) Type of fluid**
Before using a fluid, check whether it is compatible with the materials of each model by referring to the fluids listed in this catalogue. Use a fluid with a kinematic viscosity of 50 mm²/s or less. If there is something you do not know, please contact SMC.
 - 2) Flammable oil, Gas**
Check the specifications for leakage in the interior and/or exterior area.
 - 3) Corrosive gas**
Cannot be used since it will lead to cracks by stress corrosion or result in other incidents.
 - 4) Depending on water quality, a brass body can cause corrosion and internal leakage may occur. If such abnormalities occur, exchange the product for a stainless steel body.**
 - 5) Use an oil-free specification when any oily particle must not enter the passage.**
 - 6) Applicable fluid on the list may not be used depending on the operating condition. Give adequate confirmation, and then determine a model, just because the compatibility list shows the general case.**

Selection

⚠ Warning

2. Fluid quality

<Air>

1) Use clean air.

Do not use compressed air that contains chemicals, synthetic oils including organic solvents, salt or corrosive gases, etc., as it can cause damage or malfunction.

2) Install an air filter.

Install an air filter close to the valve on the upstream side. A filtration degree of 5 μm or less should be selected.

3) Install an aftercooler or air dryer, etc.


Compressed air that contains excessive drainage may cause malfunction of valves and other pneumatic equipment. To prevent this, install an aftercooler or air dryer, etc.

4) If excessive carbon powder is generated, eliminate it by installing a mist separator on the upstream side of valves.

If excessive carbon powder is generated by the compressor, it may adhere to the inside of the valves and cause a malfunction.

<Vacuum>

Please be aware that there is a range of pressure that can be used.



Vacuum piping direction: if the system uses a vacuum pump, we ask that you install the vacuum pump on the secondary side. Also, install a filter on the primary side, and be careful that no foreign material is picked up.

Please replace the valve after operating the device approximately 300,000 times.



Series VX21/22/23 Specific Product Precautions 2

Be sure to read before handling.

Refer to back cover for Safety Instructions, "Handling Precautions for SMC Products" (M-E03-3) and the Operation Manual for 2 Port Solenoid Valves for Fluid Control Precautions. Please download it via our website, <http://www.smcworld.com>

Selection

Warning

<Water>

The use of a fluid that contains foreign objects can cause problems such as malfunction and seal failure by promoting wear of the valve seat and armature, and by sticking to the sliding parts of the armature, etc. Install a suitable filter (strainer) immediately upstream from the valve. As a general rule, use 80 to 100 mesh.

The supply water includes materials that create a hard sediment or sludge such as calcium and magnesium. Sediment and sludge can cause the valve to not operate properly. Therefore, install a water softening device, which removes these materials, and a filter (strainer) directly in front of the valve.

Tap water pressure:

The water pressure for tap water is normally 0.4 MPa or less. However, in places like a high-rise building, the pressure may be 1.0 MPa. When selecting tap water, be careful of the maximum operating pressure differential.

When using water or heated water, poor operation or leaks may be caused by dezincification, erosion, corrosion, etc. The brass (C37) body of this product uses dezincification-resistant material as a standard. We also offer a stainless steel body type with improved corrosion resistance. Please use the one that fits your needs.

<Oil>

Generally, FKM is used as seal material, as it is resistant to oil. The resistance of the seal material may deteriorate depending on the type of oil, manufacturer or additives. Check the resistance before using. The kinematic viscosity must not exceed 50 mm²/s

<Steam>

The use of a steam that contains foreign objects can cause problems such as malfunction and seal failure by promoting wear of the valve seat and armature, and by sticking to the sliding parts of the armature, etc. Install a suitable filter (strainer) immediately upstream from the valve.

As a standard, the mesh count for the strainer is 100 mesh. However, the size and shape of foreign objects that occur depends on the operating environment. Check the fluid status and choose an appropriate mesh count.

The supply water to a boiler includes materials that create a hard sediment or sludge such as calcium and magnesium. Sediment and sludge from steam can cause the valve to not operate properly. Install a water softening device, which removes these materials. Do not use operation steam which contains chemicals, synthetic oils containing organic solvents, salts or corrosive gases, etc., as these can cause damage or deterioration.

3. Ambient environment

Use within the operable ambient temperature range. Check the compatibility between the product's composition materials and the ambient atmosphere. Be certain that the fluid used does not touch the external surface of the product.

4. Countermeasures against static electricity

Take measures to prevent static electricity since some fluids can cause static electricity.

Selection

Warning


5. Low temperature operation

- 1) The valve can be used in an ambient temperature of between -20 to -10°C. However, take measures to prevent freezing or solidification of impurities, etc.
- 2) When using valves for water application in cold climates, take appropriate countermeasures to prevent the water from freezing in tubing after cutting the water supply from the pump, by draining the water, etc. When warming by a heater, etc., be careful not to expose the coil portion to a heater. Installation of a dryer, heat retaining of the body is recommended to prevent a freezing condition in which the dew point temperature is high and the ambient temperature is low, and the high flow runs.

Caution

1. Leakage voltage

Particularly when using a resistor in parallel with a switching element and using a C-R element (surge voltage suppressor) to protect the switching element, take note that leakage current will flow through the resistor, C-R element, etc., creating a possible danger that the valve may not turn off.



AC/Class B built-in full-wave rectifier coil: 10% or less of rated voltage
DC coil: 2% or less of rated voltage

2. Selecting model

Material depends on fluid. Select optimal models for the fluid.

3. When the fluid is oil.

The kinematic viscosity must not exceed 50 mm²/s.

Mounting

Warning

1. If air leakage increases or equipment does not operate properly, stop operation.

After mounting is completed, confirm that it has been done correctly by performing a suitable function test.

2. Do not apply external force to the coil section.

When tightening is performed, apply a wrench or other tool to the outside of the piping connection parts.

3. Mount a valve with its coil position upward, not downward.

When mounting a valve with its coil positioned downward, foreign objects in the fluid will adhere to the iron core leading to a malfunction. Especially for strict leakage control, such as with vacuum applications and non-leak specifications, the coil must be positioned upward.

4. Do not warm the coil assembly with a heat insulator, etc.

Use tape, heaters, etc., for freeze prevention on the piping and body only. They can cause the coil to burn out.



Series VX21/22/23 Specific Product Precautions 3

Be sure to read before handling.

Refer to back cover for Safety Instructions, "Handling Precautions for SMC Products" (M-E03-3) and the Operation Manual for 2 Port Solenoid Valves for Fluid Control Precautions. Please download it via our website, <http://www.smcworld.com>

Mounting

Warning

- Secure with brackets, except in the case of steel piping and copper fittings.
- Avoid sources of vibration, or adjust the arm from the body to the minimum length so that resonance will not occur.
- Painting and coating
Warnings or specifications printed or labelled on the product should not be erased, removed or covered up.

Piping

Warning

- During use, deterioration of the tube or damage to the fittings could cause tubes to come loose from their fittings and thrash about.
To prevent uncontrolled tube movement, install protective covers or fasten tubes securely in place.
- For piping the tube, fix the product securely using the mounting holes so that the product is not in the air.

Caution

- Preparation before piping
Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.
Install piping so that it does not apply pulling, pressing, bending or other forces on the valve body.
- Avoid connecting ground lines to piping, as this may cause electric corrosion of the system.
- Tighten threads with the proper tightening torque.
When attaching fittings to valves, tighten with the proper tightening torque shown below.

Tightening Torque for Piping

Connection thread	Proper tightening torque [N·m]
Rc1/8	7 to 9
Rc1/4	12 to 14
Rc3/8	22 to 24
Rc1/2	28 to 30

- Connection of piping to products
When connecting piping to a product, refer to its operation manual to avoid mistakes regarding the supply port, etc.
- In applications such as vacuum and non-leak specifications, use caution specifically against the contamination of foreign objects or airtightness of the fittings.

Recommended Piping Conditions

- When connecting tubes using one-touch fittings, provide some spare tube length shown in Fig. 1, recommended piping configuration.
Also, do not apply external force to the fittings when binding tubes with bands, etc. (see Fig. 2.)




Fig. 1 Recommended piping configuration

Unit: mm

Tube size	Mounting pitch A			Straight portion length
	Nylon tube	Soft nylon tube	Polyurethane tube	
ø1/8"	44 or more	29 or more	25 or more	16 or more
ø6	84 or more	39 or more	39 or more	30 or more
ø1/4"	89 or more	56 or more	57 or more	32 or more
ø8	112 or more	58 or more	52 or more	40 or more
ø10	140 or more	70 or more	69 or more	50 or more
ø12	168 or more	82 or more	88 or more	60 or more




Fig. 2 Binding tubes with bands

Wiring

Caution

- As a rule, use electrical wire with a cross sectional area of 0.5 to 1.25 mm² for wiring.
Furthermore, do not allow excessive force to be applied to the lines.
- Use electrical circuits which do not generate chattering in their contacts.
- Use voltage which is within ±10% of the rated voltage. In cases with a DC power supply where importance is placed on responsiveness, stay within ±5% of the rated value. The voltage drop is the value in the lead wire section connecting the coil.
- When a surge from the solenoid affects the electrical circuitry, install a surge voltage suppressor, etc., in parallel with the solenoid. Or, adopt an option that comes with the surge voltage protection circuit. (However, a surge voltage occurs even if the surge voltage protection circuit is used. For details, please consult with SMC.)



Series VX21/22/23 Specific Product Precautions 4

Be sure to read before handling.

Refer to back cover for Safety Instructions, "Handling Precautions for SMC Products" (M-E03-3) and the Operation Manual for 2 Port Solenoid Valves for Fluid Control Precautions. Please download it via our website, <http://www.smcworld.com>

Operating Environment

Warning

1. Do not use in an atmosphere having corrosive gases, chemicals, sea water, water, water vapor, or where there is direct contact with any of these.
2. Do not use in explosive atmospheres.
3. Do not use in locations subject to vibration or impact.
4. Do not use in locations where radiated heat will be received from nearby heat sources.
5. Employ suitable protective measures in locations where there is contact with water droplets, oil or welding spatter, etc.

Maintenance

Warning

1. Removing the product

The valve will reach a high temperature when used with high temperature fluids. Confirm that the valve temperature has dropped sufficiently before performing work. If touched inadvertently, there is a danger of being burned.

- 1) Shut off the fluid supply and release the fluid pressure in the system.
- 2) Shut off the power supply.
- 3) Remove the product.

2. Low frequency operation

Switch valves at least once every 30 days to prevent malfunction. Also, in order to use it under the optimum state, conduct a regular inspection once a half year.

Caution

1. Filters and strainers

- 1) Be careful regarding clogging of filters and strainers.
- 2) Replace filter elements after one year of use, or earlier if the pressure drop reaches 0.1 MPa.
- 3) Clean strainers when the pressure drop reaches 0.1 MPa.

2. Lubrication

When using after lubricating, never forget to lubricate continuously.

3. Storage

In case of long term storage after use with heated water, thoroughly remove all moisture to prevent rust and deterioration of rubber materials, etc.

4. Exhaust the drainage from an air filter periodically.

Operating Precautions

Warning

1. If there is a possibility of reverse pressure being applied to the valve, take countermeasures such as mounting a check valve on the downstream side of the valve.
2. When problems are caused by a water hammer, install water hammer relief equipment (accumulator, etc.), or use an SMC water hammer relief valve (Series VXR). For details, please consult with SMC.


Electrical Connections

Caution

Grommet

Class B coil: AWG20 Outside insulator diameter of 2.5 mm

Class H coil: AWG18 Outside insulator diameter of 2.1 mm




Rated voltage	Lead wire colour	
	①	②
DC (Class B only)	Black	Red
100 VAC	Blue	Blue
200 VAC	Red	Red
Other AC	Grey	Grey

* There is no polarity.

DIN terminal (Class B only)


Since internal connections are shown below for the DIN terminal, make connections to the power supply accordingly.



Terminal no.	1	2
DIN terminal	+ (-)	- (+)

* There is no polarity.

- Use a heavy-duty cord with an outside cable diameter of $\phi 6$ to 12 mm.
- Use the tightening torques below for each section.



Note) For an outside cable diameter of $\phi 9$ to 12 mm, remove the internal parts of the rubber seal before using.



Series VX21/22/23 Specific Product Precautions 5

Be sure to read before handling.

Refer to back cover for Safety Instructions, "Handling Precautions for SMC Products" (M-E03-3) and the Operation Manual for 2 Port Solenoid Valves for Fluid Control Precautions. Please download it via our website, <http://www.smcworld.com>


Electrical Connections

Caution

Conduit terminal

In the case of the conduit terminal, make connections according to the marks shown below.

- Use the tightening torques below for each section.
- Properly seal the terminal connection (G1/2) with the special wiring conduit, etc.




View A-A

(Internal connection diagram)

Conduit

When used as an IP65 equivalent, use seal to install the wiring conduit. Also, use the tightening torque below for the conduit.

Class B coil: AWG20 Outside insulator diameter of 2.5 mm
Class H coil: AWG18 Outside insulator diameter of 2.1 mm



(Connection G1/2 Tightening torque of 0.5 to 0.6 N·m)

Rated voltage	Lead wire colour	
	①	②
DC	Black	Red
100 VAC	Blue	Blue
200 VAC	Red	Red
Other AC	Grey	Grey

* There is no polarity.

Description	Part no.
Seal	VCW20-15-6


Note) Please order separately.

Electrical Circuits

Caution


[DC circuit]

Grommet, Faston terminal




Without electrical option

Grommet, DIN terminal, Conduit terminal, Conduit



With surge voltage suppressor

DIN terminal, Conduit terminal




With light/surge voltage suppressor

[AC circuit]


* For AC (Class B), the standard product is equipped with surge voltage suppressor.

Grommet, DIN terminal, Conduit terminal, Conduit



Without electrical option

DIN terminal, Conduit terminal



With light/surge voltage suppressor

One-touch Fitting

Caution

For information on handling one-touch fittings and appropriate tubing, refer to page 39 and the KQ2 series one-touch fittings in KQ2's catalogue.

The KQ2 series information can be downloaded from the following SMC website, <http://www.smc.eu>