



**CT3288ARA: Fixed 10x attenuation, readout actuator, 5 mm, cable length 1.2 m**



General purpose series 500 MHz, 10x fixed attenuation oscilloscope probe. Probe features a readout actuator pin (sense pin) on the BNC connector.

- 500 MHz (-3 dB) bandwidth
- High impedance input (10 M $\Omega$ /12 pF)
- 9–18 pF compensation range
- 300 V CAT II

Features & Benefits:

- Snap-Locking Sprung Hook
- Easily replaceable tip
- Large accessory set
- Meets IEC 61010-031
- RoHS compliant

Accessories included: 15 cm Ground Lead, 15 cm Ground Lead w/0.6 mm Jack and IC Clip, Replacement Tip, Black Snap-on Sprung Hook, Tip Insulator, IC Tip, BNC Adapter, 4 pcs. Probe Tip Ground, Deluxe Trimmer Tool, Twin Lead Adapter w/ 2 IC Clips & Identifier Rings.

The High Performance family is a high quality, general purpose set of 5mm Passive Voltage Oscilloscope probes. They are excellent replacement probes for all makes and models of oscilloscopes.

Type	5 mm Passive Voltage
Bandwidth	500 MHz
Attenuation	10x
Input Impedance	10 M $\Omega$
Input Capacitance	12 pF
Output Impedance	1 M $\Omega$
Risetime	0.7 ns
IEC Rating	300 V CAT II
Compensation	9—18 pF
Cable Length	1.2 m
Readout Actuator	
Operating Temperature	0° to +50° C
Humidity	85% RH or less (at 35° C)
RoHS (2011/65/EU)	Compliant