



RPS-CT

TE Internal #: EL7600-000

RPS-CT, Printable Tubing, Continuous Printable Tubing Type, Commercial Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, Yellow

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE COMMERCIAL GRADE RPS-CT



Printable Tubing Type: **Continuous**  
 Printable Tubing Grade: **Commercial**  
 Printable Tubing Shrink Ratio: **3:1**  
 Primary Product Color: **Yellow**  
 Supplied Inner Diameter: **9.5 mm [ .375 in ]**

[All CONTINUOUS TUBE COMMERCIAL GRADE RPS-CT \(15\)](#)

**Features**

**Product Type Features**

|                        |            |
|------------------------|------------|
| Printable Tubing Type  | Continuous |
| Printable Tubing Grade | Commercial |

**Body Features**

|                               |        |
|-------------------------------|--------|
| Printable Tubing Shrink Ratio | 3:1    |
| Primary Product Color         | Yellow |

**Dimensions**

|                                 |                             |
|---------------------------------|-----------------------------|
| Supplied Inner Diameter         | 9.5 mm[.375 in]             |
| Recovered Inside Diameter       | 3.2 mm[.125 in]             |
| Compatible Cable Diameter Range | 3.5 – 8.1 mm[.137 – .32 in] |

**Usage Conditions**

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -30 – 105 °C[-22 – 221 °F] |
|-----------------------------|----------------------------|

**Operation/Application**

|                    |  |
|--------------------|--|
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
|--------------------|--|

**Printer/Label Features**

|                     |  |
|---------------------|--|
| Recommended Printer | See TE Document 411-121005 the Printer |
|---------------------|--|



Product Ribbon Matrix

Printer Technology

Thermal Transfer

Packaging Features

Packaging Quantity

50

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUL 2021 (219)<br>Candidate List Declared Against: JUN 2020 (209)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



|  |  |  |   |
|--|--|--|---|
|  <p>TE Part # 1-2186500-1<br/>T3212-PRINTER</p> |  <p>TE Part # 1-2186502-1<br/>T3224-PRINTER</p> |  <p>TE Part # 1-2186503-1<br/>T3224-SWARE-PRINTER</p> |  <p>TE Part # CP8122-000<br/>T6112DS-PRINTER</p> |
|--|--|--|---|



### Also in the Series | RPS-CT



### Customers Also Bought





## Documents

### Product Drawings

[RPS-CT-50M-9.5-OUT-4](#)

English

---

### Datasheets & Catalog Pages

[RPS-CT, Continuous Commercial Grade Heat Shrinkable Identification](#)

English

---

### Product Specifications

[RPS](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English