

## Tap wrench Basic

For holding square-head screw taps and reamers in accordance with DIN 10

**ORION**<sup>®</sup>

### Application:

For holding square-head screw taps in accordance with DIN 10, reamers, screw extractors, screw tap extensions, tools with square mounts

### Execution:

- Housing, size 0-5, made of die-cast zinc, zinc-plated arm with knurling for medium loads

### Advantage:

- Die-cast zinc ensures excellent value for money
- Ground and hardened steel jaws



<b>Art. no.</b>	<b>13549 040</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	13549040
<b>Tap wrench size</b>	4
<b>Suitable for min./max. square socket size</b>	5.5-16 mm
<b>Min./max. reamer cutting range</b>	7-20 mm
<b>Min./max. thread-cutting area, metric</b>	9-27 mm
<b>Length</b>	480 mm
<b>Gross Weight</b>	0.974 kg
<b>Product Group</b>	109

### EAN

4039247076680