

SVJC clamp holder with internal cooling, positive

For copy, longitudinal face lathing with VC indexable insert

ATORN[®]

Application

For copy, longitudinal and face turning with VC indexable insert, 35°

Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, type V, attack angle 93°, tip angle 35°, clearance angle 7°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17833 725
ISO name	SVJC R/L 2020 K16 IK G1/8
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	29.5 mm
Programming size	25 mm
Suitable for indexable inserts	VC.. 1604..
Tool design	Left
DIN	4983

EAN-Code

4050293566642