

Heavy-duty cabinet without central partition

Optionally with solid sheet metal doors or doors with viewing windows, with drawers and shelves

[®]RasterPlan

Application:

For a total loading capacity of up to 1.65 t for very heavy loads, particularly suitable for storage of the heaviest tools, such as embossing and punching dies.

Execution:

- Extremely stable welded steel structure with brazed corners, with or without central partition
- Smooth fronts due to flush overlay doors, opening angle more than 200°, continuous rod guiding
- Doors can be locked simultaneously with a triple-point security cylinder lock, incl. 2 keys
- Cabinet base can carry a load of up to 400 kg

Delivery:

Additional door designs, e.g. perforated or slotted panel doors and sidewall lining, pull-out blocks for drawers and suitable insert material with compartment dividers, additional group or main keys and further paint colours deliverable upon request.



Art. no.	50147 343
Brand	RASTERPLAN
Manufacturer Part Number	1462.06.5024
Door design	Inspection glass
Width	1000 mm
Depth	600 mm
Height	1950 mm
Number of shelves	3 PCS
Shelf width	1000 mm
Shelf depth	600 mm
Load-carrying capacity per shelf	160 kg
Number of drawers	3 PCS
Drawer front height	1 x 100 mm, 2 x 125 mm
Drawer width (inner dimension)	889 mm
Drawer depth (inner dimension)	483 mm
Load-carrying capacity per drawer	110 kg
Pullout type	Full extension
With partition wall	No
Load-carrying capacity	1650 kg
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Cabinet colour	Light grey RAL 7035
Gross Weight	147.000 kg
Product Group	5AC

EAN

4251142238462