


## Cemented carbide milling bit

Shank diameter: 3mm



### Application:

For deburring, roughing, finishing work and post-processing on cast parts, roughly machined workpieces or welding seams - can be used in hand-guided or on stationary machines.



<b>Art. no.</b>	<b>76008 285</b>
<b>Brand</b>	BIAX DRUCKLUFT
<b>Manufacturer Part Number</b>	001952037
<b>Form</b>	Conical pointed
<b>Cutting edge length</b>	10 mm
<b>Length</b>	40 mm
<b>Serration type</b>	5
<b>Model</b>	TCI 0303
<b>DIN</b>	8033
<b>Gross Weight</b>	0.005 kg
<b>Product Group</b>	761